For: File Resubmit Date: PO No.: Approval Other. GC: Architect: Mech: Engr: Rep: (Company) (Project Manager)





# LS120HSV4

Job Name/Location:

High Efficiency Single Zone Inverter

Outdoor Unit (ODU) - LSU120HSV4 Indoor Unit (IDU) - LSN120HSV4



Tag #:

### Performance:

Cooling:

Cooling Capacity (Min~Rated~Max) (Btu/h)	1,023~11,200~13,785
SEER	21.5
EER	12.5

**Heating:** 

Heating Capacity (Min~Rated~Max) (Btu/h)	1,023~13,300~22,178
HSPF	11.0

HSPF - Heating Seasonal Performance Factor

Cooling Nominal Test Conditions: Heating Nominal Test Conditions: Indoor: 80°F DB/67°F WB Indoor: 70°F DB/60°F WB Outdoor: 95°F DB/75°F WB Outdoor: 47°F DB/43°F WB

**Electrical:** 

Power Supply (V¹/Hz/Ø)	208-230/60/1

#### **Outdoor Unit:**

MOP (A)	15
MCA (A)	10
Cooling Rated Amps (A)	8.7
Heating Rated Amps (A)	8.7
Compressor (A)	8.3
Fan Motor (A)	0.40

MOP - Maximum Overcurrent Protection MCA - Minimum Circuit Ampacity

### **Total Power Input:**

Cooling Power Input (kW)	0.90
Heating Power Input (kW)	1.0

## Piping:

Liquid Line (in, OD)	1/4
Vapor Line (in, OD)	3/8
Additional Refrigerant (oz/ft)	0.22
Min/Max Pipe Length (ft) <sup>2</sup>	6.6/65.6
Piping Length (no add'l refrigerant, ft)	41.0
Max Elevation (ft)	32.8

### **Controls Features:**

- •24-Hour on/off timer Chaos wind
- •Condensate Sensor •4-Way auto swing
- Auto changeover Connection Auto restart Energy saving Built-in low ambient
  - •Inverter (variable speed
- standard, down to 14°F compressor) (cooling mode)
  - •IDU compatible with Multi F **ODUs**
- Jet cool/Jet heat
- •3M Micro Protection Filter
- •Self-cleaning indoor coil
- •Sleep mode
- •Cooling only function
- •Smart AC module

# **Operating Range:**

**Outdoor Unit:** 

Cooling (°F DB)	14-118
Heating (°F WB)	-4-65

**Indoor Unit:** 

Cooling (°F WB)	53-75
Heating (°F DB)	60-86

#### **Unit Data:**

Refrigerant Type	R410A
Refrigerant Control	EEV
Refrigerant Charge (lbs)	2.21
ODU Sound Pressure (±3 dB(A)) <sup>3</sup>	45
IDU Sound Pressure (H/M/L/Sleep) (±3 dB(A)) <sup>3</sup>	39/33/23/19
ODU Net Unit Weight (lbs)	75
ODU Shipping Weight (lbs)	79
IDU Net Unit Weight (lbs)	20
IDU Shipping Weight (lbs)	26
Heat Exchanger Coating	GoldFin™

## Fan:


ODU Type	Propeller
IDU Type	Cross Flow
Fan Speeds (Fan/Cooling/Heating	g) 6/6/6
Quantity (ODU + IDU)	1+1
Motor/Drive	Brushless Digitally Controlled/Direct
ODU Max Air Flow Rate (CFM)	1,165
IDU Air Flow H/M/L (CFM)	353/272/191
Dehumidification (pts/hr)	2.3

#### Notes:

- 1.Acceptable operating voltage: 187V-253V.
- 2. Piping lengths are equivalent.
- 3.Sound Pressure levels are tested in an anechoic chamber under ISO Standard 1996.
- 4.All communication/power cable to be minimum 18 AWG, 4-conductor, stranded,
- shielded and must comply with applicable local and national code 5.See Engineering Manual for sensible and latent capacities
- 6. Power wiring cable size must comply with the applicable local and national code.
- 7.The indoor unit comes with a dry helium charge.
- 8.This data is rated 0 ft above sea level, with 24.6 ft of refrigerant line and a 0 ft level difference between outdoor and indoor units.
- 9. Must follow installation instructions in the applicable LG installation manual.







PI-485 - PMNFP14A0

Low Ambient Wind Baffle (Cooling operation to 0°F) - ZLABGP01A

For a complete list of available accessories, contact your LG representative For continual product development, LG reserves the right to change specifications without notice.

# Outdoor Unit (ODU) - LSU120HSV4


High Efficiency Single Zone Inverter




Tag #:

Date:

PO No.:







tem No.	Part Name	Remark
1	Discharge Air Grille	
2	Gas Pipe Connection Port	
3	Liquid Pipe Connection Port	
4	Control Box	
5	Earth Screw	

# Indoor Unit (IDU) - LSN120HSV4 High Efficiency Single Zone Inverter



Tag #:

Date:

PO No.:

