

INSTALLATION MANUAL AND OPERATING INSTRUCTIONS

P/N#240005165, Rev. 1.1 [08/06]

RETAIN THIS MANUAL FOR FUTURE REFERENCE

SAFETY SYMBOLS

The following defined symbols are used throughout this manual to notify the reader of potential hazards of varying risk levels.

A DANGER A

Indicates an imminently hazardous situation which, if not avoided, WILL result in death or serious injury.

A WARNING **A**

Indicates a potentially hazardous situation which, if not avoided, COULD result in death or serious injury.

A CAUTION A

Indicates a potential hazardous situation which, if not avoided, MAY result in minor or moderate injury. It may also be used to alert against unsafe practices.

IMPORTANT: Read the following instructions COMPLETELY before installing!!

A WARNING **A**

All installations should be done only by a qualified expert and in accordance with the appropriate Argo manual. Installing an electric appliance with improper methods or materials may result in serious injury or death due to fire.

INTRODUCTION

This manual is intended to familiarize the installer and user of the Argo IR882 Control Board with its installation and operation, to assure normal troublefree performance of the control.

Argo controls are designed and manufactured with quality components to require minimal service and for maximum life and durability. Read these instructions before installing and operating the control. It is imperative that the instructions be followed carefully to insure a satisfactory installation. Failure to do so may result in breach of warranty.

MOUNTING INSTRUCTIONS

Mount the control horizontally on a solid wall or part tion. For your convenience this recommended that the control be mounted as close as possible to the device to be controlled. The control should never be mounted more than 75 feet away. Select a location that is easily accessible for installation and service.

NOTE: To reduce the possibility of re lay noise that is sometimes amplified by mounting surfaces such as sheet met al plasterboard, and similar materials, place rubber or felt washers between the case and the mounting surface

- Slide the Argo R882 Series Control Board out of the mounting rail
- 2 Position the mounting rail and mount t using at least 2 screws (not provided)
- 3. Slide the R882 Control Board back into the mounting rail.

ELECTRICAL SPECIFICATIONS & WIRING



ELECTRICAL SHOCK HAZARD! Disconnect power before install ing or servicing. Can cause severe personal injury, death, or substantial property damage if ignored.

ELECTR CAL SPECIFICATIONS & WIR NG

IR882 Features

- The IR882 Is designed to interface solid state thermostats to other systems to prevent chatter sometimes caused by power robbing thermostats.
- Each module contains three (3) SPST relays
- Modules can be easily chained for additional thermostats.
- Isolation of power sources.

General Wiring Notice

All primary wiring must be 14 AWG minimum. Torque terminal screws 6 to 7 inch pounds

U.S A. - National Electric Code and any other national state or local code requirements W r ing must be N.E.C. Class 1


CANADA C.S.A. C22.1 Canadian Electrical Code Part 1 and any other national, provincial, or local code requirements. Wiring must be C.S.A. C22.1 C.E.C. Part 1.

Power Requirements

The IR882 requires 24 VAC connection to the "24 VAC Input" terminals (left side of board). The power available at the "24 VAC Output" terminals is limited by the VA rating of the transformer used. (Transformer not included.)

| Electrical Specifications | | | |
|---|-------------------------|------------------------|------------------------------|
| Argo Part Number | Argo Model Number | Transformer Voltage | Relay Switching Action |
| Z165 | IR882 | 120V/60Hz/40Va | SPST |
| Relay rating - 2.5 amps 1/10 horsenower @ 120/240 VAC | | | |

IR882 Isolation Relay Module



24 VAC input from 24 V power source.


24 VAC output *used ONLY* for powering up other R Series board s

Note: All terminals on the IR882 are Class 2


SEQUENCE OF OPERATION

- When a thermostat calls for heat the TW-TR contacts will close and the green LED for the corresponding zone will be illuminated.
- 2 The corresponding X X terminals are then closed sending a dry contact signal to the device wired to these ter minals
- When the call from the thermostat ends the TW TR contacts will then be opened which in turn will open the corresponding X-X terminals. The green LED will also turn off.

IR882 Wiring Schematics




IR882 Applications



NOTE: 6VA per thermostat should be acceptable for most applications. Consult your thermostat manufacturer's literature for their actual VA requirements.

TECHNICAL SUPPORT

For technical support on this and all Argo products, please contact ECR International Technical Service at 1-800-325-5479. Please have your model number available when calling.



| Information Needed When Calling |
|---------------------------------|
| |
| Model Number |
| |
| Installation Date |
| |

Installer



ARGO CONTROLS

P.O. Box 4729, Utica, New York 13504 Phone: 315-797-1310 • Fax: 866-432-7329

www.argocontrols.com • E-mail: info@ecrinternational.com

In Canada Contact: ECR International Ltd. - Olsen Division, P.O. Box 900, 6800 Base Line, Wallaceburg, Ontario, Canada N8A 5E5 Ph: (519) 627-0791 • Fax: (519) 627-4719 • Web: www.ecrltd.com • E-mail: info@ecrltd.com