Job Name/Location: Tag #:

(Project Manager)

For: File Resubmit Date: Approval Other. PO No .: GC: Architect: Mech: Engr:





LA240HSV2

Art Cool™ Single Zone Inverter

Outdoor Unit (ODU)-LAU240HSV2 Indoor Unit (IDU)-LAN240HSV2

Performance:

Cooling:

Rep: (Company)

Capacity (Btu/h)	22,000
SEER	20.0
EER	10.8

Heating:

Capacity (Btu/h)	27,600
HSPF	10.0

HSPF - Heating Seasonal Performance Factor

Cooling Nominal Test Conditions: Heating Nominal Test Conditions: Indoor: 80°F DB/67°F WB Indoor: 70°F DB/60°F WB Outdoor: 95°F DB/75°F WB Outdoor: 47°F DB/43°F WB

Electrical: **Outdoor Unit:**

Power Supply (V¹/Hz/Ø)	208-230/60/1		
MOP (A)	30		
MCA (A)	19		
Cooling Rated Amps (A)	17.0		
Heating Rated Amps (A)	17.0		
Compressor (A)	14.6		
Fan Motor (A)	0.75		

MOP - Maximum Overcurrent Protection MCA - Minimum Circuit Ampacity

Indoor Unit:

Power Supply (V¹/Hz/Ø)	208-230/60/1
Cooling Power Input (kW)	2.04
Heating Power Input (kW)	1.67

Piping:


r o	
Liquid Line (in, OD)	3/8
Vapor Line (in, OD)	5/8
Additional Refrigerant (oz/ft)	0.38
Max Pipe Length (ft) ²	98
Piping Length (no add'l refrigerant, ft)	25
Max Elevation (ft)	49

Faat....

reature	5:		
•4-Way au	ito swing	Chaos wind	Jet cool/Jet heat
•24-Hour	on/off timer	 Condensate Sensor 	Plasma air purifying
 Auto rest 	art	Connection	system
Auto cha	ngeover	Energy saving	 Self-cleaning indoor coil
•Built-in lo	ow ambient	•Inverter (variable speed	•Sleep mode
standard,	down to 14°F	compressor)	 Ultra quiet operation
(cooling m	iode)		

Optional Accessories (sold separately):

■ 7-Day Programmable Controller (Black) - PQRCVSL0
7-Day Programmable Controller (White) - PQRCVSL0QW
Dry Contact for third party thermostat - PQDSBNGCM1







Operating Range:

Outdoor Unit:

Cooling (°F DB)	14-118
Heating (°F DB)	5-75

Indoor Unit:

Cooling (°F DB)	64-90
Heating (°F DB)	61-86

Unit Data:

Refrigerant Type	R410A
Refrigerant Control	EEV
Refrigerant Charge (lbs)	3.97
ODU Sound Pressure Max (±3 dB(A)) ³	53
IDU Sound Pressure (H/M/L) (±3 dB(A)) ³	45/40/35
ODU Net Unit Weight (lbs)	133
ODU Shipping Weight (lbs)	142
IDU Net Unit Weight	38
IDU Shipping Weight (lbs)	42
Heat Exchanger Coating	GoldFin™
Communication Cable (No x AWG) ⁴	4 x 18

AWG - American Wire Gage

Fan:

Propeller
Cross Flow
ing) 5/6/6
1+1
Brushless Digitally Controlled/Direct
2,119
) 600/510/420
5.5

Notes:

- 1.Acceptable operating voltage: 187V 253V.
- 2. Piping lengths are equivalent.
- 3.Sound Pressure levels are tested in an anechoic chamber under ISO Standard 1996.
- 4.All communication cable to be minimum 18 AWG, 2-conductor, stranded, shielded and must comply with applicable local and national code.
- 5.See Engineering Manual for sensible and latent capacities.
- 6.Power wiring cable size must comply with the applicable local and national code.
- 7. The indoor unit comes with a dry helium charge
- 8. This data is rated 0 ft above sea level, with 24.6 ft of refrigerant line and a 0 ft level difference between outdoor and indoor units.
- 9. Must follow installation instructions in the applicable LG installation manual.

Standard Features:

- •Limited Five Year Compressor Warranty
- •Limited Three Year Functional Parts Warranty









Outdoor Unit (ODU)-LAU240HSV2 Art Cool™ Single Zone Inverter



Tag #:
Date:
PO No.:





_	_	_	_	_	_	_	
ת	5	4	3	2	1	Item No.	
SVC value cover	Earth screw	Power & Transmission connection	Liquid pipe connection	Gas pipe connection	Air discharge grille	Part Name	
						R emarks	

Indoor Unit (IDU)-LAN240HSV2


Art Cool™ Single Zone Inverter




Tag #:

Date:

PO No.:





Unit: inch

Item No.	Part Name Front Panel	Remarks
1	Front Panel	
2	Display & Signal Receiver	
ω	Air Suction Grille	
4	Installation Plate	

AHR	CERTIFIED TM WWW.ahridirectory.org
Unitary Small AC AHRI Standard 210/2 Certification applies only when	40 n the complete system is listed with AHRI.

Page 3 of 3