





| Technical Data | | LF24(-S) US |
|------------------------|--------------|-----------------------------------------|
| Power supply | | 24 VAC ± 20% 50/60 Hz |
| | | 24 VDC ± 10% |
| Power consumption | running | 5 W |
| | holding | 2.5 W |
| Transformer sizing | | 7 VA (class 2 power source) |
| Electrical connection | | 3 ft, 18 GA appliance cable |
| (LF24-S US has 2 cable | es) | 1/2" conduit connector |
| Overload protection | | electronic throughout 0 to 95° rotation |
| Angle of rotation | | max. 95°, adjust. with mechanical stop |
| Torque | | 35 in-lb [4 Nm] |
| Direction of rotation | | reversible with cw/ccw mounting |
| Position indication | | visual indicator, 0° to 95° |
| | | (0° is spring return position) |
| Running time | motor | < 40 to 75 sec |
| (nominal) | spring | < 25 sec @-4°F to 122°F [-20°C to 50°C] |
| | | < 60 sec @-22°F [-30°C] |
| Humidity | | 5 to 95% RH non-condensing |
| Ambient temperature | | -22°F to 122°F [-30°C to 50°C] |
| Storage temperature | | -40°F to 176°F [-40°C to 80°C] |
| Housing | | NEMA type 2 / IP54 |
| Housing material | | zinc coated steel |
| Agency listings | | cULus acc. to UL 873 and |
| | | CAN/CSA C22.2 No. 24-93 |
| Noise level (max) | running | < 50 db (A) |
| sp | oring return | 62 dB (A) |
| Servicing | | maintenance free |
| Quality standard | | ISO 9001 |
| Weight | LF24 | 3.1 lbs (1.40 kg) |
| | LF24-S | 3.2 lbs (1.45 kg) |
| | | |

LF24-S US

| Auxiliary switch | 1 x SPDT 3A (0.5A) @ 250 VAC, UL Approved |
|------------------|-------------------------------------------|
| | adjustable 0° to 95° (double insulated) |

Torque min. 35 in-lb, for control of air dampers

Application

For On/Off, fail-safe control of dampers in HVAC systems. Actuator sizing should be done in accordance with the damper manufacturer's specifications. Control is On/Off from an auxiliary contact, digital output, or a manual switch.

The actuator is mounted directly to a damper shaft from 3/8" up to 1/2" in diameter by means of its universal clamp, 1/2" shaft centered at delivery. For shafts up to 3/4" use K6-1 accessory. A crank arm and several mounting brackets are available for applications where the actuator cannot be direct coupled to the damper shaft.

Operation


The LF series actuators provide true spring return operation for reliable fail-safe application and positive close off on air tight dampers. The spring return system provides consistent torque to the damper with, and without, power applied to the actuator.

The LF series provides 95° of rotation and is provided with a graduated position indicator showing 0° to $95^\circ.$

The actuator may be stalled anywhere in its normal rotation without the need of mechanical end switches. Power consumption is reduced in holding mode.

The LF24-S US version is provided with one built in auxiliary switch. This SPDT switch is provided for safety interfacing or signaling, for example, for fan start-up. The switching function is adjustable between 0° and 95°. The auxiliary switch in the LF24-S is double insulated so an electrical ground connection is not necessary.







| Accessories | | |
|-----------------------|---------------------------------------------------------------------|--|
| AV 10-18 | Shaft extension (K6-1 is required) | |
| IND-LF | Damper position indicator | |
| K6-1 | Universal clamp for up to 3/4" diameter shafts | |
| KH-LF | Crank arm for up to 1/2" round shaft | |
| Tool-06 | 8mm and 10 mm wrench | |
| ZG-LF2 | Crank arm adaptor kit for LF | |
| ZG-112 | Mounting bracket for Honeywell Mod IV, M6415 | |
| | type actuators, and new installations | |
| ZG-LF112 | Crank arm adaptor kit for Honeywell Mod IV, | |
| | M6415 type actuators, and new installations | |
| ZS-100 | Weather shield (metal) | |
| ZS-150 | Weather shield (polycarbonate) | |
| ZS-260 | Explosion-proof housing | |
| NOTE: When using LE24 | IS and E24-S US actuators, only use accessories listed on this page | |

NOTE: When using LF24 US and LF24-S US actuators, only use accessories listed on this page. For actuator wiring information and diagrams, refer to Belimo Wiring Guide.

Typical Specification

On/Off spring return damper actuators shall be direct coupled type which require no crank arm and linkage and be capable of direct mounting to a shaft up to a 3/4" diameter and center a 1/2" shaft. The actuators must be designed so that they may be used for either clockwise or counterclockwise fail-safe operation. Actuators shall be protected from overload at all angles of rotation. If required, one SPDT auxiliary switch shall be provided having the capability of being adjustable. Actuators with auxiliary switch must be constructed to meet the requirements for Double Insulation so an electrical ground is not required to meet agency listings. Actuators shall be cULus listed, have a 5 year warranty, and be manufactured under ISO 9001 International Quality Control Standards. Actuators shall be as manufactured by Belimo.

Wiring Diagrams

🔀 INSTALLATION NOTES

- Provide overload protection and disconnect as required.
- <u>CAUTION Equipment Damage!</u> Actuators may be connected in parallel.

Power consumption and input impedance must be observed.

- Actuators may also be powered by 24 VDC.
- For end position indication, interlock control, fan startup, etc., LF24-S US incorporates a built-in auxiliary switch: 1 x SPDT, 3A (0.5A) @250 VAC, UL Approved, adjustable 0° to 95°.

APPLICATION NOTES

Meets cULus requirements without the need of an electrical ground connection.

WARNING Live Electrical Components!

During installation, testing, servicing and troubleshooting of this product, it may be necessary to work with live electrical components. Have a qualified licensed electrician or other individual who has been properly trained in handling live electrical components perform these tasks. Failure to follow all electrical safety precautions when exposed to live electrical components could result in death or serious injury.

