

Invensys Energy Solutions Building Systems - Americas 1354 Clifford Avenue P.O. Box 2940 Loves Park, IL 61132-2940 www.invensysibs.com

# MAx-305 & MAx-318 Series MAx-405 thru MAx-419 Series

Oil Submerged Actuators, Two-Position General Instructions

## **Application**


For two-position operation of dampers, valves, and other equipment which require the return to normal position upon power interruption.


### **Features**

- · Compatible with most SPST control devices
- · Spring return
- 24, 120, 208, and 240 Vac models
- Actuators with part number suffix "-500" are equipped with SPDT auxiliary switch
- Rugged die cast aluminum with two 1/2" conduit openings
- · Oil immersed motor and gear train

### **Applicable Literature**

- Invensys Building Systems Cross-Reference Guide, F-26789
- · Invensys Building Systems Catalog, F-25683
- AV-390 Series, Valve Linkage for Gear Train Actuators General Instructions, F-24376.
- Material Safety Data Sheet (MSDS) for BCS-51-168
   Oil (Until Feb. 1989)
- Material Safety Data Sheet (MSDS) for BCS-51-185
   Oil (Until March 2002) (MAx-3xx-x-x-3 and MAx-4xx-x-x-3)
- Material Safety Data Sheet (MSDS) for BCS-51-185-1 Oil (Current) (MAx-3xx-x-x-4 and MAx-4xx-x-x-4)
- High Temperature Exposure Performance (UL 555S) MAx-31x-x-x-4, MAx-41x-x-x-4 Series Actuators Engineering Information EN-216, F-27068









MA6-3XX, MA6-4XX, MA7-4XX, MA8-3XX, MA8-4XX (Hazardous Locations)

Printed in U.S.A. 4-02 F-06491-25

### **SPECIFICATIONS**

### **Actuator Inputs**

Connections: Coded screw terminals.

Control Circuit: Two-wire. Power Input: See Table-1.

### **Actuator Outputs**

Torque: See Table-1.

**Shaft Rotation:** 

MA-305, MA-405, MA6-305, MA6-405, CW 180° when power is applied.
MA-318, MA-41x, MAx-318, MAx-41x, CW 170° when power is applied.

Spring Return: CCW to the original position when the actuator is de-energized.

Auxiliary Switch (-500 Models): SPDT makes (or breaks) the circuit at the powered end

of stroke.

#### **Environment**

### **Ambient Temperature Limits:**

**Shipping & Storage,** -40 to 136 °F (-40 to 58 °C).

**Operating**, -40 to 136 °F (-40 to 58 °C). **Humidity:** 5 to 95% RH, non-condensing.

Location: NEMA Type 4 when used with the gasket (provided) and water-tight conduit

connectors (not provided).

### **Agency Listings:**

**UL 873**, Underwriters Laboratories (File #E9429 Category Temperature Indicating and Regulating Equipment).

CSA, Certified by Canadian Standards Association, C22.2 No. 24 (File #LR3728).

Table-1 Model Chart.

Part Number	Power Supply		Aux.	Input	VA		Rated Torque	No Load Timing in	Mounting	Application
	Vac	Hz	Switch <sup>a</sup>	Watts	Running	Holding	lb-in. (N-m)	Seconds at 75 °F (24 °C) <sup>b</sup>	oug	Application
MA-305	24		No	- 25	56	56	- 16 (1.8)	20	Any Position (Horizontal Output Shaft	Damper
MA-305-500	24		Yes							
MA-405	120	60	No		48	48			Position	Actuators
MA-405-500	120		Yes						Preferred)	
MA-318		50	No		92	32	- 60 (6.8)		Output Shaft Must Be Horizontal	Damper and Valve Actuators
MA-318-500	24		Yes							
MA5-318			No							
MA5-318-500			Yes							
MA-416	208		No	70	104	104 38				
MA-416-500	200		Yes	Running	104					
MA-418	120		No	25	108	42				
MA-418-500	120		Yes	Holding	108					
MA-419	240		No	- -	120	39				
MA-419-500			Yes							
MA5-419	240		No							
MA5-419-500		50	Yes							

a 4.4 FLA, 26.4 LRA @ 24 or 120 Vac; 2.4 FLA, 13.2 LRA @ 240 Vac.

b Spring return timing with full load opposing spring is approximately 60 sec.

Table-2 Actuator Part Numbers for Hazardous Location Applications.

Standard	Hazardous Location Actuators Part Numbers <sup>b c</sup>			
Part Numbers <sup>a</sup>	Damper Actuators	Valve Actuators		
MA-305	MA6-305	_		
MA-305-500	MA6-305-500	_		
MA-405	MA6-405	_		
MA-405-500	MA6-405-500	<del>-</del>		
MA-318	MA6-318	MA8-318		
MA-318-500	MA6-318-500	MA8-318-500		
MA-416	MA6-416	MA8-416		
MA-416-500	MA6-416-500	MA8-416-500		
MA-418	MA6-418	MA8-418		
MA-418-500	MA6-418-500	MA8-418-500		
MA-419	MA6-419	MA8-419		
MA-419-500	MA6-419-500	MA8-419-500		
MA5-419	MA7-419	MA7-419		
MA5-419-500	MA7-419-500	MA7-419-500		

<sup>&</sup>lt;sup>a</sup> MAx-31x-x-x-4 and MAx-41x-x-x-4 series actuators provide significantly improved high temperature exposure performance for use in smoke or fire dampers, or combination smoke and fire dampers. Refer to Engineering Information EN-216 (UL 555S), F-27068.

### **ACCESSORIES**

Dam	per	On	lγ
-----	-----	----	----

AM-111	Crank arm for 5/16" diameter damper shaft
AM-112	Crank arm for 3/8" diameter damper shaft
AM-113	Crank arm for 1/2" diameter damper shaft
AM-115	Crank arm for 7/16" diameter damper shaft
AM-122	Linkage connector straight type
AM-123	Damper clip
AM-125	5/16" diameter x 20" damper rod
AM-125-048	5/16" diameter x 48" damper rod
AM-132	Ball joint connector
AM-161	Damper linkage kit
AM-161-1	Damper linkage kit
AM-301	90° mounting bracket (not used with MA6-XXX, MA7-XXX, & MA8-XXX)

### Valve Only (To be used with 60 lb-in. (6.8 N-m) actuators only, excluding MA7-XXX & MA8-XXX)

e for 2-1/2" & 3" VB-9323
3

AV-391 Linkage for 1/2" to 2" VB-7XXX and 1/2" to 1-1/4" obsolete VB-9XXX

AV-392 Linkage for 1-1/2" and 2" obsolete VB-9XXX AV-395 Linkage for 2-1/2" to 4" VB-92XX or VB-931X

# Valve Only (To be used with 60 lb-in. (6.8 N-m) MA7-XXX & MA8-XXX hazardous location actuators only)

NYBA-37 Stem extension for 1/2" to 2" VB-7XXX and 1/2" to 1-1/4" obsolete VB-9XXX, for

actuators assembled in hazardous locations enclosure (use with AV-391 linkage


kit)

NYBA-61 Mounting bracket for hazardous locations enclosure (use with AV-391 linkage kit)

<sup>&</sup>lt;sup>b</sup> Class 1, Groups C & D, and Class 2, Groups E, F, and G hazardous locations; refer to EN-56-2.

<sup>&</sup>lt;sup>c</sup> Models for hazardous locations are only available as factory-built enclosure/actuator assemblies.

### **TYPICAL APPLICATIONS (wiring diagrams)**



Actuator rotates 180° CW when thermostat or switch contacts are closed. Actuator spring returns when thermostat or switch contacts are open.

Aux. Switch for -500 Models

Figure-1 Typical Wiring for MA-305 and MA-405 Series.




Figure-2 Typical Wiring for MA-318, MA-416, MA-418, and MA-419 Series.

### **INSTALLATION**

### Inspection

Inspect the package for damage. If damaged, notify the appropriate carrier immediately. If undamaged, open the package and inspect the device for obvious damage. Return damaged products.

### Requirements

- Job wiring diagrams
- · Tools (not provided):
  - Digital Volt-ohm Meter (DVM)
  - Appropriate screwdriver(s) for cover and mounting screws
  - Appropriate drill and drill bit for mounting screws
  - Appropriate wrenches for adjustment of damper and valve linkages
- Appropriate accessories
- Mounting screws (not provided)
- Training: Installer must be a qualified, experienced technician



# Caution:

Warning:

and equipment damage.

 Do not apply power to the unit unless the damper linkage and/or the valve assembly have been installed.

Disconnect the power supply (line power) before installation to prevent electrical shock

Make all connections in accordance with the wiring diagram and in accordance with

national and local electrical codes. Use copper conductors only.

Avoid locations where excessive oil, dust, moisture, corrosive fumes or vibration, or an
explosive atmosphere is present. The actuator case is intended primarily to provide a
degree of protection against windblown dust, rain, sleet, and external ice formation
(NEMA Type 4).

### Mounting

Mount the actuator according to the following requirements:

- Allow a minimum of 6" (152 mm) clearance behind the actuator for access to the wiring compartment.
- 2. Locate the actuator in a weather-protected area.
- To ensure water and weather resistance, install the cover gasket (provided) and use water-tight conduit fittings.

### **Dampers**

Install the actuator and the damper linkage, so that 180° of actuator shaft rotation drives 90° of damper shaft rotation, as follows:

### **Actuator Mounting and Damper Linkage Installation**

1. Mount the actuator in an appropriate position near the damper.

### Note:

- MA-305 and MA-405 series actuators are not position-sensitive, and in damper applications, may be mounted in any position. However, the upright position is preferred.
- MA-318, MA-416, MA-418, and MA-419 series actuators must be mounted so that the output shaft lies in a horizontal position.
- To the extent possible, position the actuator to optimize the length of the damper rod needed to link it with the damper. A damper rod that is too long is not rigid enough for good control, and a damper rod that is too short makes it difficult to adjust the linkage.
- 2. Install crank arms onto the driven shaft and the actuator shaft. Tighten the crank arm on the driven shaft. Do not tighten the crank arm on the actuator shaft at this time.
- Install a linkage connector onto the actuator shaft crank arm, at the prick point. Refer to Figure-3 and Figure-4.




Figure-3 Location of Prick Point on Crank Arm.




Figure-4 180° Actuator Rotation Driving a Damper Rotation of 90°.

- Install a linkage connector onto the driven shaft crank arm, at the end of the slot. Refer to Figure-4.
- 5. Install the damper rod in the linkage connectors on both crank arms and tighten the linkage connector screws finger-tight.

**Caution:** Never attempt to turn the actuator shaft with a wrench or a crank; this may damage the actuator.

### Linkage Adjustment

- 1. Verify that the crank arm on the actuator shaft is loose. Rotate, by hand, the crank arm on the actuator to drive the linkage and the damper shaft through its full stroke, to ensure proper damper action.
- 2. For normally closed dampers, proceed as follows:
  - a. Return the damper to the closed position.
  - b. Tighten the crank arm on the actuator shaft.
  - c. Loosen the screw on one of the linkage connectors.
  - d. While pushing the damper closed, tighten the linkage connector screws to secure the damper rod.
- 3. For normally open dampers, proceed as follows:
  - a. Move the damper to approximately 85° of the full open position.
  - b. Tighten the crank arm on the actuator shaft.
  - c. Tighten the linkage connector screws to secure the damper rod.
- 4. Run the actuator back and forth through its full stroke and check for proper damper and linkage operation. Adjust the linkage if required.

**Caution:** When linking an actuator to a damper, be sure that it can complete its full stroke. If the damper stops the actuator before it has reached its electrical limit of travel on the power stroke, the actuator may be permanently damaged. Readjust the linkage as necessary.

### **Valves**

#### Note:

When mounting an actuator onto a valve, observe the following:

- Allow 3" (76 mm) of clearance above the assembled actuator and valve for the removal and reattachment of the actuator.
- Always install single-seat valves with pressure under the seat.
- Install all two-way valves so that they close against the flow. A tag or an arrow on the valve body indicates proper flow direction.
- Always install three-way mixing valves with two inlets and one outlet.
- Always install three-way diverting valves with one inlet and two outlets.
- For steam applications only, mount the actuator above the valve body at 45° from the vertical.
- MA-318, MA-416, MA-418, and MA-419 series actuators can be mounted in any upright position above the centerline of the valve body. However, the output shaft must lie in a horizontal position.

For detailed valve linkage installation instructions, refer to **AV-390 Series, Valve Linkage for Gear Train Actuators General Instructions, F-24376.** Refer to Figure-5 for the components of a typical valve installation of a standard actuator. For installing an actuator with a hazardous location housing, refer to Figure-5.




Figure-5 Typical Components for Valve Installation of Standard Actuator.




Figure-6 Typical Components for Valve Installation of Hazardous Location Actuator.

### Wiring

Two 1/2" conduit knockouts are provided on the actuator case. Refer to Figure-5 for terminal locations.




Figure-7 Actuator Terminal Locations.

Refer to Table-3 for the selection of the proper gage wire versus the length of the wire run.

Table-3 Power Wire Selection.

Actuator Series	Wire Size AWG	Maximum Run <sup>a b</sup> ft (m)	
	14	122 (37)	
MA-305	12	191 (58)	
	10	305 (93)	
MA-405	14	2800 (853)	
	14	44 (13)	
MA-318	12	68 (21)	
	10	110 (34)	
MA-416, MA-418, MA-419	14	950 (290)	
WA-410, WA-410, WA-419	12	1580 (482)	


a Each run has two wires.

### **CHECKOUT**

After the entire system has been installed and the actuator has been powered up, perform the following check for proper system operation. Check for the correct operation of the damper while the actuator is being stroked.

Note: Smoke control systems must be tested in accordance with NFPA Standard 92A.

- 1. Verify that the system wiring is properly connected and powered.
- Be sure the controller (manual or automatic) is operating properly according to system requirements.
- When the controller energizes the actuator, the output shaft must run to the end of the stroke (180° CW).
- 4. When the controller de-energizes the actuator, the spring will return the output shaft to its original position.
- 5. The action of the auxiliary switch (-500 models only) shall be as follows:
  - a. C makes to N.C. when the actuator is de-energized. Refer to Figure-8.
  - C makes to N.O. when the actuator is energized and the output shaft reaches the end of the stroke.



N.O. makes when actuator is energized and output shaft reaches end of stroke.

Figure-8 Action of Auxiliary Switch (-500 Models Only).

### THEORY OF OPERATION

MA-305 and MA-405 series actuator output shafts rotate 180 $^\circ$  clockwise when energized and spring return counterclockwise to 0 $^\circ$  when de-energized.

MA-31X and MA-41X series actuator output shafts rotate 170° clockwise when energized and spring return counterclockwise when de-energized.

MA-305 and MA-405 series actuator motors are assembled to a gear train and stall at the end of the power stroke.

MA-318, MA-416, MA-418, and MA-419 series actuators have an end of travel switch which reduces the running input from 70 watts to 25 watts at the end of clockwise shaft rotation.

b The length given is for a maximum two-wire run, for one actuator. When multiple actuators are used, determine the maximum run for each actuator by dividing the number of actuators into the corresponding maximum run.

### **MAINTENANCE**

**Caution:** MA-300 series and MA-400 series actuators that are used in applications where they are energized for extended periods of time must be electrically cycled at least once every six months to ensure correct operation.

Regular maintenance of the total system is recommended to assure sustained, optimum performance.

### **FIELD REPAIR**

None. Replace an inoperative actuator with a functional unit.

### **DIMENSIONAL DATA**




Figure-9 Dimensions of MA-3XX, MA5-318, MA-4XX, and MA5-419 (Standard) Actuators.




Figure-10 Dimensions of MA6-3XX, MA6-4XX, and MA7-4XX Damper Actuators for Hazardous Locations.




Figure-11 Dimensions of MA7-4XX, MA8-3XX, and MA8-4XX Valve Actuators for Hazardous Locations.