Job Name/Location: Tag #:

For: File Resubmit Date: Approval Other PO No.: GC:

Architect:

Mech: Engr:

Rep: (Company)

(Project Manager)



High Efficiency Single Zone Inverter Outdoor Unit (ODU) - LSU121HSV2 Indoor Unit (IDU) - LSN121HSV2

# Performance:

Cooling:

Capacity (Btu/h)	11,200
SEER	20.0
EER	12.5

SEER - Seasonal Energy Efficiency Ratio EER - Energy Efficiency Ratio

Heating:

Capacity (Btu/h)	13,300
HSPF	11.0

HSPF - Heating Seasonal Performance Factor

Heating Nominal Test Conditions: Cooling Nominal Test Conditions: Indoor: 80°F DB/67°F WB Indoor: 70°F DB/60°F WB Outdoor: 95°F DB/75°F WB Outdoor: 47°F DB/43°F WB

# **Electrical: Outdoor Unit:**

Power Supply (V¹/Hz/Ø)	208-230/60/1
MOP (A)	15
MCA (A)	10.0
Cooling Rated Amps (A)	7.3
Heating Rated Amps (A)	8.1
Compressor (A)	7.6
Fan Motor (A)	0.25

MOP - Maximum Overcurrent Protection MCA - Minimum Circuit Ampacity

# Indoor Unit:

Power Supply (V¹/Hz/Ø)	208-230/60/1
Cooling Power Input (kW)	0.90
Heating Power Input (kW)	1.0

# Piping:

Liquid Line (in, OD)	1/4
Vapor Line (in, OD)	3/8
Additional Refrigerant (oz/ft)	0.22
Max Pipe Length (ft) <sup>2</sup>	65
Piping Length (no add'l refrigerant, ft)	41
Max Elevation (ft)	32

#### **Controls Features:**

- •24-Hour on/off timer Energy saving
- 4-Way auto swing •Inverter (variable speed
- Auto changeover compressor)
- Auto restart •Jet cool/Jet heat
- Built-in low ambient standard, •Plasma air purifying system
- down to 14°F (cooling mode) •Self-cleaning indoor coil
- Chaos wind •Sleep mode
- Condensate Sensor Connection •Ultra quiet operation

# **Optional Accessories (sold separately)**

- 7-Day Programmable Controller (Black) PQRCVSL0
- 7-Day Programmable Controller (White) PQRCVSL0QW
- Low Ambient Wind Baffle (Cooling operation to 0°F) ZLABGP01A





# **Operating Range:**

**Outdoor Unit:** 

Cooling (°F DB)	14-118
Heating (°F DB)	5-75
1 1 11 2	

Indoor Unit:

Cooling (°F DB)	64-86
Heating (°F DB)	60-86

#### **Unit Data:**

Refrigerant Type	R410A
Refrigerant Control	EEV
Refrigerant Charge (lbs)	2.21
ODU Sound Pressure (±3 dB(A)) <sup>3</sup>	45
IDU Sound Pressure (±3 dB(A)) <sup>3</sup>	39/33/24
ODU Net Unit Weight (lbs)	77.2
ODU Shipping Weight (lbs)	81.6
IDU Net Unit Weight	22.1
IDU Shipping Weight (lbs)	26.5
Heat Exchanger Coating	GoldFin™
Communication Cable (No x AWG) <sup>4</sup>	4 x 18

# Fan:

	Propeller
	Cross Flow
g/Heating)	6/Auto/Chaos
	1 + 1
Brushless Digitally	Controlled/Direct
(CFM)	1,165
. (CFM)	350/280/210
r)	3.0
	g/Heating) Brushless Digitally ( (CFM) . (CFM)

# Notes:

- 1.Acceptable operating voltage: 187V-253V.
- 2. Piping lengths are equivalent.
- 3. Sound Pressure levels are tested in an anechoic chamber under ISO Standard 1996.
- 4.All communication cable to be minimum 18 AWG, 2-conductor, stranded, shielded and must comply with applicable local and national code.
- 5.See Engineering Manual for sensible and latent capacities.
- 6. Power wiring cable size must comply with the applicable local and national code.
- 7.The indoor unit comes with a dry helium charge. 8.This data is rated 0 ft above sea level, with 24.6 ft of refrigerant line and a 0 ft level difference between outdoor and indoor units.
- 9. Must follow installation instructions in the applicable LG installation manual.

# **Standard Features:**



- Limited Seven Year Compressor Warranty
- Limited Five Year Functional Parts Warranty







# Outdoor Unit (ODU) - LSU121HSV2

High Efficiency Single Zone Inverter





Unit: inch



5 E	4 Cc	3 Li	2 Ga	1 A	Item No.	
Earth Screw	Control Box	Liquid Pipe Connection Port	Gas Pipe Connection Port	Air Discharge Grille	Part Name	
					Remarks	

# Indoor Unit (IDU) - LSN121HSV2 High Efficiency Single Zone Inverter



Tag #:

Date:

PO No.:

