LV1, LV2 and LV3

LV1 - Easy Temp® Mechanical Baseboard Heat Thermostat

- For Single Pole 120/240 Volt Heating Systems
- For Baseboard Heating
- For Ceiling Cable and Other Radiant Heat Systems
- UL Listed
- 3-Year Warranty
- Contains No Mercury
- Clean Attractive Design
- Easy to Install and Use

FOR USE ON:

• 1 Stage Heat Only: Single Pole 120/240 VAC Systems up to 22 Amps

NOT FOR USE ON:

- Conventional 24V Heating and Cooling Systems
- Hydronic (Hot Water) Systems

DIMENSIONS:

115.8 mm (H) x 71.3 mm (W) x 51.6 mm (D) Approximately 35 mm (D) from wall when mounted





LV2 - Easy Temp® Mechanical Baseboard Heat Thermostat

- For Single and Double Pole 120/240 Volt Heating Systems
- For Baseboard Heating
- For Ceiling Cable and Other Radiant Heat Systems
- UL Listed
- 3-Year Warranty
- Contains No Mercury
- Clean Attractive Design
- Easy to Install and Use

FOR USE ON:

• 1 Stage Heat Only: Single and Double Pole 120/240 VAC Systems up to 22 Amps

NOT FOR USE ON:

- Conventional 24V Heating and Cooling Systems
- Hydronic (Hot Water) Systems

DIMENSIONS:

115.8 mm (H) x 71.3 mm (W) x 51.6 mm (D) Approximately 35 mm (D) from wall when mounted





LV3 - Easy Temp® Mechanical Line Voltage Cooling Thermostat

- For Single Pole 120/240 Volt Cooling Systems
- UL Listed
- 3-Year Warranty

• Contains No Mercury

- Clean Attractive Design
- Easy to Install and Use

FOR USE ON:

• 1 Stage Cool Only: Single Pole 120/240 VAC Systems up to 22 Amps

NOT FOR USE ON:

- Conventional 24V Heating and Cooling Systems
- Hydronic (Hot Water) Systems

DIMENSIONS:

115.8 mm (H) x 71.3 mm (W) x 51.6 mm (D) Approximately 35 mm (D) from wall when mounted










LV1, LV2 and LV3



SPECIFICATIONS: -

Heat/Cool Wires: Line, Load (LV1, LV3); Line 1, Line 2, Load 1, Load 2 (LV2).

Electrical Ratings: 22 Amps maximum, 125/250/277 VAC.

Temperature Control Range: 50°F to 90°F (10°C to 32°C). Accuracy: ±1°F over a range of

50°F to 90°F.

Environmental Limits:

Moisture and Dust: meets IP20.

Operating Humidity: 20% to 90% non-condensing.

Operating Temperature: $+32^{\circ}F$ to $+104^{\circ}F$ ($+0^{\circ}C$ to $+40^{\circ}C$). Storage Temperature: $-4^{\circ}F$ to $+130^{\circ}F$ ($-20^{\circ}C$ to $+54^{\circ}C$).

Electrical Immunity: UL Approved.



LUX Products Corporation 6000 | Commerce Parkway • Mt. Laurel, NJ 08054 (856) 234-7905 • FAX (856) 234-7825 • www.luxproproducts.com

JOB NAME:			DATE:
CONTRACTOR:			UNIT DESIGNATION:
ENGINEER:			MODEL NO.:
SUBMITTED FOR:	APPROVAL	RECORD	LOCATION: