



Fluidmaster®

PROJECT SUBMITTAL

Project _____ Date _____

Engineer / Architect _____

Builder / Developer _____

Plumbing Contractor _____

Fluidmaster Part Number(s) _____

Fluidmaster Faucet Water Supply Connectors

Connector Sizes and Lengths (in inches)

Faucet Connectors	Vinyl	SS	Circle Relative Sizes	Qty.
3/8" Comp., 7/16" Comp., 1/2" Comp., or 1/2" F.I.P. x 1/2" F.I.P.	N/A		9" 12" 16" 20" 30" 36"	
3/8" Comp. x 1/2" F.I.P.			12" 16" 20" 30" 36"	
1/2" F.I.P. x 1/2" F.I.P.			12" 16" 20" 30"	
1/2" Comp. x 1/2" F.I.P.	N/A		12" 16" 20" 30"	
3/8" Comp. x 3/8" Comp.	N/A		12" 16" 20"	
3/8" Comp. x 3/8" O.D. Comp.	N/A		12" 16" 20"	

Faucet Click Seal™ Connectors	Vinyl	SS	Circle Relative Sizes	Qty.
3/8" Comp., 7/16" Comp., 1/2" Comp., or 1/2" F.I.P. x 1/2" F.I.P.	N/A		16"	
1/2" Comp. x 1/2" F.I.P.	N/A		12" 16" 20" 30"	
1/2" F.I.P. x 1/2" F.I.P.	N/A		12" 16" 20" 30"	

Materials of Construction*:

Braid	304 Series Stainless Steel
Internal Hose	Polyvinyl Chloride (PVC)
Hose (<i>Vinyl Version only</i>)	Polyvinyl Chloride (PVC) Reinforced Vinyl
Plastic Coupling Nut (<i>Faucet - Click Seal™ only</i>)	Acetal Resin
Threaded insert (<i>Faucet - Click Seal™ only</i>)	Brass Alloy
Metal Nuts	Nickel Plated Brass Alloy
Ferrule	Nickel Plated Brass Alloy
Washer	Santoprene™
Nipple	Brass Alloy

**All connectors are lead free and contain a weighted average lead content of ≤ 0.25%.*

Technical Specifications

Flow Rate	7.18 to 7.26 GPM @ 80 PSI
Working Pressure	125 PSI
Working Temperature	40° F to 150° F

Plumbing Codes

IAPMO Uniform Plumbing Code
IPC International Plumbing Code
NPCC National Plumbing Code of Canada

Standards

ASME A112.18.6 / CSA B125.6
NSF Standard 61, Section 9

30800 Rancho Viejo Rd., San Juan Capistrano, CA 92675

www.fluidmaster.com

800.631.2011

M-F 7:30 am - 4:30 pm (PST)