



Submittal Data Information

Pressure Reducing Valves, Dual Controls

101-005

Numbers: 329, 329T, 335, 334, 334T

Supersedes: October 1, 1989

Effective: January 1, 2003

Job: _____ Engineer: _____ Contractor: _____ Rep: _____

ITEM NO.	MODEL NO.	

Features

- Fast Fill Rate on All Models.
- Exclusive Fast Fill Lever Lock.
- Built-In Check to Prevent Emptying the System if Incoming Pressure Fails.
- Adjustable Set Pressure of 10 to 25 psi.
- Pressure Setting Adjustment Separated from Fast Fill Lever for Easy, Fast Adjustment.

Performance Data Pressure Reducing Valves

Maximum Fluid Temperature: 212°F (100°C)
Maximum Supply Side Pressure: 100 psi (689kpa)
Set Pressure Range: 10 - 25 psi (69 - 172kpa)
Factory Setting of System Side: 12 psi (83kpa)

Performance Data Dual Controls

Maximum Fluid Temperature: 212°F (100°C)
Maximum Supply Side Pressure: 100 psi (689kpa)
Relief Valve Set to Release at: 30 psi (207kpa)

Connection Sizes

Model 329: 1/2" Sweat Union Inlet, 1/2" NPT Outlet
Model 329-T: 1/2" NPT Union Inlet, 1/2" NPT Outlet
Model 335: 3/4" NPT Union Inlet, 3/4" NPT Outlet
Model 334: 1/2" Sweat Union Inlet, 1/2" NPT Outlet
Model 334-T: 1/2" NPT Union Inlet, 1/2" NPT Outlet


Purpose

To automatically feed water to a system whenever pressure in the system drops below the pressure setting of the valve. The Dual Control combines the Boiler Feed Valve with an in-line Pressure Relief Valve connected at the outlet end.


Pressure Reducing Valves Dimensions & Weights

		A		B		C		Ship Wt.		Ship Wt. Ctn. 6	
Model	Material	in.	mm	in.	mm	in.	mm	lbs.	Kg	lbs.	Kg
329	Cast Iron	4-1/4	108	3-3/4	95	1-3/8	35	2.4	1.4	30	14
329-T	Cast Iron	4-3/8	111	3-3/4	95	1-3/8	35	2.4	1.4	30	14
335	Bronze	3-3/4	95	3-3/4	95	1-3/8	35	2.4	1.4	30	14

Models 329 & 329-T




Model 335



Dual Controls Dimensions & Weights

		A		B		C		Ship Wt.		Ship Wt. Ctn. 6	
Model	Material	in.	mm	in.	mm	in.	mm	lbs.	Kg	lbs.	Kg
334	Cast Iron	7-1/4	184	3-3/4	95	1-3/8	35	3.9	1.8	24	11
334-T	Cast Iron	7-3/8	187	3-3/4	95	1-3/8	35	3.9	1.8	24	11

Models 334 & 334-T



Do it Once. Do it Right.

Taco, Inc., 1160 Cranston Street, Cranston, RI 02920 Telephone: (401) 942-8000 Fax: (401) 942-2360

Taco (Canada), Ltd., 6180 Ordan Drive, Mississauga, Ontario L5T 2B3 Telephone: (905) 564-9422 Fax: (905) 564-9436

Visit our website at: www.taco-hvac.com

Printed in USA
Copyright 2005
TACO, Inc.