




PG9MXA 4-WAY MULTIPOISE TWO-STAGE CONDENSING GAS FURNACE

Product Data



A98071

Utilizing the extensive resources available to Payne, a new standard of excellence has been achieved with the model PG9MXA.

The model is a unique 4-way multipoise condensing furnace with features like no other product in its class. The PG9MXA builds on the many Payne successes in the furnace industry and establishes a new standard for all high-efficiency gas furnaces.

FEATURES

PG9MXA combines two heating stages to vary the amount of gas being used from low-heat to high-heat stage. The low-stage operation allows longer running periods, which helps maintain

your most comfortable temperature, prevents drafts, reduces noise, and enhances the air quality of your home. During extreme cold, the high-heat stage will run to ensure that you are still comfortable.

Highly Efficient ECM Blower Motor - The highly efficient ECM motor and Payne's control logic can help selected 13- and 14-SEER Payne Air Conditioners achieve added energy efficiency up to 1.5 SEER as compared to the Air-Conditioning and Refrigeration Institute's standard coil-only rating (A/Cs up to 3.5 tons) when paired with selected Payne evaporator coils.

Primary Heat Exchanger & Secondary Heat Exchanger - The primary heat exchanger is corrosion resistant. The secondary heat exchanger is built with a patented lamination process that bonds a corrosion-proof lining of polypropylene to a heavy, galvanized steel shell.

Hot Surface Igniter - It is capable of running at line voltage and does not require complex voltage regulators as do other brands.

Adjustable Continuous Fan - Improves comfort all year long by allowing you to select the continuous fan speed right at the thermostat.


Dehumidification - Reduces summertime humidity levels by nearly 10% over standard systems.

4-Way Multipoise Design - Allows the model PG9MXA to be installed in an upflow, downflow, or horizontal orientation. Factory configured for upflow applications with only simple drain connection changes required for conversion to downflow or horizontal.

Direct or Non-direct Venting - The PG9MXA can be installed as a Non-Direct 1-pipe vent or Direct 2-pipe vent furnace. This provides added flexibility to meet diverse installation needs.

Two-Speed Inducer Motor - This motor works with the inducer fan to optimize combustion efficiency and exhaust the flue gases out of the house.

Soft Motor Mounts - These motor mounts help to absorb shock.



- NOTES:**
- Minimum return-air openings at furnace, based on metal duct. If flex duct is used, see flex duct manufacturer's recommendations for equivalent diameters.
 - Minimum return-air opening at furnace:
 - For 800 CFM 16-in. (406mm) round or 14 1/2 (368mm) x 12-in. (305mm) rectangle.
 - For 1200 CFM 20-in. (508mm) round or 14 1/2 (368mm) x 19 1/2-in. (495mm) rectangle.
 - For 1600 CFM 22-in. (559mm) round or 14 1/2 (368mm) x 23 1/4-in. (591mm) rectangle.
 - For airflow requirements above 1800 CFM, see Air Delivery table in Product Data literature for specific use of single side inlets. The use of both side inlets, a combination of 1 side and the bottom, or the bottom only will ensure adequate return air openings for airflow requirements above 1800 CFM at 0.5" W.C. ESP.

DIMENSIONS – IN. (MM)

UNIT SIZE	A	D	E
036060	17 – 1/2 (445)	15 – 7/8 (403)	16 (406)
036080	17 – 1/2 (445)	15 – 7/8 (403)	16 (406)
048080	17 – 1/2 (445)	15 – 7/8 (403)	16 (406)
060100	21 (533)	19 – 3/8 (492)	19 – 1/2 (495)
060120	24 – 1/2 (622)	22 – 7/8 (581)	23 (584)

CLEARANCE TO COMBUSTIBLES

INSTALLATION


- This forced air furnace is equipped for use with natural gas at altitudes 0 - 10,000 ft (0 - 3,050m), except 140 size furnaces are only approved for altitudes 0 - 7,000 ft (0 - 2,135m).
- An accessory kit, supplied by the manufacturer, shall be used to convert to propane gas use or may be required for some natural gas applications.
- This furnace is for indoor installation in a building constructed on site. This furnace may be installed in a manufactured (mobile) home when stated on rating plate and using factory authorized kit.
- This furnace may be installed on combustible flooring in alcove or closet at **Minimum Inches Clearance To Combustible Construction** as described below.
- This furnace requires a special venting system. Refer to the installation instructions for parts list and method of installation. In the US this furnace is for use with schedule-40 PVC, PVC-DWV, CPVC, or ABS-DWV pipe, and must not be vented in common with other gas-fired appliances. In Canada, refer to installation instructions for vent materials. Construction through which vent/air intake pipes may be installed is maximum 24 inches (610 mm), minimum 3/4 inches (19 mm) thickness (including roofing materials).
- Cette fournaise à air pulsé est équipée pour utilisation avec gaz naturel et altitudes comprises entre 0 - 3,050m (0 - 10,000 pi), excepté queles fournaises de 140 taille sont pour altitudes comprises entre 0 - 2,135m (0 - 7,000pi).
- Utiliser une trousse de conversion, fournie par le fabricant, pour passer au gaz propane ou pour certaines installations au gaz naturel.
- Cette fournaise à air pulsé est pour installation à l'intérieur dans un bâtiment construit sur place. Cette fournaise à air pulsé peut être installée dans une maison préfabriquée (maison mobile) si prescrit par la plaque signalétique et si l'on utilise une trousse spécifiée par le fabricant.
- Cette fournaise peut être installée sur un plancher combustible dans un enfoncement ou un placard en observant les **Dégagement Minimum En Pouces Avec Éléments De Construction Combustibles**.
- Cette fournaise nécessite un système d'évacuation spécial. La méthode d'installation et la liste des pièces nécessaires figurent dans les instructions d'installation. Aux Etats-Unis, cette fournaise doit s'utiliser avec la tuyauterie des nomenclatures 40 PVC, PVC-DWV, CPVC, ou ABS-DWV et elle ne peut pas être ventilée conjointement avec d'autres appareils à gaz. Au Canada, referer aux instructions d'installation pour les matériaux à ventiler. Épaisseur de la construction au travers de laquelle il est possible de faire passer les tuyaux d'aération (admission/évacuation): 24 po (610 mm) maximum, 3/4 po (19mm) minimum (y compris la toiture).

For upflow and downflow applications, furnace must be installed level, or pitched within 1/2" (12.7mm) of level. For a horizontal application, the furnace must be pitched minimum 1/4" (6.35mm) to maximum of 1/2" (12.7mm) forward for proper drainage. See Installation Manual for IMPORTANT unit support details on horizontal applications.

Pour des applications de flux ascendant et descendant, la fournaise doit être installée de niveau ou inclinée à pas plus de 1/2" (12.7mm) du niveau. Pour une application horizontale, la fournaise doit être inclinée entre minimum 1/4" (6.35mm) et maximum 1/2" (12.7mm) du niveau pour le drainage approprié. En cas d'installation en position horizontale, consulter les renseignements IMPORTANTS sur le support dans le manuel d'installation.

LEVEL 0" (0) TO
1/2" (12.7mm) MAX

UPFLOW OR
DOWNFLOW



MIN 1/4" (6.35mm) TO
1/2" (12.7mm) MAX

HORIZONTAL

MINIMUM INCHES CLEARANCE TO COMBUSTIBLE CONSTRUCTION

ALL POSITIONS:

- * Minimum front clearance for service 24 inches (610mm).
- † † 140 size furnaces require 1 inch back clearance to combustible materials.

DOWNFLOW POSITIONS:

- † For installation on combustible floors only when installed on special base No. KGASB0201ALL or NAHA01101SB, Coil Assembly, Part No. CAR, CAP, CNPV, CNRV or Coil Casing, Part No. KCAKC, or WENC or WTNC.

HORIZONTAL POSITIONS:

- Line contact is permissible only between lines formed by intersections of top and two sides of furnace jacket, and building joists, studs, or framing.
- § Clearance shown is for air inlet and air outlet ends.
- Ø 120 and 140 size furnaces require 1 inch bottom clearance to combustible materials.

DÉGAGEMENT MINIMUM EN POUCES AVEC ÉLÉMENTS DE CONSTRUCTION COMBUSTIBLES

POUR TOUS LES POSITIONS:

- * Dégagement avant minimum de 24 po (610mm) pour l'entretien.
- † † Pour les fournaises de 140 taille, 1 po (25mm) dégagement des matériaux combustibles est requis au-arrière.

POUR LA POSITION COURANT DESCENDANT:

- † Pour l'installation sur le plancher combustible seulement quand on utilise la base spéciale, pièce n° KGASB0201ALL ou NAHA01101SB, l'ensemble serpent, pièce n° CAR, CAP, CNPV, CNRV, ou le carter de serpent, pièce n° KCAKC ou WENC ou WTNC.

POUR LA POSITION HORIZONTALE:


- Le contact n'est permis qu'entre les lignes formées par les intersections du dessus et des deux côtés de la chemise de la fournaise, et des solives, des montants ou de la charpente du bâtiment.
- § La distance indiquée concerne l'extrémité du tuyau d'arrivée d'air et l'extrémité du tuyau de sortie d'air.
- Ø Pour les fournaises de 120 et 140 taille, 1 po (25mm) dégagement des matériaux combustibles est requis au-dessous.

This furnace is approved for UPFLOW, DOWNFLOW and HORIZONTAL installations.

Cette fournaise est approuvée pour l'installation HORIZONTALE et la circulation d'air VERS LE HAUT et VERS LE BAS.

Clearance arrows do not change with furnace orientation.

Les flèches de dégagement ne change pas avec l'orientation de la génératrice d'air chaud.



Clearance in inches
Dégagement (po).

Vent clearance to combustibles 0".
0 (po) Dégagement d'évent avec combustibles.

335122-201 REV. B LIT TOP

A08435



MEETS DOE RESIDENTIAL
CONSERVATION SERVICES
PROGRAM STANDARDS

Before purchasing this
appliance, read important
energy cost and
efficiency information
available from your retailer.

These products are
engineered and
manufactured under
an ISO 9001 registered
quality system.

As an ENERGY STAR®
Partner, Payne Heating
& Cooling has determined
that this product meets the
ENERGY STAR® guidelines for
energy efficiency.

SPECIFICATIONS

PG9MXA

UNIT SIZE			036060	036080	048080	060100	060120
CAPACITY* Direct Vent (2 – pipe) (Shaded capacities are specified on the rating plate)	Low	Upflow	37000	49000	49000	61000	73000
		Downflow	36000	49000	49000	61000	73000
		Horizontal	36000	49000	49000	61000	73000
	High	Upflow	56000	75000	75000	93000	113000
		Downflow	56000	75000	75000	93000	112000
		Horizontal	56000	74000	74000	93000	112000
CAPACITY* Non–Direct vent (1 –pipe)	Low	Upflow	36000	49000	49000	61000	73000
		Downflow	36000	49000	49000	61000	73000
		Horizontal	36000	48000	49000	61000	73000
	High	Upflow	56000	75000	75000	94000	113000
		Downflow	56000	75000	75000	93000	112000
		Horizontal	56000	74000	74000	93000	112000
AFUE* Direct Vent (2–pipe) Nonweatherized ICS		Upflow	92.5				
		Downflow	91				
		Horizontal	92.1				
AFUE* Non–Direct Vent (1 –pipe) Nonweatherized ICS		Upflow	92.1				
		Downflow	90.7				
		Horizontal	91.7				
Input Btuh †	Low		39000	52000	52000	65000	78000
	High		60000	80000	80000	100000	120000
CERTIFIED TEMPERATURE RANGE(F)	High		30–60 16.5–33)	40–70 (22–38.5)	30–60 16.5–33)	30–60 16.5–33)	40–70 (22–38.5)
	Low		20–50 (11–27.5)	30–60 16.5–33)	30–60 16.5–33)	30–60 16.5–33)	30–60 16.5–33)
CERTIFIED EX STATIC PRESSURE (in. wc)		Heating	0.12	0.15	0.15	0.20	0.20
		Cooling	0.50	0.50	0.50	0.50	0.50
AIRFLOW (CFM)‡		High Heat	1040	1180	1450	1890	2065
		Low Heat	635	835	910	935	1425
		Cooling	1250	1240	1620	1635	1925
ELECTRICAL							
Unit Volts–Hertz–Phase			115–60–1				
Operating Voltage Range Min–Max**			104 – 127				
Maximum Unit Amps			8.2	8.3	9.9	12.1	12.4
Unit Ampacity††			11	11	13	15.9	16.2
Minimum Wire Size			14	14	14	12	12
Maximum Wire Length (Ft / M)‡‡			33 (10.0)	33 (10.0)	28 (8.5)	36 (11.0)	35 (10.7)
Maximum Fuse Size or Ckt Bkr Amps†††			15	15	20	20	20
Transformer (24v)			40va				
External Control Power Available		Heating	19				
		Cooling	35				
Air Conditioning Blower Relay			Standard				
CONTROLS							
Limit Control			SPST				
Heating Blower Control (Off Delay)			Selectable 90, 120, 150, or 180 seconds				
Burners (Monoport)			3	4	4	5	6
Gas Connection Size			1/2–in. (13 mm) NPT				
GAS CONTROLS							
2–Stage Redundant Gas Valve	Manufacturer		White–Rodgers				
	Min. Inlet Pressure (in. wc)		4.5 (Natural Gas)				
	Max. Inlet Pressure (In. wc)		13.5 (Natural Gas)				
Ignition Device			Hot Surface				
BLOWER DATA							
Direct–Drive Motor HP ECM–X–13			1/2	1/2	3/4	1	1
Motor Full Load Amps			6.8	6.8	8.4	10.9	10.9
RPM (Nominal) –Speeds			1050–5	1050–5	1050–5	1050–5	1050–5
Blower Wheel Diameter x Width – In. (mm)			10 X 7 (254X178)	10 X 7 (254 X 178)	11 X 8 (279 X 203)	11 X 10 (203 X 254)	11 X 10 (203 X 254)
Filter Size (In. / mm)–Permanent Washable			(1) 16 X 25 X 3/4 (406 X 635 X 19)			(1) 20 X 25 X 3/4 (508 X 635 X 19)	(1) 24 X 25 X 3/4 (610 X 635 X 19)

See notes at end of table.

SPECIFICATIONS (CONT)

FACTORY—AUTHORIZED AND LISTED DEALER—INSTALLED OPTIONS	
Gas Conversion Kit — Natural—to—Propane	KGANP4901AAA
Gas Conversion Kit — Propane—to—Natural	KGAPN4701AAA
Twinning Kit	N/A
Downflow Base***	KGASB0301ALL
Vent Termination Kit (Bracket Only for 2 Pipes)	2—in. (51 mm)—KGAVT0101BRA 3—in. (76 mm)—KGAVT0201BRA
Concentric Vent Termination Kit (Single Exit)	2—in. (51 mm)—KGAVT0701CVT 3—in. (76 mm)—KGAVT0801CVT
Condensate Freeze Protection Kit	KGAHT0101CFP
Condensate Neutralizer Kit (Obtained thru RCD)	P908—0001
Vent Exhaust Pipe External Trap Kit	KGAET0106ETK
Door Gasket Kit	KGBAC011DGK
Unframed Filter, Permanent Washable 3/4" (19 mm) 16 x 25 (406 x 635)	KGAWF1301UFR
Unframed Filter, Permanent Washable 3/4" (19 mm) 20 x 25 (508 x 635)	KGAWF1401UFR
Unframed Filter, Permanent Washable 3/4" (19 mm) 24 x 25 (610 x 635)	KGAWF1501UFR

*U.S.A. — Gas input ratings are certified for elevations to 2000 ft. (610 M). For elevations above 2000 ft. (610 M), reduce ratings 2% for each 1000 ft. (305 M) above sea level. In Canada, derate the unit 5% for elevations 2000 to 4500 ft. (610 to 1372 M) above sea level.

†Capacity and AFUE in accordance with U.S. Government DOE test procedures Effective November 10, 1997.

‡ •Airflow shown is with factory—supplied 3/4—in. (19 mm) washable filter(s).

•For air delivery above 1800 CFM, see Air Delivery table for other options.

•An airflow reduction of up to 7% may occur when using the factory—specified 4—5/16—in. (110 mm) wide, high efficiency media filter.

•For best furnace efficiency when using the 4—5/16—in. (110 mm) wide media filter, adjust the blower speed tap to near the mid—point of the rise range.

**Permissible voltage limits for proper furnace operation.

††Unit ampacity = 125% of largest component's full load amps plus 100% of all other potential operating components (EAC, humidifier, etc.)

‡‡Length shown in measured one way along wire path between unit and service panel for maximum 2% voltage drop.

***Required for installation on combustible floors when no coil box is used, or when any coil box other than a CNPV, CAPV, CAP, or CAR cased coil is used.

N/A — Not Applicable

ICS — Isolated Combustion System

MAXIMUM ALLOWABLE PIPE LENGTH – FT (M)

PG9MXA

ALTITUDE FT (M)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY	NUMBER OF 90° ELBOWS					
		TERMINATION TYPE	PIPE DIA – IN. (mm)*	PIPE DIA – IN. (mm)*	1	2	3	4	5	6
0 to 2000 (0 to 610)	60,000	2 Pipe or 2-in Concentric	1-1/2 (38)	1-1/2 (38)	20 (6.1)	15 (4.6)	10 (3.0)	5 (1.5)	NA	NA
			2 (51)	2 (51)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)
	80,000	2 Pipe or 2-in Concentric	1-1/2 (38)	1-1/2 (38)	10 (3.0)	NA	NA	NA	NA	NA
			2 (51)	2 (51)	55 (16.8)	50 (15.2)	35 (10.7)	30 (9.1)	30 (9.1)	20 (6.1)
			2-1/2 (64)	2-1/2 (64)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)
	100,000	2 Pipe or 3-in Concentric	2 (51)	2 (51)	5 (1.5)	NA	NA	NA	NA	NA
			2-1/2 (64)	2-1/2 (64)	40 (12.2)	30 (9.1)	20 (6.1)	20 (6.1)	10 (3.0)	NA
			3 (76)	3 (76)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)
	120,000	2 Pipe or 3-in. Concentric	2-1/2 (64) one disk	2-1/2 (64)#	10 (3.0)	NA	NA	NA	NA	NA
			3 (76)†	NA	45 (13.7)	40 (12.2)	35 (10.7)	30 (9.1)	25 (7.6)	20 (6.1)
			3 (76) † no disk	3 (76)†#	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)
ALTITUDE FT (M)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY	NUMBER OF 90° ELBOWS					
		TERMINATION TYPE	PIPE DIA – IN. (mm)*	PIPE DIA – IN. (mm)*	1	2	3	4	5	6
2001 to 3000† (610 to 914)	60,000	2 Pipe or 2-in Concentric	1-1/2 (38)	1-1/2 (38)	17 (5.2)	12 (3.7)	7 (2.1)	NA	NA	NA
			2 (51)	2 (51)	70 (21.3)	67 (20.4)	66 (20.1)	61 (18.6)	61 (18.6)	61 (18.6)
	80,000	2 Pipe or 2-in Concentric	2 (51)	2 (51)	49 (14.9)	44 (13.4)	30 (9.1)	25 (7.6)	25 (7.6)	15 (4.6)
			2-1/2 (64)	2-1/2 (64)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)
	100,000	2 Pipe or 3-in Concentric	2-1/2 (64)	2-1/2 (64)	35 (10.7)	26 (7.9)	16 (4.9)	16 (4.9)	6 (1.8)	NA
			3 (76)	3 (76)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	66 (20.1)	61 (18.6)
	120,000	2 Pipe or 3-in. Concentric	3 (76)	NA	14 (4.3)	9 (2.7)	NA	NA	NA	NA
			NA	3 (76)†#	63 (19.2)	62 (18.9)	62 (18.9)	61 (18.6)	61 (18.6)	61 (18.6)
			3 (76)† no disk	NA	70 (21.3)	70 (21.3)	63 (19.2)	56 (17.1)	50 (15.2)	43 (13.1)
			4 (102)† no disk	4 (102)† no disk	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)
ALTITUDE FT (M)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY	NUMBER OF 90° ELBOWS					
		TERMINATION TYPE	PIPE DIA – IN (mm)*	PIPE DIA – IN (mm)*	1	2	3	4	5	6
3001 to 4000† (914 to 1219)	60,000	2 Pipe or 2-in Concentric	1-1/2 (38)	1-1/2 (38)	16 (4.9)	11 (3.4)	6 (1.8)	NA	NA	NA
			2 (51)	2 (51)	68 (20.7)	63 (19.2)	62 (18.9)	57 (17.4)	57 (17.4)	56 (17.1)
	80,000	2 Pipe or 2-in Concentric	2 (51)	2 (51)	46 (14.)	41 (12.5)	28 (8.5)	23 (7.0)	22 (6.7)	13 (4.)
			2-1/2 (64)	2-1/2 (64)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)
	100,000	2 Pipe or 3-in Concentric	2-1/2 (64)	2-1/2 (64)	33 (10.1)	24 (7.3)	15 (4.6)	14 (4.3)	5 (1.5)	NA
			3 (76)	3 (76)	70 (21.3)	70 (21.3)	70 (21.3)	66 (20.1)	61 (18.6)	56 (17.1)
	120,000	2 Pipe or 3-in. Concentric	3 (76)† no disk	NA	65 (19.8)	58 (17.7)	51 (15.5)	44 (13.4)	38 (11.6)	31 (9.4)
			NA	3 (76)†#	59 (18.0)	59 (18.0)	58 (17.7)	57 (17.4)	57 (17.4)	56 (17.1)
		4† no disk	4 (102)† no disk	4 (102) † no disk	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)

MAXIMUM ALLOWABLE PIPE LENGTH – FT (M) CONT.

ALTITUDE FT (M)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY	NUMBER OF 90° ELBOWS					
		TERMINATION TYPE	PIPE DIA – IN. (mm)*	PIPE DIA – IN. (mm)*	1	2	3	4	5	6
4001 to 5000† (1219 to 1524)	60,000	2 Pipe or 2-in Concentric	1-1/2 (38)	1-1/2 (38)	15 (4.6)	10 (3.0)	5 (1.5)	NA	NA	NA
			2 (51)	2 (51)	64 (19.5)	59 (18.0)	58 (17.7)	53 (16.2)	52 (15.8)	52 (15.8)
	80,000	2 Pipe or 2-in Concentric	2 (51)	2 (51)	44 (13.4)	39 (11.9)	26 (7.9)	21 (6.4)	20 (6.1)	11 (3.4)
			2-1/2 (64)	2-1/2 (64)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)
	100,000	2 Pipe or 3-in Concentric	2-1/2 (64)	2-1/2 (64)	31 (9.4)	22 (6.7)	13 (4.0)	12 (3.7)	NA	NA
			3 (76)	3 (76)	70 (21.3)	70 (21.3)	67 (20.4)	62 (18.9)	57 (17.4)	52 (15.8)
	120,000	2 Pipe or 3-in. Concentric	3 (76)† no disk	NA	53 (16.2)	46 (14.0)	40 (12.2)	33 (10.1)	26 (7.9)	20 (6.1)
			NA	3 (76)†#	56 (17.1)	55 (16.8)	54 (16.5)	53 (16.2)	52 (15.8)	52 (15.8)
			4 (102)† no disk	4 (102)† no disk	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)
ALTITUDE FT (M)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY	NUMBER OF 90° ELBOWS					
		TERMINATION TYPE	PIPE DIA – IN. (mm)*	PIPE DIA – IN. (mm)*	1	2	3	4	5	6
5001 to 6000† (1524 to 1829)	60,000	2 Pipe or 2-in Concentric	1-1/2 (38)	1-1/2 (38)	14 (4.3)	9 (2.7)	NA	NA	NA	NA
			2 (51)	2 (51)	60 (18.3)	55 (16.8)	54 (16.5)	49 (14.9)	48 (14.6)	47 (14.3)
	80,000	2 Pipe or 2-in Concentric	2 (51)	2 (51)	41 (12.5)	36 (11.0)	23 (7.0)	18 (5.5)	17 (5.2)	8 (2.4)
			2-1/2 (64)	2-1/2 (64)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)
	100,000	2 Pipe or 3-in Concentric	2-1/2 (64)	2-1/2 (64)	29 (8.8)	21 (6.4)	12 (3.7)	11 (3.4)	NA	NA
			3 (76)	3 (76)	70 (21.3)	67 (20.4)	62 (18.9)	57 (17.4)	52 (15.8)	47 (14.3)
	120,000	2 Pipe or 3-in. Concentric	3 (76)† no disk	NA	42 (12.8)	35 (10.7)	29 (8.8)	22 (6.7)	15 (4.6)	9 (2.7)
			NA	3 (76)†#	53 (16.2)	52	50 (15.2)	49 (14.9)	48 (14.6)	47 (14.3)
			4 (102)† no disk	4 (102)† no disk	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)	70 (21.3)
ALTITUDE FT (M)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY	NUMBER OF 90° ELBOWS					
		TERMINATION TYPE	PIPE DIA – IN. (mm)*	PIPE DIA – IN. (mm)*	1	2	3	4	5	6
6001 to 7000† (1829 to 2134)	60,000	2 Pipe or 2-in Concentric	1-1/2 (38)	1-1/2 (38)	13 (4.0)	8 (2.4)	NA	NA	NA	NA
			2 (51)	2 (51)	57 (17.4)	52 (15.8)	50 (15.2)	45 (13.7)	44 (13.4)	43 (13.1)
	80,000	2 Pipe or 2-in Concentric	2 (51)	2 (51)	38 (11.6)	33 (10.1)	21 (6.4)	16 (4.9)	15 (4.6)	6 (1.8)
			2-1/2 (64)	2-1/2 (64)	70 (21.3)	70 (21.3)	68 (20.7)	67 (20.4)	66 (20.1)	64 (19.5)
	100,000	2 Pipe or 3-in Concentric	2-1/2 (64)	2-1/2 (64)	27 (8.2)	19 (5.8)	10 (3.0)	9 (2.7)	NA	NA
			3 (76)	3 (76)	68 (20.7)	63 (19.2)	58 (17.7)	53 (16.2)	48 (14.6)	43 (13.1)
	120,000	2 Pipe or 3-in. Concentric	3 (76)† no disk	NA	31 (9.4)	24 (7.3)	18 (5.5)	11 (3.4)	NA	NA
			NA	3 (76)†#	49 (14.9)	48 (14.6)	47 (14.3)	45 (13.7)	44 (13.4)	43 (13.1)

See notes at end of table.

MAXIMUM ALLOWABLE PIPE LENGTH – FT (M) CONT.

PG9MXA

ALTITUDE FT (M)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY	NUMBER OF 90° ELBOWS					
		TERMINATION TYPE	PIPE DIA – IN. (mm)*	PIPE DIA – IN. (mm)*	1	2	3	4	5	6
7001 to 8000‡ (2134 to 2438)	60,000	2 Pipe or 2-in Concentric	1-1/2 (38)	1-1/2 (38)	12 (3.7)	7 (2.1)	NA	NA	NA	NA
			2 (51)	2 (51)	53 (16.2)	48 (14.6)	46 (14.)	41 (12.5)	40 (12.2)	38 (11.6)
	80,000	2 Pipe or 2-in Concentric	2 (51)	2 (51)	36 (11.0)	31 (9.4)	19 (5.8)	14 (4.3)	12 (3.7)	NA
			2-1/2 (64)	2-1/2 (64)	66 (20.1)	65 (19.8)	63 (19.2)	62 (18.9)	60 (18.3)	59 (18.0)
	100,000	2 Pipe or 3-in Concentric	2-1/2 (64)	2-1/2 (64)	25 (7.6)	17 (5.2)	8 (2.4)	7 (2.1)	NA	NA
			3 (76)	3 (76)	63 (19.2)	58 (17.7)	53 (16.2)	48 (14.6)	43 (13.1)	38 (11.6)
	120,000	2 Pipe or 3-in. Concentric	3 (76)† no disk	NA	20 (6.1)	13 (4.0)	7 (2.1)	NA	NA	NA
			NA	3 (76)†#	46 (14.)	44 (13.4)	43 (13.1)	41 (12.5)	40 (12.2)	38 (11.6)
			4 (102)† no disk	4 (102)† no disk	61 (18.6)	56 (17.1)	51 (15.5)	46 (14.0)	41 (12.5)	36 (11.0)
ALTITUDE FT (M)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY	NUMBER OF 90° ELBOWS					
		TERMINATION TYPE	PIPE DIA – IN. (mm)*	PIPE DIA – IN. (mm)*	1	2	3	4	5	6
8001 to 9000‡ (2438 to 2743)	60,000	2 Pipe or 2-in Concentric	1-1/2 (38)	1-1/2 (38)	11 (3.4)	6 (1.8)	NA	NA	NA	NA
			2 (51)	2 (51)	49 (14.9)	44 (13.4)	42 (12.8)	37 (11.3)	35 (10.7)	34 (10.4)
	80,000	2 Pipe or 2-in Concentric	2 (51)	2 (51)	33 (10.1)	28 (8.5)	17 (5.2)	12 (3.7)	10 (3.0)	NA
			2-1/2 (64)	2-1/2 (64)	62 (18.9)	60 (18.3)	58 (17.7)	56 (17.1)	55 (16.8)	53 (16.2)
	100,000	2 Pipe or 3-in Concentric	2-1/2 (64)	2-1/2 (64)	23 (7.0)	15 (4.6)	7 (2.1)	5 (1.5)	NA	NA
			3 (76)	3 (76)	59 (18.0)	54 (16.5)	49 (14.9)	44 (13.4)	39 (11.9)	34 (10.4)
	120,000	2 Pipe or 3-in. Concentric	3 (76)† no disk	NA	10 (3.)	NA	NA	NA	NA	NA
			NA	3 (76)†#	43 (13.1)	41 (12.5)	39 (11.9)	37 (11.3)	35 (10.7)	34 (10.4)
			4 (102)† no disk	4† no disk	35 (10.7)	30 (9.1)	25 (7.6)	20 (6.1)	15 (4.6)	10 (3.0)
ALTITUDE FT (M)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY	NUMBER OF 90° ELBOWS					
		TERMINATION TYPE	PIPE DIA – IN. (mm)*	PIPE DIA – IN. (mm)*	1	2	3	4	5	6
9001 to 10,000‡ (2743 to 3048)	60,000	2 Pipe or 2-in Concentric	2 (51)	2 (51)	45 (13.7)	40 (12.2)	38 (11.6)	33 (10.1)	31 (9.4)	29 (8.8)
	80,000	2 Pipe or 2-in Concentric	2 (51)	2 (51)	30 (9.1)	25 (7.6)	14 (4.3)	9 (2.7)	7 (2.1)	NA
			2-1/2 (64)	2-1/2 (64)	57 (17.4)	55 (16.8)	53 (16.2)	51 (15.5)	49 (14.9)	47 (14.3)
	100,000	2 Pipe or 3-in Concentric	2-1/2 (64)	2-1/2 (64)	21 (6.4)	13 (4.0)	5 (1.5)	NA	NA	NA
			3 (76)	3 (76)	54 (16.5)	49 (14.9)	44 (13.4)	39 (11.9)	34 (10.4)	29 (8.8)
	120,000	2 Pipe or 3-in. Concentric	NA	3 (76)†#	39 (11.9)	37 (11.3)	35 (10.7)	33 (10.1)	31 (9.4)	29 (8.8)
			4 (102)† no disk	4 (102)† no disk	10 (3.0)	5 (1.5)	NA	NA	NA	NA

* Disk usage – Unless otherwise specified, use perforated disk assembly (factory-supplied in loose parts bag).

If one disk is stated, separate 2 halves of perforated disk assembly and use shouldered disk half. When using shouldered disk half, install screen side toward inlet box.

† Wide radius elbow.

‡ Vent sizing for Canadian installations over 4500 ft (1370 M) above sea level are subject to acceptance by the local authorities having jurisdiction.

NA—Not Allowed; pressure switch will not make.

Elbows and pipe sections within the furnace casing and at the vent termination should not be included in vent length or elbow count.

The minimum pipe length is 5 ft (1.5 M) for all applications.

Use 3-in. (76 mm) diameter vent termination kit for installations requiring 4-in. (102 mm) diameter pipe.

NOTES:

Do not use pipe size greater than those specified in table or incomplete combustion, flame disturbance, or flame sense lockout may occur.

Size both the combustion—air and vent pipe independently, then use the larger diameter for both pipes.

Assume two 45° elbows equal one 90° elbow. Wide radius elbows are desirable and may be required in some cases.

**MAXIMUM ALLOWABLE EXPOSED VENT PIPE LENGTH - FT (M)
WITH AND WITHOUT INSULATION IN WINTER DESIGN TEMPERATURE AMBIENT***

UNIT SIZE	WINTER DESIGN TEMPERATURE °F (°C)	MAX PIPE DIAMETER – IN (mm)	WITHOUT INSULATION	WITH 3/8-IN. (10 mm) OR THICKER INSULATION†
060	20 (–7)	2 (51)	44 (13.4)	70 (21.3)
	0 (–18)	2 (51)	21 (6.4)	70 (21.3)
	–20 (–29)	2 (51)	20 (6.0)	57 (17.3)
080	20 (–7)	2 (51)	55 (16.7)	55 (16.7)
	0 (–18)	2 (51)	30 (9.1)	55 (16.7)
	–20 (–29)	2 (51)	16 (4.8)	55 (16.7)
	20 (–7)	2.5 (64)	58 (17.6)	70 (21.3)
	0 (–18)	2.5 (64)	29 (8.8)	70 (21.3)
	–20 (–29)	2.5 (64)	14 (4.2)	67 (20.4)
100	20 (–7)	2.5 (64)	40 (12.1)	40 (12.1)
	0 (–18)	2.5 (64)	38 (11.5)	40 (12.1)
	–20 (–29)	2.5 (64)	21 (6.4)	40 (12.1)
	20 (–7)	3 (76)	63 (19.2)	70 (21.3)
	0 (–18)	3 (76)	30 (9.1)	70 (21.3)
	–20 (–29)	3 (76)	12 (3.6)	70 (21.3)
120	20 (–7)	3 (76)	70 (21.3)	70 (21.3)
	0 (–18)	3 (76)	38 (11.5)	70 (21.3)
	–20 (–29)	3 (76)	19 (5.7)	70 (21.3)
	20 (–7)	4 (102)	65 (19.8)	70 (21.3)
	0 (–18)	4 (102)	26 (7.9)	70 (21.3)
	–20 (–29)	4 (102)	5 (1.5)	65 (19.8)


* Pipe length (ft / M) specified for maximum pipe lengths located in unconditioned spaces. Pipes located in unconditioned space cannot exceed total allowable pipe length as specified in Table.

† Insulation thickness based on R value of 3.5 per in.


DOWNFLOW SUBBASE DIMENSIONS - IN. (MM)

FURNACE CASING WIDTH	FURNACE IN DOWNFLOW APPLICATION	PLENUM OPENING		FLOOR OPENING		HOLE NO. FOR WIDTH ADJUSTMENT
		A	B	C	D	
17-1/2 (445)	Furnace with or without Cased Coil Assembly or Coil Box	15-1/8 (384)	19 (483)	16-3/4 (425)	20-3/8 (518)	3
21 (533)	Furnace with or without Cased Coil Assembly or Coil Box	18-5/8 (473)	19 (483)	20-1/4 (514)	20-3/8 (518)	2
24-1/2 (622)	Furnace with or without Cased Coil Assembly or Coil Box	22-1/8 (562)	19 (483)	23-3/4 (603)	20-3/8 (518)	1

*The plenum should be constructed 1/4-in. (6 mm) smaller in width and depth than the plenum dimensions shown above.



COMBUSTION-AIR PIPE FOR NON-DIRECT VENT (1-PIPE) APPLICATION (SIZES 040 THROUGH 120 ONLY)




A96211

LENGTH OF STRAIGHT PIPE PORTION OF COMBUSTION AIR INLET PIPE ASSEMBLY (IN.)

CASING WIDTH	A
17-1/2 (445 mm)	8-1/2 ± 1/2 (216 ± 13 mm)
21 (533 mm)	10-1/2 ± 1/2 (267 ± 13 mm)
24-1/2 (622 mm)	12 ± 1/2 (305 ± 13 mm)

CONCENTRIC VENT FOR DIRECT VENT (2-PIPE) APPLICATION (ALL MODEL SIZES)



KIT PART NO.	A*	B	C	D†	E	F
KGAVT0701CVT	33-3/8 (848)	2 (51)	3-1/2 (89)	16-5/8 (422)	6-1/4 (159)	5-3/4 (146)
KGAVT0801CVT	38-7/8 (987)	3 (76)	4-1/2 (114)	21-1/8 (537)	7-3/8 (187)	6-1/2 (165)

*Dimension A will change accordingly as Dimension D is lengthened or shortened.

†Dimension D may be lengthened to 60-in. (1524 mm) maximum. Dimension D may also be shortened by cutting the pipes provided in the kit to 12-in. (305 mm) minimum.

AIR DELIVERY - CFM (WITH FILTER)

UNIT SIZE	RETURN-AIR SUPPLY	SPEED	EXTERNAL STATIC PRESSURE (in. wc)									
			0.1	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1
036060	SIDE/BOTTOM	5(Gry)	1430	1390	1345	1300	1250	1205	1150	1080	995	845
		3(Blu)	1240	1200	1145	1100	1040	975	915	860	790	730
		4(Yel)	1090	1030	980	935	850	800	730	665	590	525
		1(Red)	900	835	780	705	635	565	490	410	335	200
		2(Org)	805	620	440	380	300	—	—	—	—	—
036080	SIDE/BOTTOM	5(Gry)	1400	1360	1325	1285	1240	1205	1160	1125	1075	1000
		3(Blu)	1340	1300	1265	1215	1180	1135	1100	1055	1015	965
		4(Yel)	1195	1160	1115	1065	1025	985	935	895	850	800
		1(Red)	1025	980	935	880	835	795	745	685	635	585
		2(Org)	855	800	745	680	635	560	515	460	420	360
048080	SIDE/BOTTOM	5(Gry)	1720	1695	1690	1655	1620	1580	1540	1495	1465	1415
		3(Blu)	1565	1535	1530	1490	1450	1420	1375	1335	1295	1255
		4(Yel)	1330	1310	1270	1220	1180	1135	1095	1055	1010	970
		2(Org)	1210	1180	1135	1085	1035	995	950	910	865	810
		1(Red)	1110	1065	1005	960	910	865	820	770	720	670
060100	SIDE/BOTTOM	5(Gry)	2070	2020	1985	1925	1890	1850	1795	1755	1690	1610
		3(Blu)	1815	1775	1730	1690	1635	1595	1555	1500	1460	1410
		4(Yel)	1580	1535	1480	1440	1380	1380	1340	1285	1235	1185
		2(Org)	1380	1325	1275	1220	1220	1165	1105	1060	1000	960
		1(Red)	1170	1105	1055	985	935	870	805	765	705	660
060120	SIDE/BOTTOM	5(Gry)	2250	2205	2155	2110	2065	2020	1970	1925	1870	1790
		3(Blu)	2130	2085	2030	1980	1925	1880	1830	1775	1730	1675
		4(Yel)	1890	1835	1790	1740	1690	1640	1590	1535	1480	1435
		1(Red)	1640	1585	1525	1475	1425	1365	1315	1260	1200	1140
		2(Org)	1420	1370	1305	1255	1190	1135	1065	1010	940	880

NOTES:

* Airflow shown is with factory supplied 3/4-in. (19 mm) washable filter.*A filter is required for each return air opening.

*An airflow reduction of up to 7% may occur when using the factory-specified 4-5/16-in. (110 mm) wide, high efficiency media filter.

*For best furnace efficiency when using the 4 5/16-in. (110 mm) wide media filter, adjust blower speed tap to near the mid-point of the rise range.

*For horizontal and downflow applications, use one side or bottom or bottom only as an airflow reference.

PG9MXA

