

EP Flow-through Multi-port Tee

Submittal Information
Revision C: March 21, 2013

Project Information

Job Name:

Location:

Part No. Ordered:

Engineer:

Date Submitted:

Contractor:


Submitted By:

Manufacturer's Representative:

Approved By:

Technical Data

Material:	UDEL GF120
Maximum Temperature (no pressure):	320°F (160°C)
Maximum Working Temperature/Pressure:	210°F (99°C) at 150 psi
Maximum Manifold Flow for ¾" Outlet:	7.5 gpm at 8 fps 3.75 gpm at 4 fps
Maximum Manifold Flow for 1" Outlet:	16.5 gpm at 8 fps 6.6 gpm at 4 fps



Product Information and Application Use

EP Flow-through Multi-port Tee features ¾" ProPEX® inlets with ½" ProPEX branch outlets or 1" ProPEX inlets or ¾" ProPEX inlets with ½" ProPEX branch outlets.¹ The tee is made of EP, the time-tested, high-performance material used in demanding hot-water applications.

✓ Description	Part Number	A	B	C	D	E	Weight
EP Flow-through Multi-port Tee, 2 outlets, ¾" x ¾" ProPEX	Q2227557	4.40"	1.77"	1.25"	¾" ProPEX	¾" ProPEX	0.08 lbs.
EP Flow-through Multi-port Tee, 3 outlets, ¾" x ¾" ProPEX	Q2237557	5.70"	1.77"	1.25"	¾" ProPEX	¾" ProPEX	0.10 lbs.
EP Flow-through Multi-port Tee, 3 outlets, 1" x ¾" ProPEX	Q2231057	6.20"	1.88"	1.25"	1" ProPEX	¾" ProPEX	0.14 lbs.
EP Flow-through Multi-port Tee, 4 outlets, ¾" x ¾" ProPEX	Q2247557	7.80"	1.77"	1.50"	¾" ProPEX	¾" ProPEX	0.14 lbs.
EP Flow-through Multi-port Tee, 4 outlets, 1" x ¾" ProPEX	Q2241057	7.10"	2.00"	1.25"	1" ProPEX	¾" ProPEX	0.17 lbs.
EP Flow-through Multi-port Tee, 4 outlets, 1" x 1" ProPEX	Q2241051	7.68"	1.88"	1.25"	1" ProPEX	1" ProPEX	0.18 lbs.
EP Flow-through Multi-port Tee, 6 outlets, ¾" x ¾" ProPEX	Q2267557	9.41"	1.62"	1.25"	¾" ProPEX	¾" ProPEX	0.18 lbs.
EP Flow-through Multi-port Tee, 6 outlets, 1" x ¾" ProPEX	Q2261057	9.60"	2.00"	1.25"	1" ProPEX	¾" ProPEX	0.24 lbs.
EP Flow-through Multi-port Tee, 6 outlets, 1" x 1" ProPEX	Q2261051	9.90"	2.00"	1.25"	1" ProPEX	1" ProPEX	0.25 lbs.

Installation

Any product designed to mount 1" copper pipe (for the ¾" EP Flow-through Multi-port Tee) or 1¼" copper pipe (for the 1" EP Flow-through Multi-port Tee) can serve as a mounting bracket. For more information, refer to the Uponor Professional Plumbing Installation Guide.

Standards

CAN/CSA B137.5; ASTM F877; ASTM F1960

Codes

IPC; UPC; NSPC; NPC of Canada

Listings

ANSI/NSF -14- and 61-certified; ICC ESR 1099; IAPMO 3946; HUD MR 1269

Related Applications

PEX-a Plumbing Systems

Contact Information

Uponor, Inc.
5925 148th Street West
Apple Valley, MN 55124 USA
Phone: (800) 321-4739
Fax: (952) 891-2008
www.uponorpro.com

Uponor Ltd.
655 Park Street
Regina, SK S4N 5N1 CANADA
Phone: (888) 994-7726
Fax: (800) 638-9517
www.uponorpro.com

¹ProPEX® is a registered trademark of Uponor, Inc. ProPEX™ is a trademark of Uponor Ltd.