## PSP722E

# Energy STAR

### Everything 'Stat®



#### **COMPATIBLE WITH:**

- Most 24v Gas, Oil, Electric Heating and Air Conditioning Systems
- Multi-stage Heat Pumps
- 2 Wire Hydronic Systems
- Hydronic Air Handlers
- Millivolt Systems

#### **NOT COMPATIBLE WITH:**

- 3 Wire Hydronic Systems
- Line Voltage Systems (Without Transformer)


#### PSP722E 2H/2C DIGITAL PROGRAMMABLE THERMOSTAT

- Universal Compatibility Everything'Stat®
- Controls up to 2 Stages of Heat and 2 Stages of Cooling Plus Auxiliary and Emergency Heat
- Auto Changeover
- Large Hybrid Dot Matrix Display
- Auxiliary and Emergency Heat Indicators
- EL (Electro Luminescent) Backlight
- IAQ Independently Programmable Fan
- 7 Day Programming
- Default ENERGY STAR Approved Program
- 4 Periods Per Day
- Temporary Override
- Hold
- Vacation Hold
- Optional Smart Recovery
- ENERGY STAR Compliant
- Programmable Filter Timer with Change Filter Indicator
- Energy Usage Monitor
- Fahrenheit or Celsius Temperature Display
- 12/24 Hour Clock
- Easy Programming with LUX Speed Dial™

- Advanced Copy Function for Fast Easy Programming
- Nonvolatile Memory for All Programs and Settings
- Daylight Savings Button
- Multimode Keyboard Lockout with User Programmable 3 Digit Code
- Programmable High and Low Setting Limits
- Defeatable Audible Button Response
- Menu Driven Setup Done from the Front Panel
- Temperature Offset (User calibration)
- Outdoor Temperature Sensor Capability
- 3 Remote Indoor Sensor Capability
- Dual Power Capable (System/Battery)
- Multi-Stage Adjustable Temperature Differential/Cycle Rate
- Programmable Length Minimum Run Time
- Programmable Auto-Changeover Dead-Band
- Programmable Fan Delays for Heat, Cool, in Both On and Off
- Heat Pump Lock Out with Adjustable Disable Temperature







#### **GENERAL DESCRIPTION:** •

6" (150mm) wide x 4%" (110mm) tall x 11/4" (30mm) deep

**Description:** Universally compatible Everything 'Stat® offers programmable control of single or multistage heating and cooling systems. Temperature control adjustable.

#### SPECIFICATIONS: •

Heat/Cool Terminals: RH, RC, O, B, W1, W2, Y1, Y2, G, E, C.

Electrical Ratings: 11/2 AMPS at each terminal, 2 AMPS total 24v AC. System or Battery

Powered: 2 "AA" Batteries (optional).

**Temperature Control Range:** 45°F to 90°F (7° to 32°). Accuracy: ±1°F over a range of

50°F to 95°F.

#### **Environmental Limits:**

Moisture and Dust: meets IP20.

Operating Humidity: 20% to 90% non-condensing.

Operating Temperature:  $+32^{\circ}F$  to  $+95^{\circ}F$  ( $+0^{\circ}C$  to  $+35^{\circ}C$ ). Storage Temperature:  $-4^{\circ}F$  to  $+130^{\circ}F$  ( $-20^{\circ}C$  to  $+54^{\circ}C$ ).

Electrical Immunity: meets relevant CE specifications.

Optional Wall Plate: Decorative Wall Plate is available for thermostat.

6%'' (165mm) wide x 4%'' (110mm) tall.



**LUX Products Corporation** 6000 | Commerce Parkway • Mt. Laurel, NJ 08054 (856) 234-7905 • FAX (856) 234-7825 • www.luxproproducts.com

JOB NAME:			DATE:
CONTRACTOR:			UNIT DESIGNATION:
ENGINEER:			MODEL NO.:
SUBMITTED FOR:	APPROVAL	RECORD	LOCATION: