
For Residential and Commercial Applications					
Job Name		Engineer / Architect			
Job Location		Wholesaler			
Submittal Date		Contractor			

Multi-Turn Dual Outlet Stop w/ Loose Key -SR1701 Female Iron Pipe x Compression x Compression

Use: For use in potable water distribution systems. Not intended for recirculating water systems that produce continuous use temperatures above 115° F. For those applications, use BrassCraft KT series ball stops

Design Features:

- Machined one-piece brass body provides strength, durability and long-lasting performance
- Large loose key handle provides a secure grip for troublefree on/off operation
- Removable loose key handle helps protect against accidental stop operation during rough-ins and general use
- **Compliant Stops** available for California and Vermont "low-lead" requirements



Operating Specifications:

Temperature: 40°- 140° F Pressure: 125 psi maximum

Standard

MATERIAL SPECIFICATIONS					
Valve Body	C36000 brass				
Lock Shield Stem	C36000 brass				
Bib & Packing Washers	Nitrile or EPDM rubber				
Packing Nut	C36000 brass				
Loose Key	Zinc die cast				
Compression Sleeve	C36000 brass				
Compression Nut	C36000 brass				

Compliant

1/2" F.I.P. x 3/8" OD Compression x 3/8" OD Compression w/ loose key, chrome plated

MATERIAL SPECIFICATIONS				
Valve Body	Compliant brass			
Lock Shield Stem	Compliant brass			
Bib & Packing Washers	Nitrile or EPDM rubber			
Packing Nut	Compliant brass			
Loose Key	Zinc die cast			
Compression Sleeve	C36000 brass			
Compression Nut	C36000 brass			

Standard Part Listing:

SR1701LRX R1


☐ SR17011R C1

	SR1701LR C1	1/2" F.I.P. x 3/8" OD Compression x 3/8" OD Compression w/ loose key, chrome plated				
	SR1701LR R1	1/2" F.I.P. x 3/8" OD Compression x 3/8" OD Compression w/ loose key, chrome plated				
Compliant Part Listing:						
	SR1701LRX C1	1/2" F.I.P. x 3/8" OD Compression x 3/8" OD Compression w/ loose key, chrome plated				

This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft. This specification must be returned to BrassCraft if requested.



SR1701 Multi-Turn Dual Outlet Stop w/ Loose Key – Female Iron Pipe x Compression x Compression



PART DIMENSIONS (Inches)					
Model	DIM. A	DIM. B	DIM. C		
SR1701LR	1.06	2.38	1.79		
SR1701LRX	1.06	2.38	1.79		

Listings & Certifications:

- IAPMO listed to ASME A112.18.1-05 / CSA B125.1-05 (File # 0645)
- CSA listed to ASME A112.18.1-05 / CSA B125.1-05 (File # 204593)
- Compliant product CSA approved to California Health & Safety Code 116875 and Vermont Bill S.152 (Project # 2174785)









