Document No. 149-991 May 11, 2007

Q-Series Duct Relative Humidity and Relative Humidity & Temperature Sensors



Figure 1: Q-Series Duct Relative Humidity and Relative Humidity & Temperature Sensor.



Figure 2: Q-Series Relative Humidity Removable Sensing Tip

Description

The Q-Series Duct Relative Humidity and Relative Humidity & Temperature Sensors monitor and transmit changes in humidity and temperature to the building control systems. These units are especially suited for applications where precise, stable humidity sensing is required. Certified units are also available where certification is required. Several models are available for humidity only (in 5%, 2% and certified) or for humidity and temperature sensing (also in 5%, 2% and certified versions). The humidity only units are available in either 4 to 20 mA or 0 to 10 Volt signal versions. Combination humidity and temperature units are also available in either dual current or voltage versions, transmitting proportional signals back to the controller. Nickel 1000 ohm or Platinum 1000 ohm RTD temperature outputs on combination versions are also offered.

2% and certified versions are equipped with a removable, replaceable sensing tip. The removable sensing tips have a Lumberg connection that allows the user to screw off the tip without disrupting the installation or wiring. Siemens sensors with replaceable tips are ideal for applications where measurement accuracy is critical and sensor replacement is not an option. Replaceable sensing tips eliminate the need for accuracy adjustment.

All certified sensors include a certificate of calibration. Humidity calibration and certification is based on a 3-point process at 20, 50, and 85% rh @ 23°C.

Specifications – Humidity Element

Measurement range		0 to 100% rh
Accuracy at room	QFM2xxx types:	±5% rh, 0 to 95% rh (±3% rh, 30 to 70% rh)
temperature @ 73°F (20°C): types:	QFM3xxx	±2% rh, 0 to 95% rh
Temperature effect		Less than 0.1% per degree C
Sensing element		Capacitive humidity sensing element
Output signalrh only units		4 to 20 mA or 0 to 10 Vdc, 0 to 100% linear, proportional
Output signal rh/T units		0 to 10 Vdc or 4 to 20mA (both outputs), 0 to 100% linear, proportional
Polarity protection		Yes
Calibration		None
Time constant		Approx. 20 seconds in moving air

Specifications—Temperature Element (for combination RH/T units only)

-	QFM2110 (Platinum)		•
	QFM2120 (Nickel)	QFM2160	QFM31xx
	QFM2140 (T1)	QFM2171	QFM41xx
Accuracy:	± 1.4°F: 59°F to 95°F (± 0.8°C): (15°C to 35°C)	± 1.4°F: 59°F to 95°F (± 0.8°C): (15°C to 35°C)	
	± 1.8°F: -31°F to 59°F and 95°F to 158°F (± 1.0°C): (-35°C to 15°C and 35°C to 60°C)		9°F and 95°F to 158°F to 15°C and 35°C to 60°C)
Output signal	Platinum 1K ohm RTD (385α) Nickel 1K ohm RTD (Siemens) T1 (PTC)	0 to 10 Vdc (QFMx160 4 to 20 mA (QFMx171	,


General Specifications

0 to 1000/
0 to 100%
-31°F to 140°F (-35°C to 60°C)
-40°F to 158°F (-40°C to 70°C)
18 AWG cable length shared in conduit with other sensor wiring 750 ft. (229 m) max
Screw terminals
Probe: .6" OD x 7.2" L (15 mm x 183 mm)
Housing: 3.1" L × 2.3" W × 1.5" D (80 mm × 60 mm × 40 mm)
13.5 to 35 Vdc
Less than 500 ohms
Polycarbonate plastic, UL 94-5VB rated, suitable for plenum installations
IP 65 (QFM3xxx, QFM4xxx types), IP54 (QFM2xxx types), NEMA 1 (all types)
Teflon, 10 micron filter
UL listed to UL 873 for Temperature Indicating and Regulating Equipment
EC Directive on electromagnetic compatibility: 89/336/EEC

Ordering Information

Part Number	Description	
QFM2100	Duct humidity sensor, (5%) 0 to 10 Vdc	
QFM2101	Duct humidity sensor, (5%) 4 to 20 mA	
QFM2110	Duct humidity sensor, (5%) 0 to 10 Vdc/Temp 1K ohm Platinum RTD (385 Alpha)	
QFM2120	Duct humidity sensor, (5%) 0 to 10 Vdc/Temp 1K ohm Nickel RTD	
QFM2140	Duct humidity sensor, (5%) 0 to 10 Vdc/Temp T1	
QFM2160	Duct humidity sensor, (5%) 0 to 10 Vdc/Temp 0 to 10 V dc	
QFM2171	Duct humidity sensor, (5%) 4 to 20 mA/Temp 4 to 20 mA	
QFM3100	Duct humidity sensor, (2%) 0 to 10 Vdc	
QFM3101	Duct humidity sensor, (2%) 4 to 20 mA	
QFM3160	Duct humidity sensor, (2%) 0 to 10 Vdc/Temp 0 to 10 Vdc	
QFM3171	Duct humidity sensor, (2%) 4 to 20 mA/Temp 4 to 20 mA	
QFM4101	Duct humidity sensor, 4 to 20 mA (certified)	
QFM4160	Duct humidity sensor, 0 to 10 Vdc/Temp 0 to 10 Vdc (certified)	
QFM4171	Duct humidity sensor, 4 to 20 mA/Temp 4 to 20 mA (certified)	
Accessories		
AQF3101	Sensor filter cap	
AQF3150	Replaceable 2% sensor tip	
AQF4150	Replaceable 2% certified sensor tip	
74 662 0048 0	Replacement conduit clamps	
74 662 0068 0	Replacement flange kit	

Product Naming Key



NOTE: For combination RH&T versions, mixed 4-20mA and 0-10 V signals not offered. NOTE: For combination RH&T, 2% versions, only 0-10 V or 4-20mA temperature signal offered.

Information in this document is based on specifications believed correct at the time of publication. The right is reserved to make changes as design improvements are introduced. Other product or company names mentioned herein may be the trademarks of their respective owners. © 2007 Siemens Building Technologies, Inc.

Buffalo Grove, IL 60089-4513