# **GAS OUTLET BOX**

696 series Ox Box™

#### **SPECIFICATION**

Sioux Chief 696 series Ox Box gas outlet box shall be used where necessary in plumbing and gas supply systems for residential or commercial units. Box shall allow for mounting with supply line from top or bottom, on-stud or between studs. Unit shall be available with yellow handle. Valve shall be available with or without brass shank. Metal support bracket shall install into top track of box for between stud configuration. Outlet shall be  $\frac{1}{2}$ " or  $\frac{3}{4}$ ." Valve shall be  $\frac{1}{4}$ -turn operation.

### **MATERIALS**

outlet box: ABS frame: ABS

bracket: galvanized steel valve body: cast brass

valve handle: powder-coated yellow zinc

screw: chrome steel

shank: zinc adapter\*: brass plug: steel

components: Teflon teats and chrome-plated brass ball

\* Available in 1/2" and 3/4".

#### **VALVE RATING**

max working pressure: ½ PSIG max testing pressure: 10 PSI

#### **GAS/GAS MIXES**

natural gas propane

#### **CERTIFICATIONS/APPROVALS**

ANSI Z21.15 CSA

## **DIMENSIONS**


A: frame width 534"
B: frame height 714"
C: frame opening width 358"
D: frame opening height 518"
E: rough-in box inner width 4"
F: rough-in box overall depth 312"
G: rough-in box inner height 512"

H: supply connection (see 'A' and 'B' below)

I: outlet connection (see 'A' below)


J: bracket length 18" K: bracket width 5%"

bracket thickness 18 gauge





696-1020GF



#### 69

# 696-10 A B GF

e.g. 696-1020GF = Gas Ox Box with 1/2" inlet and outlet

 $\underline{A}$  VALVE CONNECTION  $\underline{B}$  ADAPTER  $\underline{C}$  2  $\frac{1}{2}$ " outlet  $\times$   $\frac{1}{2}$ " inlet  $\underline{C}$  0 none

 $\Box$  3 3/4" outlet × 3/4" inlet  $\Box$  1 female × male NPT adapter

Create Item Number