



Submittal Data **VHN-1C-FA**

Spirovent® High Velocity Drain Microbubble™ Eliminator and Dirt Separator

Job Name:
 Engineer:
 Contractor:
 Representative:

Tag	Model	Flow	Size	Location

	Specifications:																			
	<table> <tr> <td>Shell</td><td>Steel</td></tr> <tr> <td>Vent Head</td><td>Brass</td></tr> <tr> <td>Float</td><td>Non-Ferrous</td></tr> <tr> <td>Seal</td><td>Viton</td></tr> <tr> <td>O Ring</td><td>Viton</td></tr> <tr> <td>Skim Valve</td><td>Brass</td></tr> <tr> <td>Coalescing Medium</td><td>Copper</td></tr> <tr> <td>Ball Valve</td><td>Brass</td></tr> <tr> <td>Max. Working Pressure</td><td>150 psig</td></tr> <tr> <td>Max. Operating Temperature</td><td>270°F</td></tr> </table>	Shell	Steel	Vent Head	Brass	Float	Non-Ferrous	Seal	Viton	O Ring	Viton	Skim Valve	Brass	Coalescing Medium	Copper	Ball Valve	Brass	Max. Working Pressure	150 psig	Max. Operating Temperature
Shell	Steel																			
Vent Head	Brass																			
Float	Non-Ferrous																			
Seal	Viton																			
O Ring	Viton																			
Skim Valve	Brass																			
Coalescing Medium	Copper																			
Ball Valve	Brass																			
Max. Working Pressure	150 psig																			
Max. Operating Temperature	270°F																			
Notes: Removable lower head to facilitate cleaning as required.																				

PS - Pipe Size	2"	2 ½"	3"	4"	5"	6"	8"	10"	12"
D (inches)	6.3	6.3	8.6	8.6	12.8	12.8	16.0	20.0	24.0
DF (inches)	11.2	11.2	13.4	13.4	18.1	18.1	22.8	28.1	33.1
H2 (inches)	35.8	35.8	45.1	45.1	61.8	61.8	78.5	95.0	113.0
h2 (inches)	15.9	15.9	20.7	20.7	29.3	29.3	37.6	47.0	55.0
LF (inches)	15.2	15.7	20.2	20.6	27.7	27.7	33.6	37.5	42.5
e (inches)	1	1	1	1	1	1	1	1	1
Weight (lbs)	120	150	195	262	479	505	820	1269	2025
Rec. Flow (gpm)	105	155	225	405	630	910	1610	2450	3500
Model VHN---FA*	200	250	300	400	500	600	800	1000	1200

(Dimensions for reference only)

*Flanged ASME Section VIII, Division 1 Stamped and Registered