

284-50



TEMPERATURE CONTROL FOR HEATING WITH WEATHERPROOF ENCLOSURE

FEATURES

- Weatherproof enclosure.
- Furnished with 6" stripped leads.
- Remote bulb.

SPECIFICATIONS

Enclosure CSA Enc. 3 (NEMA 3)
Agency CSA

Model Number	Range	Differential	Switch Action	Capillary Length	Bulb Size	Motor Rating (Full Load)		Resistive (Non-Inductive)	
						120 VAC	240 VAC	120 VAC	240 VAC
284-50	20 to 122°F (6.7 to 50°C)	Fixed 6.8°F (3.8°C)	Open on Rise	10 ft.	5/16" x 4 3/16"	10.0A	6.0A	25.0A	25.0A



230-22

TEMPERATURE CONTROLS FOR HEATING

Provide Regulation of Duct Temperatures in Conjunction with Air Handling Units or Control of Circulator for Indoor-Outdoor Regulation from a Remote Point

FEATURES

- Hydraulic action element – Unaffected by vibration.
- Switch case mounts in any position – No leveling required. Includes bulb mounting clip.
- High electrical rating permits operation of most equipment without use of relays or motor starters.
- Dustproof steel case – Dial visible and can be adjusted through cover. Case has knockouts on top and bottom.
- Temperature dial graduated in °F and °C.

SPECIFICATIONS

Dimensions 5 3/4" H x 2 5/16" W x 2 9/16" D
Finish Grey color
Agency U.L. listed and C.S.A. certified

Model Number	Range	Differential	Capillary Length	Bulb Size	Switch Action	Full Electrical Rating	Motor Rating (Full Load)		Resistive (Non-inductive)	
							120 VAC	240 VAC	120 VAC	240 VAC
230-22 ①	20 to 120°F (-6 to +49°C)	Adj. 4 to 30°F (2.2 to 17°C)	8 ft.	6 1/4 x 3/8"	Open on Rise	FG See page 416	14.0A	7.0A	25.0A	22.0A

① U.L. approved adjustable dial stop, factory set at 90°F maximum.