

BOSHART INDUSTRIES

Telephone: 1-519-595-4444 - Toll Free: 1-800-561-3164

Fax: 1-519-595-4380 - www.boshart.com

6-11

April 23/12

WATER LEVEL GAUGE

- 4-1/2" Dial - Aluminum rotating dial
- 304 SS case and bezel with side screws
- Acrylic window
- Brass pointer, black finish
- Brass movement
- Ranges: 0-390' H₂O
- Bourdon Tube - Phosphor Bronze, soft soldered
- Connection: 1/4" NPT LM, Brass
- Accuracy: $\pm 3-2-3$ %




The gauge is used to indicate the depth of water in a well. Gauge and air line to well bottom are charged with air. The pressure required to permit air to escape from the end of the air line is a measure of the head of water above the end of the air line. The length of air line may be set on the adjustable dial to permit reading water level in feet below the ground surface.

PART NO.	RANGE	INCREMENTS	LIST PRICE-A
PG45-WL	0-390' H ₂ O	1	21.64

BI-METAL THERMOMETERS

- 2-1/2" and 3" Dials
- General purpose industrial thermometer
- Coiled bi-metal element
- Bulb - Stem with detaching thermowell
- Accuracy : $\pm 2\%$
- Working Range - Maximum scale value
- 6 Bar Maximum Thermowell rating
- Aluminum Case / Acrylic Window
- Dual Scale °F & °C
- Stainless Steel Thermowell on Model SS25



* Measurements for 2 1/2" dial *

* Measurements for 3" dial

PART NO.	DIAL	DUAL RANGE		CONN.	THERMOWELL LENGTH	INCREMENTS	LIST PRICE-A
TW25-CB2-250-25	2-1/2"	32-250 °F	0-120 °C	1/2" CBM	2-1/2"	1	12.05
TW30-CB2-250-25	3"	32-250 °F	0-120 °C	1/2" CBM	2-1/2"	1	16.49
TW25-CB2-250-SS25	2-1/2"	32-250 °F	0-120 °C	1/2" CBM SS	2-1/2"	1	17.75

HOT WATER THERMOMETERS


- For use with hot water
- 1/2" NPT Brass Thermowell
- Temperature Range: 40°F to 280°F (5°C to 135°C)
- Red Liquid

ANGLE

PART NO.	DESCRIPTION	LIST PRICE-A
THW8-A2-280	8" Hot Water	13.95

STRAIGHT

PART NO.	DESCRIPTION	LIST PRICE-A
THW8-S2-280	8" Hot Water	13.10



BRASS THERMOWELLS

- For use with TW25-CB2-250-25

PART NO.	DESCRIPTION	LIST PRICE-A
TW-05/40MM	2.5" 1/2" MPT	7.17

