


**261-3**  
**Single Pole**



**262-2**  
**Two-Pole Disconnect**

## ELECTRIC HEAT REMOTE BULB THERMOSTATS

Specially Designed for use on Portable Heaters, Baseboard Convector and a Wide Variety of Uses in the Commercial Scientific and Agricultural Fields


### FEATURES

- Compact size.
- Model 261 has shaft position that breaks one side of the line.
- Model 262 has shaft position that breaks both sides of the line.
- Silent switch – No chatter or arc-flash.
- Shaft adjustable through range in 240° of arc (295° of arc including “OFF” position).

### SPECIFICATIONS

Ambient Temperature Rating	150°F (66°C)
Dimensions Model 261	2 <sup>15</sup> / <sub>16</sub> " H x 1 <sup>3</sup> / <sub>4</sub> " W x 1 <sup>29</sup> / <sub>32</sub> " D
Dimensions Model 262	3 <sup>11</sup> / <sub>16</sub> " H x 1 <sup>3</sup> / <sub>4</sub> " W x 2 <sup>9</sup> / <sub>16</sub> " D
Shaft extension beyond bracket Model 261	2 <sup>5</sup> / <sub>32</sub> "
Shaft extension beyond bracket Model 262	1 <sup>3</sup> / <sub>16</sub> "
Bulb size Model 261-3	3 <sup>7</sup> / <sub>8</sub> " x 3 <sup>3</sup> / <sub>8</sub> "
Bulb size Model 261-36	3 <sup>3</sup> / <sub>8</sub> " x 3 <sup>3</sup> / <sub>8</sub> "
Bulb size Model 262-2	3 <sup>7</sup> / <sub>8</sub> " x 3 <sup>3</sup> / <sub>8</sub> "

Model Number	Range	Differential	Switch Action	Capillary Length	Resistive (Non-Inductive)
261-3	55 to 103°F (13 to 39°C)	1.5°F	Open on Rise	6"	22.0A, 120 VAC (2500W)
261-36	35 to 95°F (2 to 35°C)	1.5°F	Open on Rise	24"	22.0A, 240 VAC (5000W) 18.0A, 277 VAC (5000W)
262-2	55 to 103°F (13 to 39°C)	1.5°F	Open on Rise	6"	22.0A, 240 VAC (5000W) 18.0A, 277 VAC (5000W)



**2B61-1**  
**Single Pole**

## ELECTRIC HEAT REMOTE BULB THERMOSTAT

Snap-Action Thermostat with Color-Coded Leads have Both Inductive and Non-Inductive Ratings for Increased Flexibility

### FEATURES

- Mounting interchangeable with most competitive models.
- Color-coded leads.
- Shaft adjustable through range in 240° of arc (295° of arc including “OFF” position).
- Liquid charged bulb quickly responds to temperature changes.
- Precision snap switch.

### SPECIFICATIONS

Ambient Temperature Rating	150°F (66°C)
Dimensions	2 <sup>11</sup> / <sub>16</sub> " H x 1 <sup>1</sup> / <sub>4</sub> " W x 1 <sup>7</sup> / <sub>16</sub> " D
Bulb size	5 <sup>1</sup> / <sub>2</sub> " x 3 <sup>3</sup> / <sub>8</sub> "
Lead lengths	18"

Model Number	Range	Differential	Switch Action	Capillary Length	AC Electrical Rating	
					Resistive (Non-Inductive)	Motor (Full Load)
2B61-1	55 to 105°F (13 to 40°C)	3.0°F (1.6°C)	Open on Rise (Snap-Action)	15"	25.0A, 120 V, 240 V 22.0A, 277 V	10.0A, 120 V, 60LRA 6.0A, 240 V, 36LRA