

Magnetic Tip


Tape Measures

Magnetic Attraction!

At last, the obvious! Malco's "Magnetic Tip" tape measure is ideal for every ferrous metalworking project! Use it for HVAC ductwork installations, ceiling grid applications, metal stud framing and more. A powerful magnet and self-supporting 1" wide blade makes 1-person measurements and measuring elevations an easy task. The magnetic tip and big standout blade can even be used as a pick-up tool! A double riveted tip connection, abrasion-resistant, nylon coated blade and rubber-clad housing and blade stop assure lasting performance.



Powerful Magnets! Ideal for working with metal!



Zero Commencement:
When Hanging and pulling magnet,
deduct 1/16" from measurement.



A MULTITUDE OF JOB SITE USES: Metal Ductwork | Ceiling Grids
| Metal Stud Framing Measuring Elevations | One-Person Measurements |
Extended blade tip even works as pick-up tool!

Non-Magnetic Tape Measures



- Non Magnetic 1" Tape Measures
- Double Riveted Tip Connection
- Rubber-Clad Housing

Specifications

Catalog Number	Description	Net Wt. oz. (g)
T416M	1" x 16' Magnetic Tip Tape Measure	10 (284)
T425M	1" x 25' Magnetic Tip Tape Measure	14 (397)
T430M	1" x 30' Magnetic Tip Tape Measure	17 (482)
CT425	1" x 25' Tape Measure	13 (369)
CT430	1" x 30' Tape Measure	16 (454)

48AR




Made from .125 thickness extruded aluminum. This 48" rule is 2" wide. Large and clear, easy to read, thermo-bonded red markings on gray finish. Can be read from either end. Graduations in eighths and sixteenths.

48BS



Tinner's Circumference Rules

48CR



Standard bench rules with circumference readings for sheet metal work. Made from Stainless Steel which means they never need to be oiled. Fully etched markings are black filled for easy reading. 150 circumference inches in 1/8" increments both sides. Rules are 48" long x 1-1/4" wide.



MW10

Ergonomic Pistol Grip offers greater comfort and less wrist fatigue.

Popular 10-inch wheel is versatile for many jobs. Reads up to 10,000 feet.



Strong, positive Clamp-Lock mechanism holds telescoping handle at desired length.


5-Digit Counters to read up to 10,000 ft.
2-Section Telescoping Handles, with positive Clamp-Lock Mechanism.
Ergonomic Pistol Grips.
Handy Kickstands.

Polyvinyl wheel treads assure adequate traction on smooth or rough surfaces.




Distance Measuring Wheels

**New!
in 2011**



MW19

For Accurate Measurements in Most Outdoor Conditions



19"

Applications Include:
Fencing, Paving, Landscaping, Grounds Maintenance, Irrigation, Surveying and Estimating.

- Comfortable Pistol-Grip Handle
- Twist and Lock Telescoping Handle Shaft
- POLYVINYL TREAD for Improved Traction
- Kickstand Molded into Counter-Housing

Specifications

Catalog Number	Description	Upper Scale Graduations	Lower Scale Graduations	Graduations	Net Weight lbs. (oz)
48AR	48" Straight Edge	—	—	Increments to 1/16"	1 (16)
48BS	48" Tinner's Circumference Rule (<i>Semi-Flexible</i>)	Increments to 1/16" both sides	150 circumference inches in 1/8" increments both sides	—	—
48CR	48" Tinner's Circumference Rule (<i>Heavy-Duty</i>)	Increments to 1/16" both sides	150 circumference inches in 1/8" increments both sides	—	—

Catalog Number	Description	Wheel Diameter in. (mm)	Nominal Circumference ft.	Storage Length in.	Extended Length in.	Net Weight lbs. (oz)
MW10	10" Diameter Measuring Wheel	10"	3'	25"	41"	2.10 (0.95)
MW19	19" Diameter Measuring Wheel	19"	5'	29"	41.75"	—

Speed Chalk Reel

100 foot reel rewinds
3-1/2 times FASTER!



Large chalk capacity. Screw off cap prevents chalk leakage. Press-in handle feature lets line out freely, while handle is locked in place. Locking handle also allows use as a plumb bob. Durable high impact chrome plated case.

Chalk / Plumb Line



Chalk / plumb line marks on any surface, including wood, brick, stone and metal. Lightweight case is die-cast aluminum with baked enamel finish. Side action winding reel lock releases automatically on rewind. Hook ring holds line securely. Wedge lock plumb bob tip prevents chalk leakage, opens for quick, easy refilling. "Pop-in" line spool is easily replaceable.

Combination Squares



Machined head has self aligning zinc drawbolt for easy blade installation. Satin finish steel blades are precision stamped in eighths and sixteenths on each side. Level vials are durable acrylic. The SCS16 square also features a hardened scribe with brass bushing and pencil guide on blade.

Powdered Chalk



Vibrant blue and permanent red chalk lays down a hard, clean line that won't blow away. Available in 8 oz. plastic dispensing bottles.

Specifications

Catalog Number	Description	Line Length ft. (m)	Color	Net Weight oz. (g)
CLPS100	Speed Chalk Reel	100 (30.48)	—	—
CLP100	Chalk / Plumb Line	100 (30.48)	—	—
SCS12	12" with solid mounted vial	—	—	12 (340)
SCS16	16" with scribe & pencil guide, 360 view vial	—	—	14 (397)
C8B	Blue Powdered Chalk	—	●	8 (227)
C8R	Red Powdered Chalk	—	●	8 (227)

Replacement Part for CLP100

CLR100 Replacement Spool

Aluminum Levels

Strong and durable extruded aluminum frame is heat treated and grooved on both gauging surfaces.

Unique construction design features multi-directional vial. Dust proof covers are screwed in to protect vial. Top read feature makes for quick, easy reading. Available in 24" (61 cm) length.

With top read center vial.



Magnetic Base

Holds firmly to metal surfaces, thus freeing hands. Magnetic strip is matched to milled aluminum edge for professional accuracy and exceptional holding power.

With top read center vial.

Top Reading Torpedo Levels

Duplex milled aluminum frame with "cyclocac" end plates is lightweight and withstands shock or abuse. Precision cast parallel edges will not scratch work surface. Three large vials - plumb, level and 45°. White vial holders and top read feature facilitate quick, easy reading. Grooved working edge designed for use on pipe and conduit.



Magnetic Base

Pocket Level

Strong molded plastic frame with pocket clip. Multi view vial reads top, bottom or side. Ideal for leveling thermostats.



Specifications

Catalog Number	Description	Line Length in. (cm)	Number of Vials	I-Beam Stock Size in. (mm)
L24AT	24" Aluminum Level	24 (61)	3	1 x 2-1/8 (25 x 54)
L24ATM	24" Aluminum Level with Magnetic Base	24 (61)	3	1 x 2-1/8 (25 x 54)
L5	Pocket Level	5 (127)	1	—
L9	9" Top Reading Torpedo Level	9 (229)	3	—
L9M	9" Top Reading Torpedo Level with Magnetic Base	9 (229)	3	—