



WRS110



WRS220

Key Selling Points

Two Solutions

The WRS110 offers users the high-end resolution of 0.1 oz. accuracy with a 110 lbs. weight capacity for technicians requiring tighter precision. While the WRS220 gives an additional 220 lbs. weight capacity at 0.2 oz. resolution. Both scales feature uncompromising repeatability regardless of how centered the weight is on the measuring platform. The battery life offers unprecedented performance needed for today's wirelessly connected equipment.



Smart Technology

The WRS110 and WRS220 display readings on smart device only, eliminating the hassle of dealing with a wired remote. Both scales use a free iOS® and Android™ App, which offer a user programmable alarm and selectable measuring units between English and Metric. These scales also offer techs an extended range to help reduce dropped connections.

Real-World Toughness

The dynamic body design is very durable and compact with an overload protection to withstand 150% of maximum load capacity.

Competitive Comparison

Refrigerant Scale Competitive Comparison		
Brand	UEi	Fieldpiece
Model #	WRS110	SRS1
		
Capacity (Load cell)	110Lbs (50 Kg)	110Lbs (50 Kg)
Accuracy	68° to 122°F = ±0.25% F.S. ±1 dgt 32° to 68°F & 122° to 158°F = ±0.6% F.S. ±1 dgt	±5%/readin +(10g)
Resolution	0.1 oz (3g.)	0.25 oz
Programmable alarm	•	•
Built-in memory	In App	
Display		In remote
Wireless	•	
35 feet/ 10m wireless distance	•	
Free App	•	
No-slip rubberized pad	•	•
Weight	5.3 lbs	6.6 lbs.
Power	9V	9V
Battery life	Min 40 hrs/ Target 80 hrs	80 hrs
Carrying case		Soft-sided padded case w/shoulder strap
Warranty	1-year	1-year

Download this competitive comparison here.

Competitive product functionality, features, accessories and pricing are based on public information available at time of publication and subject to change without notice. Competitive brands and images are property of their respective owners.

Patent Pending





WRS220 Competitive Comparison

Refrigerant Scale Competitive Comparison				
Brand	UEi	Robinair	Fieldpiece	CPS
Model #	WRS220	TIF9020A	SRS2C	220
				
Capacity (Load cell)	220 lbs (100 Kg)	200Lbs (100 Kg)	220 lbs (100 Kg)	220 lbs (100 Kg)
Accuracy	68° to 122°F ±0.2% F.S. ±1 dgt 32° to 68°F/122° to 158°F ±0.4% F.S. ±1 dgt	±5%/reading	±0.03%/reading +(0.15 lbs)	±.015%/reading
Resolution	0.2 oz (5g.)	0.2 oz	0.25 oz	0.25 oz
Programmable alarm	•	•	•	•
Built-in memory	In App			
Display		In remote	In remote	In remote
Wireless	•		•	
Remote		•	•	•
35 ft (10m) wireless distance	•			
Free App	•			
No-slip rubberized pad	•	•	•	•
Weight	5.3 lbs	6.15 lbs	7.1 lbs	5.6 lbs
Power	9V	9V	(6) AA	(2) 9V
Battery life	Min 40 hrs/ Target 80 hrs	20 hurs	80 hrs	60 hrs
Carrying case	Soft case	Hard plastic case	Nylon case w/strap	Hard plastic case
Warranty	1-year	2-year	1-year	



Download this competitive comparison here.

Competitive product functionality, features, accessories and pricing are based on public information available at time of publication and subject to change without notice. Competitive brands and images are property of their respective owners.

WWW.UEITEST.COM

Copyright © 2017 Kane USA Inc. All Rights Reserved. L408
IOS® and Android™ are property of their respective owners. iPhone® is a trademark of Apple, Inc., registered in the U.S. and other countries.

USA **1.800.547.5740**
CANADA **1.877.475.0648**