

Bulb Wells

Description

Bulb Wells are used in conjunction with Remote Bulb Temperature Controls where bulb insertion into a vessel or container to sense temperature is required. WZ Series Wells are used with TE-6000 and TE-6300 sensors.


A variety of shapes, sizes, and materials are available for a wide range of applications. Refer to the appropriate temperature control for the exact bulb well required.

WEL Series Bulb Wells

Accessories

The Code No. FTG13A-600R packing nut assembly is used in applications where the temperature does not fall below -35°F (-37°C). The maximum liquid pressure limit is

150 PSIG (1034 kPa). Use with Style 1, 3/8 in. diameter bulb for direct immersion application. A19s require models with support tube; A70s and A72s do not need support tubes.



FTG13A-600R Packing Nut Assembly

Selection Charts

WEL Series Bulb Wells

| Code Number | See Fig- ure | Dimension In. | | | Pipe Thread In. | | Material | | Maxi- | Maximum | Type of | Plating | See |
|--------------------------|--------------------|---------------|---------|------|-----------------|--------------|--------------------|--------------------|----------------|------------------|-----------------|-----------|------|
| | | Α | В | С | Inside D | Outside E | Connector | Tube | mum Temp °F | Pressure PSIG | Solder Joint | | Note |
| WEL11A-601R | 2 | 2-3/8 | 2-5/16 | .299 | - | 1/2 | Brass | Copper | 250 | 300 | Soft | - | 1 |
| WZ-1000-2 | 1 | 5-1/4 | 1-1/4 | .500 | 1/2 | 1/2 | Stainless steel | Stainless steel | 300 | 400 | - | - | 3 |
| WZ-1000-4 | 1 | 5-1/4 | 1-1/4 | .500 | 1/2 | 1/2 | Stainless steel | Stainless steel | 600 | 400 | - | _ | _ |
| WZ-1000-5 | 2 | 2-3/8 | 2-5/16 | .299 | - | 1/2 | Malleable | Brass | 250 | 300 | - | - | 3 |
| WEL14A-600R ¹ | 3 | 4-3/4 | 1-13/16 | .444 | _ | 1/2 | Monel | Monel | 700 | 1000 | TIG weld | - | 2 |
| WEL14A-601R ¹ | 3 | 7-9/16 | 1-13/16 | .430 | - | 1/2 | Brass | Copper | 250 | 300 | Silver | Brite-Dip | 2 |
| WEL14A-602R ¹ | 3 | 4-15/16 | 1-13/16 | .430 | - | 1/2 | Brass | Copper | 250 | 300 | Silver | Brite-Dip | 2 |
| WEL14A-603R ¹ | 3 | 5 13/16 | 1 13/16 | .430 | - | 1/2 | Brass | Copper | 250 | 300 | Silver | Brite-Dip | 2 |
| WEL16A-600R | 2 | 2-3/8 | 1-5/16 | .299 | - | 1/2 | Brass | Copper | 250 | 300 | Soft | - | 1 |
| WEL16A-601R | 2 | 2-13/16 | 1-13/16 | .375 | - | 1/2 | Brass | Copper | 250 | 300 | Soft | - | 2 |
| WEL17A-600R ² | 1 | 10-7/16 | 3/4 | .763 | 1/2 | 3/4 | Malleable | Copper | 250 | 250 | Silver | Tin | - |
| WEL17A-601R ² | 1 | 8-11/16 | 3/4 | .763 | 1/2 | 3/4 | Malleable | Copper | 250 | 250 | Silver | Tin | _ |
| WEL17A-602R ² | 1 | 10-7/16 | 3/4 | .753 | 1/2 | 3/4 | Malleable | Steel | 250 | 540 | Silver | Tin | - |
| WEL17A-604R ² | 1 | 14-13/32 | 3/4 | .763 | 1/2 | 3/4 | Malleable | Copper | 250 | 250 | Silver | Tin | - |
| WEL18A-600R ² | 1 | 3-1/2 | 3/4 | .773 | 1/2 | 3/4 | Malleable | Steel | 250 | 150 | Silver | Tin | - |
| WEL18A-602R ² | 1 | 3-1/2 | 3/4 | .773 | 1/2 | 3/4 | Malleable | Brass | 250 | 150 | Silver | Tin | - |

- 1. For 3/8 in. style 1 bulbs.
- 2. For 11/16 in. diameter style 4 bulbs. Style 1 can be used, but is not fastened into well
- Note 1: With phenolic bushing; 0.093 in. slot.
- Note 2: With phenolic bushing; 0.125 in. slot.
- Note 3: Includes thermal compound.

T-800 Wells

| Code Number | Description | | | | | | |
|-------------|----------------------------------|--|--|--|--|--|--|
| T-800-1605 | Brass well, 6-1/2 inch | | | | | | |
| T-800-1606 | Stainless steel well, 5-1/4 inch | | | | | | |
| T-800-1618 | Brass well, 9-1/2 inch | | | | | | |

T-800 Wells (Continued)

| Code Number | Description |
|-------------|-----------------------------|
| T-800-1620 | Brass well, 9-1/2 inch |
| T-800-1624 | Dual brass well, 6-1/2 inch |