

For Liquid and Steam Service

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

LEAD FREE*

Series LF777S,

LFS777S

Wye-Pattern Lead Free* Bronze Strainers

Sizes: 1/2" – 4" (15-100mm)

Series LF777S, LFS777S Wye-Pattern Lead Free* Bronze Strainers are designed to protect system components from dirt, rust and other damaging debris in the piping system. This series features a retainer cap tapped for closure plug. The LF777S and LFS777S feature Lead Free* construction to comply with Lead Free* installation requirements.

Features

- Lead Free* cast copper silicon alloy body
- Wye-pattern
- Retainer cap tapped for closure plug

Models

LF777S – 1/2" – 4" (15 – 100mm) threaded connections

LFS777S – 1/2" – 2" (15 – 50mm) solder connections

Specifications

A wye-pattern Lead Free* bronze strainer to be installed as indicated on the plans. Lead Free* Wye-Pattern Cast copper silicon alloy Strainers shall be constructed using Lead Free* materials. Lead Free LF777S and LFS777S shall comply with state codes and standards, where applicable, requiring reduced lead content. The strainer must have retainer cap tapped for closure plug. Strainer shall be rated to 400psi (27.6 bar) WOG @ 210°F (99°C); 125psi (8.6 bar) WSP @ 353°F (178°F) for sizes 1/2" – 3" (15 – 75mm) and 300psi (20.7 bar) WOG @ 210°F (99°C); 125psi (8.6 bar) @ 353°F (178°C) for size 4" (100mm). Strainer shall be a Watts Series LF777S (threaded ends) or LFS777S (solder ends).



LF777S



LFS777S

BAA/ARRA Compliant**

**This product complies with the Buy American Act and The American Recovery and Reinvestment Act. For more information, visit watts.com.

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

The logo for Watts, featuring a stylized blue and white 'W' followed by the word "WATTS" in a bold, black, sans-serif font with a registered trademark symbol.

Materials

Body:	Lead Free* cast copper silicon alloy
Retainer Cap:	1/2" (15mm): Lead Free* copper silicon alloy 3/4" – 4" (20-100): Lead Free* cast copper silicon alloy
Cap Gasket:	1/2" – 2" (15-50mm): EPDM Other sizes consult factory
Standard Screen:	1/2" – 2 1/2" (15-65mm): 304 stainless steel #20 mesh, 3" (75mm): 3/64" (1.2mm) 304 stainless steel perforated screen 4" (100mm): 1/8" (3mm) 304 stainless steel perforated screen


Pressure – Temperature

Maximum Working Pressure:	
1/2" – 3" (15-75mm)	400psi (27.6 bar) WOG @ 210°F (99°C) 125psi (8.6 bar) WSP @ 353°F (178°F)
4" (100mm)	300psi (20.7 bar) WOG @ 210°F (99°C) 125psi (8.6 bar) WSP @ 353°F (178°F)

Screen Options

304 Stainless Steel Wire Mesh Liners: (#30, #40, #60, #80, #100)
304 Stainless Steel Perforated Screens: (1/32", 3/64", 1/16", 1/8", 3/16", 1/4")
Consult factory for ordering codes


Performance Data



Dimensions – Weights


LF777S

SIZE (DN)		DIMENSIONS						WEIGHT	
		A		B		C (NPT)			
in.	mm	in.	mm	in.	mm	in.	mm	lbs.	kgs.
1/4	8	2 11/16	68	1 11/16	43	3/8	10	1.7	0.77
3/8	10	2 11/16	68	1 11/16	43	3/8	10	1.7	0.77
1/2	15	3	76	2	51	3/8	10	1.7	0.77
3/4	20	3 5/16	84	2 5/16	59	1/2	15	1.7	0.77
1	25	4 1/2	114	2 5/16	59	3/4	20	2.7	1.22
1 1/4	32	5 1/8	130	3 1/8	79	3/4	20	3.0	1.36
1 1/2	40	5 7/8	149	3 3/4	95	1	25	4.0	1.81
2	50	6 3/16	157	4 7/8	124	1 1/4	32	7.4	3.36
2 1/2	65	8 1/8	206	4 19/16	125	1 1/4	32	12.0	5.44
3	75	10 7/8	257	6 11/16	170	1 1/2	40	24.0	10.90
4	100	13	325	10 1/2	267	1 1/2	40	41.0	18.60



LFS777S

SIZE (DN)		DIMENSIONS						WEIGHT	
		A		B		C (NPT)			
in.	mm	in.	mm	in.	mm	in.	mm	lbs.	kgs.
1/2	15	3 3/8	86	2 1/16	52	3/8	10	1.5	0.68
3/4	20	3 3/4	95	2 9/16	65	1/2	15	1.6	0.73
1	25	5	127	3	76	3/4	20	2.5	1.13
1 1/4	32	5 5/8	143	3 1/4	82	3/4	20	2.8	1.25
1 1/2	40	6 7/16	164	3 13/16	97	1	25	4.0	1.81
2	50	7 1/2	191	4 3/8	118	1 1/4	32	7.4	3.39



A Watts Water Technologies Company



ISO 9001-2008
CERTIFIED

USA: Tel: (978) 688-1811 • Fax: (978) 794-1848 • www.watts.com
Canada: Tel: (905) 332-4090 • Fax: (905) 332-7068 • www.watts.ca