

quality . service
innovation . integrity

Model 76



Features

This "Aqua-Mate" model submersible pump is designed for use in residential or commercial dewatering applications and can be used to transfer groundwater or effluent. The inner stainless steel can is designed to provide great heat dissipation from the motor, ensuring a long service life. As with every Zoeller pump, each one is 100% pressure-tested, submerged and run to ensure quality and reliability for years of trouble-free performance! This attention to detail is an inherent feature of every pump, making it one of the most reliable in the industry.

- Automatic units include a float-operated, 2-pole mechanical switch, a plastic float guard, a stainless steel switch arm, and a solid, buoyant polypropylene float, which prevents water from filling the float and causing a malfunction.
- For nonautomatic pumps, variable level control systems and containers of various sizes are available for longer cycles.
- Includes a plastic handle for easy installation and removal.
- Hermetically sealed to be watertight, dust-tight, and completely submersible.

Reserve Powered Design: For unusual conditions, a reserve safety factor is engineered into the design of every pump.

Specifications

Motor Characteristics

Horse Power	1/2 HP
Voltage	115 V
Phase	1 Ph
Hertz	60 Hz
RPM	3400 RPM
Type	Permanent split capacitor
Insulation	Class B
Amps	5.0 Amps

Pump Characteristics

Operation	Automatic or nonautomatic
Auto On/ Off Points	8-1/2" / 3-5/8" (21.6 cm / 9.2 cm)
Discharge Size	1-1/2" NPT
Solids Handling	3/8" (10 mm) spherical solids
Cord Length	9' (3 m) standard
Cord Type	UL listed, 3-wire cord and plug
Max Head	25' (7.6 m)
Max Flow Rate	50 GPM (189 LPM)
Max Operating Temp	110° F (43° C)
Cooling	Oil free
Motor Protection	Auto reset thermal overload

Materials Characteristics

Motor Housing	Engineered plastic
Pump Housing	Engineered plastic
Base	Engineered plastic
Upper Bearing	Ball bearing
Lower Bearing	Ball bearing
Mechanical Seals	Carbon and ceramic
Impeller Type	Non-clogging vortex
Impeller	Engineered plastic
Hardware	Stainless steel
Motor Shaft	410 stainless steel
Gasket	Buna-N o-ring

60 Hz




PUMP COMPANY


Zoeller Family of Water Solutions™

FM1779_Ea

Model 76



013436



SK1979

Model

Model Number	Seal	Mode	Volts	Phase	Amps	HP	Hz	Lbs	Kg
M76	Single	Auto	115	1	5.0	1/2	60	12	5
N76	Single	Non	115	1	5.0	1/2	60	12	5

Your Peace of Mind is Our Top Priority®
3649 Cane Run Rd | Louisville, KY 40211 USA
1-800-928-7867 | Fax: +1 502-774-3624
www.zoeller.com

Product information presented here reflects conditions at time of publication. Consult factory regarding discrepancies or inconsistencies. Copyright 2013. All rights reserved.