



Air Conditioning & Heating

PRODUCT SPECIFICATIONS



13 SEER / R-410A

1½- TO 5-TON

COOLING CAPACITY:
18,000 - 60,000 BTU/H



GSX13

ENERGY-EFFICIENT

SPLIT SYSTEM AIR CONDITIONER

The Goodman® brand GSX13 uses the environmentally friendly refrigerant R-410A and features operating sound levels that are among the best in the heating and cooling industry. With its 13 SEER rating, the GSX13 will help reduce energy consumption throughout the life of the system compared to lower SEER-rated equipment.

Standard Features

- R-410A environmentally friendly refrigerant
- Energy-efficient compressor
- Factory-installed filter dryer
- Copper tube/enhanced aluminum fin coil
- Service valves with sweat connections and easy-access gauge ports
- Contactor with lug connection
- Ground lug connection
- ARI Certified; ETL Listed

Cabinet Features

- Unique Goodman® sound control top design
- Steel louver coil guard
- Heavy-gauge galvanized-steel cabinet
- Attractive Architectural Gray powder-paint finish with 500-hour salt-spray approval
- Top and side maintenance access
- Single-panel access to controls with space provided for field-installed accessories
- When properly anchored, meets the 2001 Florida Building Code unit integrity requirements for hurricane-type winds (Anchor bracket kits available.)

Contents

Nomenclature.....	2
Product Specifications.....	3
Dimensions.....	5
Expanded Cooling Data.....	6
ARI Performance Ratings.....	26
Wiring Diagrams.....	41
Accessories	43



NOMENCLATURE

	G	S	X	13	036	1	A	A	
	1	2	3	4,5	6,7,8	9	10	11	
Brand							Engineering *		
G Goodman® (Standard Feature Set Models)							Minor Revision		
S Goodman® (High Feature Set Models)							Engineering *		
							Major Revision		
Product Category							Electrical		
S Split System							1	208/230 V, 1 Phase, 60 Hz	
							2	220/240 V, 1 Phase, 50 Hz	
							3	208/230 V, 3 Phase, 60 Hz	
							4	460 V, 3 Phase, 60 Hz	
							5	380/415 V, 3 Phase, 50 Hz	
Unit Type							Nominal Capacity		
C Condenser R-22							018	1½ Tons	048 4 Tons
X Condenser R-410A							024	2 Tons	060 5 Tons
H Heat Pump R-22							030	2½ Tons	090 7½ tons
Z Heat Pump R-410A							036	3 Tons	120 10 Tons
							042	3½ Tons	
Efficiency									
13 13 SEER									
14 14 SEER									
16 16 SEER									

* Neither used for order entry or inventory management.

SPECIFICATIONS

	GSX13 0181A*	GSX13 0181B*	GSX13 0241A*	GSX13 0241B*	GSX13 0301A*	GSX13 0301B*
Capacities						
Nominal Cooling (BTU/h)	18,000	18,000	24,000	24,000	30,000	30,000
SEER / EER	13 / 11	13 / 11	13 / 11	13 / 11	13 / 11	13 / 11
Decibels	72	72	72	72	73	73
Compressor						
RLA	9.0	9.0	13.4	13.5	12.8	12.8
LRA	48	48	58.3	58.3	64	64
Condenser Fan Motor						
Horsepower	1/6	1/6	1/6	1/6	1/6	1/6
FLA	1.1	1.1	1.1	1.1	1.1	1.1
Refrigeration System						
Refrigerant Line Size ¹						
Liquid Line Size ("O.D.)	3/8"	3/8"	3/8"	3/8"	3/8"	3/8"
Suction Line Size ("O.D.)	3/4"	3/4"	3/4"	3/4"	3/4"	3/4"
Refrigerant Connection Size						
Liquid Valve Size ("O.D.)	3/8"	3/8"	3/8"	3/8"	3/8"	3/8"
Suction Valve Size ("O.D.) ^{3 4}	3/4"	3/4"	3/4"	3/4"	3/4"	3/4"
Valve Type	Sweat	Sweat	Sweat	Sweat	Sweat	Sweat
Refrigerant Charge	120	75	116	82	129	84
Shipped with Orifice Size	0.049	0.051	0.053	0.057	0.059	0.059
Electrical Data						
Voltage-Hz / Phase	208/230-60/1	208/230-60/1	208/230-60/1	208/230-60/1	208/230-60/1	208/230-60/1
Minimum Circuit Ampacity ²	12.3	12.3	17.9	18.0	17.1	17.1
Max. Overcurrent Protection ³	20 amps	20 amps	30 amps	30 amps	30 amps	30 amps
Min / Max Volts	197/253	197/253	197/253	197/253	197/253	197/253
Electrical Conduit Size	1/2" or 3/4"	1/2" or 3/4"	1/2" or 3/4"	1/2" or 3/4"	1/2" or 3/4"	1/2" or 3/4"
Ship Weight (lbs)	178	149	178	151	180	152

¹ Wire size should be determined in accordance with National Electrical Codes; extensive wire runs will require larger wire sizes

² Must use time-delay fuses or HACR-type circuit breakers of the same size as noted.

³ Installer will need to supply 3/4" to 7/8" adapters for suction line connections.

⁴ Installer will need to supply 7/8" to 1 1/8" adapters for suction line connections.

Notes

- Always check the S&R plate for electrical data on the unit being installed.
- Unit is charged with refrigerant for 15' of 3/8" liquid line. System charge must be adjusted per Installation Instructions Final Charge Procedure.

SPECIFICATIONS (CONT.)

	GSX13 0361A*	GSX13 0421A*	GSX13 0421B*	GSX13 0481A*	GSX13 0481B*	GSX13 0601A*
Capacities						
Nominal Cooling (BTU/h)	36,000	42,000	42,000	48,000	48,000	60,000
SEER / EER	13 / 11	13 / 11	13 / 11	13 / 11	13 / 11	13 / 11
Decibels	74	75	75	76	76	73
Compressor						
RLA	16.6	17.9	17.9	19.8	19.9	26.4
LRA	79	112	112	109	109	134
Condenser Fan Motor						
Horsepower	1/6	1/6	1/4	1/4	1/4	1/4
FLA	1.1	1.1	1.5	1.5	1.5	1.5
Refrigeration System						
Refrigerant Line Size ¹						
Liquid Line Size ("O.D.)	3/8"	3/8"	3/8"	3/8"	3/8"	3/8"
Suction Line Size ("O.D.)	7/8"	1 1/8"	1 1/8"	1 1/8"	1 1/8"	1 1/8"
Refrigerant Connection Size						
Liquid Valve Size ("O.D.)	3/8"	3/8"	3/8"	3/8"	3/8"	3/8"
Suction Valve Size ("O.D.) ^{3 4}	3/4" ³	7/8" ⁴	7/8" ⁴	7/8" ⁴	7/8" ⁴	7/8" ⁴
Valve Type	Sweat	Sweat	Sweat	Sweat	Sweat	Sweat
Refrigerant Charge	131	151	127	166	131	187
Shipped with Orifice Size	0.068	0.074	0.076	0.080	0.080	0.092
Electrical Data						
Voltage-Hz / Phase	208/230-60/1	208/230-60/1	208/230-60/1	208/230-60/1	208/230-60/1	208/230-60/1
Minimum Circuit Ampacity ²	21.9	23.5	23.9	26.3	26.3	34.5
Max. Overcurrent Protection ³	35 amps	40 amps	40 amps	45 amps	45 amps	60 amps
Min / Max Volts	197/253	197/253	197/253	197/253	197/253	197/253
Electrical Conduit Size	1/2" or 3/4"	1/2" or 3/4"	1/2" or 3/4"	1/2" or 3/4"	1/2" or 3/4"	1/2" or 3/4"
Ship Weight (lbs)	197	219	194	225	195	240

¹ Wire size should be determined in accordance with National Electrical Codes; extensive wire runs will require larger wire sizes

² Must use time-delay fuses or HACR-type circuit breakers of the same size as noted.


³ Installer will need to supply 3/4" to 7/8" adapters for suction line connections.

⁴ Installer will need to supply 7/8" to 1 1/8" adapters for suction line connections.

Notes

- Always check the S&R plate for electrical data on the unit being installed.
- Unit is charged with refrigerant for 15' of 3/8" liquid line. System charge must be adjusted per Installation Instructions Final Charge Procedure.

DIMENSIONS



Model	Dimensions		
	W"	D"	H"
GSX130181A*	26"	26"	32¼"
GSX130181B*	26"	26"	27½"
GSX130241A*	26"	26"	32¼"
GSX130241B*	26"	26"	27½"
GSX130301A*	26"	26"	32¼"
GSX130301B*	26"	26"	27½"
GSX130361A*	29"	29"	32¼"
GSX130421A*	29"	29"	34¼"
GSX130421B*	29"	29"	36¼"
GSX130481A*	29"	29"	38¼"
GSX130481B*	29"	29"	36¼"
GSX130601A*	35½"	35½"	38¼"

EXPANDED COOLING DATA — GSX130301B* / CA*F3030*6B* (CONT.)

IDB	Airflow	Outdoor Ambient Temperature																													
		65°F						75°F						85°F						105°F						115°F					
		Entering Indoor Wet Bulb Temperature																													
875	MBh	59	63	67	71	59	63	67	71	59	63	67	71	59	63	67	71	59	63	67	71	59	63	67	71						
		25.8	26.4	28.2	30.1	25.2	25.8	27.5	29.4	24.6	25.1	26.9	28.7	24.0	24.5	26.2	28.0	22.8	23.3	24.9	26.6	21.1	21.6	23.1	24.7						
	S/T	0.86	0.81	0.66	0.49	0.90	0.84	0.68	0.51	0.92	0.86	0.70	0.52	0.95	0.89	0.72	0.54	0.98	0.92	0.75	0.56	0.99	0.93	0.76	0.57						
	ΔT	23	22	20	16	24	23	20	16	24	23	20	16	24	23	20	16	24	23	20	16	22	21	18	15						
	kW	1.97	2.01	2.07	2.13	2.11	2.15	2.22	2.29	2.24	2.28	2.35	2.43	2.35	2.40	2.47	2.55	2.44	2.49	2.57	2.66	2.52	2.58	2.66	2.75						
	Amps	7.0	7.1	7.3	7.6	7.5	7.7	7.9	8.2	8.2	8.4	8.6	9.0	8.7	8.9	9.2	9.6	9.3	9.5	9.8	10.2	9.8	10.1	10.4	10.8						
	Hi PR	233	250	264	276	261	281	297	310	297	320	338	352	338	364	384	401	381	410	432	451	420	452	478	498						
	Lo PR	104	111	121	129	110	117	128	136	114	122	133	142	120	128	140	149	126	134	146	156	130	139	151	161						
	MBh	28.0	28.6	30.5	32.6	27.3	27.9	29.8	31.9	26.7	27.2	29.1	31.1	26.0	26.6	28.4	30.4	24.7	25.3	27.0	28.8	22.9	23.4	25.0	26.7						
	S/T	0.90	0.84	0.68	0.51	0.93	0.87	0.71	0.53	0.95	0.89	0.73	0.54	0.98	0.92	0.75	0.56	1.00	0.96	0.78	0.58	1.00	0.96	0.78	0.59						
80	ΔT	23	22	19	15	23	22	19	16	23	22	19	16	23	22	19	16	23	22	19	15	21	21	18	14						
	kW	2.01	2.05	2.12	2.18	2.16	2.20	2.27	2.34	2.29	2.34	2.41	2.49	2.40	2.46	2.53	2.61	2.50	2.56	2.64	2.72	2.59	2.64	2.73	2.82						
	Amps	7.1	7.3	7.6	7.8	7.7	7.9	8.2	8.5	8.4	8.6	8.9	9.2	9.0	9.2	9.5	9.9	9.6	9.8	10.1	10.5	10.1	10.4	10.7	11.1						
	Hi PR	240	258	273	284	269	290	306	319	306	330	348	363	349	375	396	413	392	422	446	465	433	466	493	514						
	Lo PR	107	114	125	133	114	121	132	140	118	126	137	146	124	132	144	153	130	138	151	161	134	143	156	166						
	MBh	28.8	29.4	31.4	33.6	28.1	28.7	30.7	32.8	27.5	28.1	30.0	32.1	26.8	27.4	29.3	31.3	25.5	26.0	27.8	29.7	23.6	24.1	25.7	27.5						
	S/T	0.94	0.88	0.72	0.54	1.00	0.91	0.74	0.56	1.00	0.94	0.76	0.57	1.00	0.97	0.79	0.59	1.00	1.00	0.82	0.61	1.00	1.00	0.82	0.62						
	ΔT	22	21	18	15	23	21	19	15	22	21	19	15	22	22	19	15	21	21	19	15	19	20	17	14						
	kW	2.03	2.07	2.13	2.20	2.18	2.22	2.29	2.36	2.31	2.36	2.43	2.51	2.42	2.48	2.55	2.64	2.52	2.58	2.66	2.74	2.61	2.66	2.75	2.84						
	Amps	7.2	7.4	7.6	7.9	7.8	8.0	8.2	8.6	8.5	8.7	9.0	9.3	9.1	9.3	9.6	10.0	9.6	9.9	10.2	10.6	10.2	10.5	10.8	11.2						
Hi PR	242	261	275	287	272	293	309	322	309	333	351	367	352	379	400	417	396	426	450	470	438	471	498	519							
Lo PR	109	116	126	134	115	122	133	142	119	127	138	147	125	133	145	155	131	140	152	162	136	144	158	168							

85	875	MBh	26.3	26.8	28.0	29.9	25.7	26.1	27.4	29.2	25.0	25.5	26.7	28.5	24.4	24.9	26.1	27.8	23.2	23.7	24.8	26.4	21.5	21.9	23.0	24.5
		S/T	0.91	0.87	0.79	0.64	0.94	0.91	0.82	0.66	0.96	0.93	0.84	0.68	0.99	0.96	0.86	0.70	1.00	0.99	0.90	0.73	1.00	1.00	0.91	0.73
		ΔT	25	25	23	20	25	25	24	20	25	25	24	20	25	25	24	21	24	25	23	20	23	23	22	19
		kW	1.98	2.02	2.08	2.15	2.13	2.17	2.24	2.31	2.25	2.30	2.37	2.45	2.37	2.42	2.49	2.57	2.46	2.51	2.59	2.68	2.54	2.60	2.68	2.77
		Amps	7.0	7.2	7.4	7.7	7.6	7.8	8.0	8.3	8.2	8.4	8.7	9.0	8.8	9.0	9.3	9.7	9.4	9.6	9.9	10.3	9.9	10.2	10.5	10.9
	Hi PR	235	253	267	279	264	284	300	313	300	323	341	356	342	368	388	405	384	414	437	456	425	457	483	503	
	Lo PR	105	112	122	130	111	118	129	138	116	123	134	143	121	129	141	150	127	135	148	157	132	140	153	163	
	MBh	28.5	29.0	30.4	32.4	27.8	28.3	29.7	31.7	27.1	27.7	29.0	30.9	26.5	27.0	28.3	30.1	25.1	25.6	26.8	28.6	23.3	23.7	24.9	26.5	
	S/T	0.94	0.91	0.82	0.66	0.97	0.94	0.85	0.69	1.00	0.96	0.87	0.71	1.00	0.99	0.90	0.73	1.00	1.00	0.93	0.76	1.00	1.00	0.94	0.76	
	ΔT	25	24	23	20	25	24	23	20	25	24	23	20	24	25	23	20	23	24	23	20	21	22	21	19	
1000	kW	2.03	2.07	2.13	2.20	2.18	2.22	2.29	2.36	2.31	2.36	2.43	2.51	2.42	2.48	2.55	2.64	2.52	2.58	2.66	2.74	2.61	2.66	2.75	2.84	
	Amps	7.2	7.4	7.6	7.9	7.8	8.0	8.2	8.6	8.5	8.7	9.0	9.3	9.1	9.3	9.6	10.0	9.6	9.9	10.2	10.6	10.2	10.5	10.8	11.2	
	Hi PR	242	261	275	287	272	293	309	322	309	333	351	367	352	379	400	417	396	426	450	470	438	471	498	519	
	Lo PR	109	116	126	134	115	122	133	142	119	127	138	147	125	133	145	155	131	140	152	162	136	144	158	168	
	MBh	29.3	29.9	31.3	33.4	28.6	29.2	30.6	32.6	27.9	28.5	29.8	31.8	27.3	27.8	29.1	31.1	25.9	26.4	27.7	29.5	24.0	24.5	25.6	27.3	
1125	S/T	0.98	0.95	0.86	0.70	1.00	0.98	0.89	0.72	1.00	1.00	0.91	0.74	1.00	1.00	0.94	0.76	1.00	1.00	0.98	0.79	1.00	1.00	0.98	0.80	
	ΔT	24	23	22	19	23	23	22	19	23	23	22	19	22	23	22	19	21	22	22	19	20	20	21	18	
	kW	2.04	2.08	2.15	2.21	2.19	2.24	2.31	2.38	2.33	2.37	2.45	2.53	2.44	2.49	2.57	2.66	2.54	2.60	2.68	2.77	2.63	2.69	2.77	2.86	
	Amps	7.3	7.4	7.7	8.0	7.9	8.1	8.3	8.6	8.5	8.8	9.0	9.4	9.1	9.4	9.7	10.0	9.7	10.0	10.3	10.7	10.3	10.6	10.9	11.3	
	Hi PR	245	263	278	290	275	296	312	326	312	336	355	370	356	383	404	422	400	431	455	474	442	476	503	524	
Lo PR	110	117	127	136	116	123	135	143	120	128	140	149	126	135	147	156	133	141	154	164	137	146	159	170		

DB: Entering Indoor Dry Bulb Temperature
High and low pressures are measured at the liquid and suction service valves.

Shaded area reflects ARI conditions

Amps = outdoor unit amps (comp. + fan)
kW = Total system power

EXPANDED COOLING DATA — GSX130361A* / CA*F4860*6**

		Outdoor Ambient Temperature																							
		65°F				75°F				85°F				95°F				105°F				115°F			
IDB	Airflow	59	63	67	71	59	63	67	71	59	63	67	71	59	63	67	71	59	63	67	71	59	63	67	71
70	MBh	34.3	35.5	38.9	-	33.5	34.7	38.0	-	32.7	33.9	37.1	-	31.9	33.1	36.2	-	30.3	31.4	34.4	-	28.1	29.1	31.9	-
	S/T	0.72	0.60	0.42	-	0.75	0.63	0.43	-	0.77	0.64	0.44	-	0.79	0.66	0.46	-	0.82	0.69	0.48	-	0.83	0.69	0.48	-
	ΔT	17	15	11	-	17	15	11	-	17	15	11	-	17	15	11	-	17	15	11	-	16	14	10	-
	kW	2.45	2.50	2.58	-	2.63	2.69	2.77	-	2.79	2.85	2.94	-	2.94	3.00	3.09	-	3.06	3.12	3.22	-	3.16	3.23	3.33	-
	Amps	8.8	9.0	9.3	-	9.6	9.8	10.1	-	10.4	10.7	11.0	-	11.1	11.4	11.8	-	11.9	12.2	12.6	-	12.6	12.9	13.4	-
	Hi PR	234	252	266	-	262	282	298	-	298	321	339	-	340	366	386	-	382	411	434	-	422	454	480	-
	Lo PR	106	112	123	-	112	119	130	-	116	123	135	-	122	130	142	-	128	136	148	-	132	141	153	-
	MBh	33.3	34.5	37.8	-	32.5	33.7	36.9	-	31.7	32.9	36.1	-	31.0	32.1	35.2	-	29.4	30.5	33.4	-	27.3	28.3	31.0	-
	S/T	0.69	0.58	0.40	-	0.71	0.60	0.41	-	0.73	0.61	0.42	-	0.76	0.63	0.44	-	0.79	0.66	0.45	-	0.79	0.66	0.46	-
	ΔT	18	15	12	-	18	15	12	-	18	15	12	-	18	16	12	-	18	15	12	-	17	14	11	-
1050	kW	2.43	2.48	2.56	-	2.61	2.67	2.75	-	2.77	2.83	2.92	-	2.91	2.97	3.07	-	3.03	3.10	3.20	-	3.13	3.20	3.31	-
	Amps	8.7	9.0	9.3	-	9.5	9.7	10.0	-	10.3	10.6	10.9	-	11.0	11.3	11.7	-	11.8	12.1	12.5	-	12.5	12.8	13.2	-
	Hi PR	231	249	263	-	260	279	295	-	295	318	336	-	336	362	382	-	378	407	430	-	418	450	475	-
	Lo PR	105	111	122	-	111	118	128	-	115	122	133	-	121	128	140	-	126	135	147	-	131	139	152	-
	MBh	30.7	31.9	34.9	-	30.0	31.1	34.1	-	29.3	30.4	33.3	-	28.6	29.6	32.5	-	27.2	28.2	30.8	-	25.2	26.1	28.6	-
	S/T	0.67	0.56	0.38	-	0.69	0.58	0.40	-	0.71	0.59	0.41	-	0.73	0.61	0.42	-	0.76	0.63	0.44	-	0.76	0.64	0.44	-
	ΔT	18	15	12	-	18	16	12	-	18	16	12	-	18	16	12	-	18	16	12	-	17	15	11	-
	kW	2.38	2.43	2.50	-	2.55	2.61	2.69	-	2.71	2.76	2.85	-	2.84	2.90	2.99	-	2.96	3.02	3.12	-	3.06	3.12	3.22	-
	Amps	8.5	8.7	9.0	-	9.2	9.4	9.7	-	10.0	10.3	10.6	-	10.7	11.0	11.4	-	11.4	11.7	12.1	-	12.1	12.4	12.9	-
	Hi PR	224	242	255	-	252	271	286	-	286	308	326	-	326	351	371	-	367	395	417	-	406	436	461	-
	Lo PR	101	108	118	-	107	114	125	-	111	119	129	-	117	125	136	-	123	130	142	-	127	135	147	-
75	MBh	34.9	35.9	38.9	41.7	34.1	35.1	38.0	40.7	33.3	34.2	37.1	39.8	32.4	33.4	36.2	38.8	30.8	31.7	34.4	36.9	28.6	29.4	31.8	34.2
	S/T	0.82	0.74	0.56	0.36	0.85	0.76	0.58	0.37	0.87	0.78	0.59	0.38	0.90	0.81	0.61	0.39	0.94	0.84	0.63	0.41	0.94	0.84	0.64	0.41
	ΔT	20	18	15	10	20	18	15	10	20	18	15	10	20	18	15	10	20	18	15	10	18	17	14	10
	kW	2.47	2.52	2.60	2.68	2.66	2.71	2.79	2.88	2.82	2.88	2.97	3.06	2.96	3.02	3.12	3.22	3.08	3.15	3.25	3.36	3.19	3.26	3.36	3.47
	Amps	8.9	9.1	9.4	9.8	9.6	9.9	10.2	10.6	10.5	10.8	11.1	11.6	11.3	11.5	11.9	12.4	12.0	12.3	12.7	13.2	12.7	13.0	13.5	14.0
	Hi PR	236	254	268	280	265	285	301	314	301	324	342	357	343	369	390	407	386	415	439	458	427	459	485	506
	Lo PR	107	114	124	132	113	120	131	139	117	125	136	145	123	131	143	152	129	137	150	160	133	142	155	165
	MBh	33.9	34.9	37.7	40.5	33.1	34.1	36.9	39.6	32.3	33.2	36.0	38.6	31.5	32.4	35.1	37.7	29.9	30.8	33.3	35.8	27.7	28.5	30.9	33.2
	S/T	0.78	0.70	0.53	0.34	0.81	0.73	0.55	0.35	0.83	0.75	0.56	0.36	0.86	0.77	0.58	0.37	0.89	0.80	0.60	0.39	0.90	0.81	0.61	0.39
	ΔT	20	19	15	11	21	19	16	11	21	19	16	11	21	19	16	11	20	19	15	11	19	18	14	10
	kW	2.45	2.50	2.58	2.66	2.63	2.69	2.77	2.86	2.79	2.85	2.94	3.04	2.94	3.00	3.09	3.20	3.06	3.12	3.22	3.33	3.16	3.23	3.33	3.44
1050	Amps	8.8	9.0	9.3	9.7	9.6	9.8	10.1	10.5	10.4	10.7	11.0	11.5	11.1	11.4	11.8	12.3	11.9	12.2	12.6	13.1	12.6	12.9	13.4	13.9
	Hi PR	234	252	266	277	262	282	298	311	298	321	339	354	340	366	386	403	382	411	434	453	422	454	480	501
	Lo PR	106	112	123	131	112	119	130	138	116	123	135	144	122	130	142	151	128	136	148	158	132	141	153	163
	MBh	31.3	32.2	34.8	37.4	30.5	31.4	34.0	36.5	29.8	30.7	33.2	35.6	29.1	29.9	32.4	34.8	27.6	28.4	30.8	33.0	25.6	26.3	28.5	30.6
	S/T	0.76	0.68	0.51	0.33	0.78	0.70	0.53	0.34	0.80	0.72	0.54	0.35	0.83	0.74	0.56	0.36	0.86	0.77	0.58	0.37	0.87	0.78	0.59	0.38
	ΔT	21	19	16	11	21	19	16	11	21	19	16	11	21	19	16	11	21	19	16	11	19	18	15	10
	kW	2.40	2.45	2.52	2.60	2.57	2.63	2.71	2.79	2.73	2.79	2.87	2.96	2.87	2.93	3.02	3.12	2.98	3.05	3.14	3.25	3.08	3.15	3.25	3.36
	Amps	8.6	8.8	9.1	9.4	9.3	9.5	9.8	10.2	10.1	10.4	10.7	11.1	10.8	11.1	11.5	11.9	11.5	11.8	12.2	12.7	12.2	12.6	13.0	13.5
	Hi PR	227	244	258	269	254	274	289	302	289	311	329	343	330	355	375	391	371	399	421	439	410	441	466	486
	Lo PR	103	109	119	127	108	115	126	134	113	120	131	139	118	126	137	146	124	132	144	153	128	136	149	159

IDB: Entering Indoor Dry Bulb Temperature
 High and low pressures are measured at the liquid and suction service valves.
 Shaded area reflects ACCA (TVA) conditions
 Amps = outdoor unit amps (comp.+fan)
 kW = Total system power

EXPANDED COOLING DATA — GSX130481A* / CA*F4860*6**

		Outdoor Ambient Temperature																							
		65°F				75°F				85°F				95°F				105°F				115°F			
IDB	Airflow	59	63	67	71	59	63	67	71	59	63	67	71	59	63	67	71	59	63	67	71	59	63	67	71
70	MBh	45.1	46.7	51.2	-	44.0	45.6	50.0	-	43.0	44.5	48.8	-	41.9	43.5	47.6	-	39.8	41.3	45.2	-	36.9	38.2	41.9	-
	S/T	0.75	0.63	0.44	-	0.78	0.65	0.45	-	0.80	0.67	0.46	-	0.83	0.69	0.48	-	0.86	0.72	0.50	-	0.86	0.72	0.50	-
	ΔT	17	15	11	-	18	15	12	-	18	15	12	-	18	15	12	-	17	15	11	-	16	14	11	-
	kW	3.16	3.22	3.33	-	3.40	3.48	3.59	-	3.62	3.70	3.83	-	3.82	3.90	4.03	-	3.98	4.07	4.21	-	4.12	4.22	4.36	-
	Amps	11.6	11.9	12.3	-	12.5	12.9	13.3	-	13.7	14.0	14.5	-	14.6	15.0	15.5	-	15.6	16.0	16.5	-	16.5	17.0	17.5	-
	Hi PR	236	253	268	-	264	284	300	-	301	323	342	-	342	368	389	-	385	414	438	-	425	458	484	-
	Lo PR	110	117	128	-	116	124	135	-	121	129	140	-	127	135	147	-	133	142	155	-	138	146	160	-
	MBh	43.8	45.4	49.7	-	42.7	44.3	48.5	-	41.7	43.2	47.4	-	40.7	42.2	46.2	-	38.7	40.1	43.9	-	35.8	37.1	40.7	-
	S/T	0.72	0.60	0.42	-	0.74	0.62	0.43	-	0.76	0.64	0.44	-	0.79	0.66	0.46	-	0.82	0.68	0.47	-	0.82	0.69	0.48	-
	ΔT	18	16	12	-	18	16	12	-	18	16	12	-	18	16	12	-	18	16	12	-	17	15	11	-
1400	kW	3.13	3.20	3.30	-	3.38	3.45	3.56	-	3.59	3.67	3.80	-	3.79	3.87	4.00	-	3.95	4.04	4.17	-	4.09	4.18	4.32	-
	Amps	11.5	11.8	12.1	-	12.4	12.7	13.2	-	13.5	13.9	14.3	-	14.5	14.8	15.4	-	15.4	15.8	16.4	-	16.4	16.8	17.4	-
	Hi PR	233	251	265	-	262	282	297	-	298	320	338	-	339	365	385	-	381	410	433	-	421	453	479	-
	Lo PR	109	116	127	-	115	123	134	-	120	127	139	-	126	134	146	-	132	140	153	-	136	145	158	-
	MBh	40.4	41.9	45.9	-	39.5	40.9	44.8	-	38.5	39.9	43.7	-	37.6	38.9	42.7	-	35.7	37.0	40.5	-	33.1	34.3	37.5	-
	S/T	0.69	0.58	0.40	-	0.72	0.60	0.42	-	0.74	0.61	0.43	-	0.76	0.63	0.44	-	0.79	0.66	0.46	-	0.80	0.66	0.46	-
	ΔT	18	16	12	-	19	16	12	-	19	16	12	-	19	16	12	-	18	16	12	-	17	15	11	-
	kW	3.05	3.12	3.22	-	3.29	3.37	3.47	-	3.50	3.58	3.70	-	3.69	3.77	3.90	-	3.85	3.93	4.07	-	3.98	4.07	4.21	-
	Amps	11.2	11.4	11.8	-	12.1	12.4	12.8	-	13.1	13.5	13.9	-	14.1	14.4	14.9	-	15.0	15.4	15.9	-	15.9	16.3	16.9	-
	Hi PR	226	243	257	-	254	273	288	-	289	311	328	-	329	354	374	-	370	398	420	-	409	440	464	-
	Lo PR	106	112	123	-	112	119	130	-	116	124	135	-	122	130	142	-	128	136	148	-	132	141	154	-
75	MBh	45.8	47.2	51.1	54.8	44.8	46.1	49.9	53.6	43.7	45.0	48.7	52.3	42.6	43.9	47.5	51.0	40.5	41.7	45.1	48.5	37.5	38.6	41.8	44.9
	S/T	0.86	0.77	0.58	0.37	0.89	0.79	0.60	0.39	0.91	0.81	0.62	0.40	0.94	0.84	0.64	0.41	0.97	0.87	0.66	0.42	0.98	0.88	0.67	0.43
	ΔT	20	18	15	10	20	19	15	11	20	19	15	11	20	19	15	11	20	19	15	11	19	17	14	10
	kW	3.18	3.25	3.36	3.47	3.43	3.51	3.62	3.75	3.65	3.74	3.86	3.99	3.85	3.94	4.07	4.21	4.02	4.11	4.25	4.39	4.16	4.26	4.40	4.55
	Amps	11.7	12.0	12.4	12.9	12.7	13.0	13.4	13.9	13.8	14.1	14.6	15.2	14.8	15.1	15.6	16.3	15.7	16.1	16.7	17.3	16.7	17.1	17.7	18.4
	Hi PR	238	256	270	282	267	287	303	316	304	327	345	360	346	372	393	410	389	419	442	461	430	463	488	509
	Lo PR	111	118	129	138	118	125	136	145	122	130	142	151	128	136	149	159	134	143	156	166	139	148	161	172
	MBh	44.5	45.8	49.6	53.2	43.5	44.8	48.4	52.0	42.4	43.7	47.3	50.8	41.4	42.6	46.1	49.5	39.3	40.5	43.8	47.0	36.4	37.5	40.6	43.6
	S/T	0.82	0.73	0.55	0.36	0.85	0.76	0.57	0.37	0.87	0.78	0.59	0.38	0.90	0.80	0.61	0.39	0.93	0.83	0.63	0.40	0.94	0.84	0.63	0.41
	ΔT	21	19	16	11	21	19	16	11	21	19	16	11	21	20	16	11	21	19	16	11	20	18	15	10
1600	kW	3.16	3.22	3.33	3.44	3.40	3.48	3.59	3.71	3.62	3.71	3.83	3.96	3.82	3.90	4.04	4.17	3.98	4.07	4.21	4.36	4.12	4.22	4.36	4.51
	Amps	11.6	11.9	12.3	12.7	12.5	12.9	13.3	13.8	13.7	14.0	14.5	15.0	14.6	15.0	15.5	16.1	15.6	16.0	16.5	17.2	16.5	17.0	17.5	18.2
	Hi PR	236	253	268	279	264	284	300	313	301	323	342	356	342	368	389	406	385	415	438	457	426	458	484	504
	Lo PR	110	117	128	136	116	124	135	144	121	129	140	150	127	135	148	157	133	142	155	165	138	146	160	170
	MBh	41.1	42.3	45.8	49.1	40.1	41.3	44.7	48.0	39.2	40.3	43.7	46.8	38.2	39.3	42.6	45.7	36.3	37.4	40.5	43.4	33.6	34.6	37.5	40.2
	S/T	0.79	0.70	0.53	0.34	0.82	0.73	0.55	0.36	0.84	0.75	0.57	0.36	0.86	0.77	0.58	0.38	0.90	0.80	0.61	0.39	0.90	0.81	0.61	0.39
	ΔT	21	20	16	11	22	20	16	11	22	20	16	11	22	20	16	11	21	20	16	11	20	18	15	10
	kW	3.08	3.15	3.25	3.35	3.32	3.39	3.50	3.62	3.53	3.61	3.73	3.86	3.72	3.80	3.93	4.07	3.88	3.97	4.10	4.24	4.02	4.11	4.25	4.40
	Amps	11.3	11.5	11.9	12.4	12.2	12.5	12.9	13.4	13.3	13.6	14.1	14.6	14.2	14.6	15.1	15.6	15.1	15.5	16.1	16.7	16.1	16.5	17.0	17.7
	Hi PR	228	246	260	271	256	276	291	304	292	314	331	346	332	357	377	394	374	402	425	443	413	444	469	489
	Lo PR	107	114	124	132	113	120	131	140	117	125	136	145	123	131	143	152	129	137	150	160	134	142	155	165

IDB: Entering Indoor Dry Bulb Temperature
 High and low pressures are measured at the liquid and suction service valves.
 Shaded area reflects ACCA (TVA) conditions
 Amps = outdoor unit amps (comp.+fan)
 kW = Total system power

EXPANDED COOLING DATA — GSX130481B* / CA*F4860*6B*

		Outdoor Ambient Temperature																							
		65°F				75°F				85°F				95°F				105°F				115°F			
IDB	Airflow	59	63	67	71	59	63	67	71	59	63	67	71	59	63	67	71	59	63	67	71	59	63	67	71
70	MBh	40.4	41.9	45.9	-	39.5	40.9	44.8	-	38.5	39.9	43.7	-	37.6	38.9	42.7	-	35.7	37.0	40.5	-	33.1	34.3	37.5	-
	S/T	0.71	0.59	0.41	-	0.73	0.61	0.42	-	0.75	0.63	0.44	-	0.78	0.65	0.45	-	0.81	0.67	0.47	-	0.81	0.68	0.47	-
	ΔT	19	16	12	-	19	16	12	-	19	16	13	-	19	17	13	-	19	16	12	-	18	15	12	-
	kW	3.17	3.23	3.32	-	3.39	3.46	3.56	-	3.59	3.66	3.77	-	3.77	3.84	3.96	-	3.91	4.00	4.12	-	4.04	4.13	4.26	-
	Amps	11.6	11.9	12.3	-	12.6	12.9	13.3	-	13.7	14.0	14.5	-	14.6	15.0	15.5	-	15.5	15.9	16.5	-	16.5	16.9	17.4	-
	Hi PR	215	231	244	-	241	259	274	-	274	295	311	-	312	336	354	-	351	377	399	-	388	417	440	-
	Lo PR	104	111	121	-	110	117	128	-	115	122	133	-	120	128	140	-	126	134	146	-	130	139	151	-
	MBh	43.8	45.4	49.7	-	42.7	44.3	48.5	-	41.7	43.2	47.4	-	40.7	42.2	46.2	-	38.7	40.1	43.9	-	35.8	37.1	40.7	-
	S/T	0.73	0.61	0.43	-	0.76	0.64	0.44	-	0.78	0.65	0.45	-	0.81	0.67	0.47	-	0.84	0.70	0.48	-	0.84	0.70	0.49	-
	ΔT	18	16	12	-	19	16	12	-	19	16	12	-	19	16	12	-	19	16	12	-	17	15	11	-
1600	kW	3.24	3.30	3.40	-	3.47	3.54	3.65	-	3.67	3.75	3.87	-	3.86	3.94	4.06	-	4.01	4.09	4.22	-	4.14	4.23	4.36	-
	Amps	12.0	12.3	12.7	-	12.9	13.2	13.7	-	14.1	14.4	14.9	-	15.0	15.4	15.9	-	16.0	16.4	16.9	-	16.9	17.4	17.9	-
	Hi PR	221	238	251	-	248	267	282	-	282	304	321	-	321	346	365	-	362	389	411	-	400	430	454	-
	Lo PR	108	114	125	-	114	121	132	-	118	126	137	-	124	132	144	-	130	138	151	-	134	143	156	-
	MBh	45.1	46.7	51.2	-	44.0	45.6	50.0	-	43.0	44.5	48.8	-	41.9	43.5	47.6	-	39.8	41.3	45.2	-	36.9	38.2	41.9	-
	S/T	0.77	0.64	0.45	-	0.80	0.67	0.46	-	0.82	0.68	0.47	-	0.85	0.71	0.49	-	0.88	0.73	0.51	-	0.88	0.74	0.51	-
	ΔT	18	15	12	-	18	16	12	-	18	16	12	-	18	16	12	-	18	15	12	-	17	14	11	-
	kW	3.26	3.33	3.42	-	3.50	3.57	3.67	-	3.70	3.78	3.90	-	3.89	3.97	4.09	-	4.04	4.13	4.26	-	4.18	4.26	4.40	-
	Amps	12.1	12.4	12.8	-	13.0	13.4	13.8	-	14.2	14.5	15.0	-	15.2	15.5	16.0	-	16.1	16.5	17.1	-	17.1	17.5	18.1	-
	Hi PR	223	240	254	-	251	270	285	-	285	307	324	-	325	349	369	-	365	393	415	-	404	434	459	-
	Lo PR	109	116	126	-	115	122	133	-	119	127	139	-	125	133	146	-	131	140	152	-	136	144	158	-

75	MBh	41.1	42.3	45.8	49.1	40.1	41.3	44.7	48.0	39.2	40.3	43.7	46.8	38.2	39.3	42.6	45.7	36.3	37.4	40.5	43.4	33.6	34.6	37.5	40.2
	S/T	0.81	0.72	0.55	0.35	0.83	0.75	0.56	0.36	0.86	0.77	0.58	0.37	0.88	0.79	0.60	0.38	0.92	0.82	0.62	0.40	0.92	0.83	0.63	0.40
	ΔT	22	20	16	11	22	20	17	11	22	20	17	11	22	20	17	12	22	20	16	11	20	19	15	11
	kW	3.19	3.25	3.35	3.45	3.42	3.49	3.59	3.70	3.62	3.69	3.80	3.92	3.79	3.87	3.99	4.12	3.95	4.03	4.15	4.29	4.08	4.16	4.29	4.43
	Amps	11.7	12.0	12.4	12.9	12.7	13.0	13.4	13.9	13.8	14.1	14.6	15.1	14.7	15.1	15.6	16.2	15.7	16.1	16.6	17.2	16.6	17.0	17.6	18.3
	Hi PR	217	233	246	257	243	262	276	288	277	298	314	328	315	339	358	373	354	381	403	420	391	421	445	464
	Lo PR	105	112	122	130	111	118	129	138	116	123	134	143	122	129	141	150	127	136	148	158	132	140	153	163
	MBh	44.5	45.8	49.6	53.2	43.5	44.8	48.4	52.0	42.4	43.7	47.3	50.8	41.4	42.6	46.1	49.5	39.3	40.5	43.8	47.0	36.4	37.5	40.6	43.6
	S/T	0.84	0.75	0.57	0.36	0.87	0.77	0.59	0.38	0.89	0.79	0.60	0.39	0.92	0.82	0.62	0.40	0.95	0.85	0.64	0.41	0.96	0.86	0.65	0.42
	ΔT	21	20	16	11	22	20	16	11	22	20	16	11	22	20	16	11	21	20	16	11	20	18	15	10
1600	kW	3.26	3.33	3.42	3.53	3.50	3.57	3.68	3.79	3.70	3.78	3.90	4.02	3.89	3.97	4.09	4.22	4.04	4.13	4.26	4.39	4.18	4.26	4.40	4.54
	Amps	12.1	12.4	12.8	13.2	13.1	13.4	13.8	14.3	14.2	14.5	15.0	15.6	15.2	15.5	16.1	16.7	16.1	16.5	17.1	17.7	17.1	17.5	18.1	18.8
	Hi PR	223	240	254	265	251	270	285	297	285	307	324	338	325	349	369	385	365	393	415	433	404	434	459	478
	Lo PR	109	116	126	134	115	122	133	142	119	127	139	148	125	133	146	155	131	140	153	162	136	145	158	168
	MBh	45.8	47.2	51.1	54.8	44.8	46.1	49.9	53.6	43.7	45.0	48.7	52.3	42.6	43.9	47.5	51.0	40.5	41.7	45.1	48.5	37.5	38.6	41.8	44.9
	S/T	0.88	0.78	0.59	0.38	0.91	0.81	0.61	0.40	0.93	0.83	0.63	0.41	0.96	0.86	0.65	0.42	1.00	0.89	0.67	0.43	1.00	0.90	0.68	0.44
	ΔT	21	19	15	11	21	19	16	11	21	19	16	11	21	19	16	11	21	19	16	11	19	18	15	10
	kW	3.29	3.35	3.45	3.55	3.52	3.59	3.70	3.82	3.73	3.81	3.93	4.05	3.92	4.00	4.12	4.26	4.07	4.16	4.29	4.43	4.21	4.30	4.44	4.58
	Amps	12.2	12.5	12.9	13.4	13.2	13.5	13.9	14.5	14.3	14.7	15.1	15.7	15.3	15.7	16.2	16.8	16.3	16.7	17.2	17.9	17.3	17.7	18.3	19.0
	Hi PR	226	243	256	267	253	272	288	300	288	310	327	341	328	353	373	389	369	397	419	437	408	439	463	483
	Lo PR	110	117	127	136	116	123	135	143	120	128	140	149	127	135	147	157	133	141	154	164	137	146	159	170

IDB: Entering Indoor Dry Bulb Temperature
 High and low pressures are measured at the liquid and suction service valves.
 Shaded area reflects ACCA (TVA) conditions
 Amps = outdoor unit amps (comp.+fan)
 kW = Total system power

EXPANDED COOLING DATA — GSX130481B* / CA*F4860*6B* (CONT.)

		Outdoor Ambient Temperature																							
		65°F				75°F				85°F				95°F				105°F				115°F			
IDB	Airflow	59	63	67	71	59	63	67	71	59	63	67	71	59	63	67	71	59	63	67	71	59	63	67	71
80	MBh	41.8	42.7	45.6	48.8	40.8	41.7	44.6	47.7	39.9	40.7	43.5	46.5	38.9	39.7	42.5	45.4	36.9	37.8	40.3	43.1	34.2	35.0	37.4	39.9
	S/T	0.88	0.83	0.67	0.50	0.92	0.86	0.70	0.52	0.94	0.88	0.72	0.54	0.97	0.91	0.74	0.55	1.01	0.94	0.77	0.57	1.01	0.95	0.77	0.58
	ΔT	24	23	20	16	25	24	20	16	25	24	20	16	25	24	21	16	24	23	20	16	23	22	19	15
	kW	3.21	3.28	3.37	3.47	3.44	3.51	3.62	3.73	3.65	3.72	3.83	3.95	3.82	3.90	4.03	4.15	3.98	4.06	4.19	4.32	4.11	4.20	4.33	4.47
	Amps	11.9	12.1	12.5	13.0	12.8	13.1	13.6	14.1	13.9	14.3	14.7	15.3	14.9	15.2	15.8	16.3	15.8	16.2	16.8	17.4	16.8	17.2	17.8	18.5
	Hi PR	219	236	249	259	246	264	279	291	279	301	317	331	318	342	362	377	358	385	407	424	395	426	449	469
	Lo PR	106	113	124	132	112	120	131	139	117	124	136	145	123	131	143	152	129	137	149	159	133	142	155	165
	MBh	45.3	46.3	49.5	52.9	44.2	45.2	48.3	51.6	43.2	44.1	47.2	50.4	42.1	43.1	46.0	49.2	40.0	40.9	43.7	46.7	37.1	37.9	40.5	43.3
	S/T	0.92	0.86	0.70	0.52	0.95	0.89	0.72	0.54	0.97	0.91	0.74	0.56	1.00	0.94	0.77	0.57	1.00	0.98	0.80	0.60	1.00	0.99	0.80	0.60
	ΔT	24	23	20	16	24	23	20	16	24	23	20	16	24	23	20	16	23	23	20	16	21	21	19	15
	kW	3.29	3.35	3.45	3.56	3.52	3.59	3.70	3.82	3.73	3.81	3.93	4.05	3.92	4.00	4.12	4.26	4.07	4.16	4.29	4.43	4.21	4.30	4.44	4.58
1600	Amps	12.2	12.5	12.9	13.4	13.2	13.5	13.9	14.5	14.3	14.7	15.2	15.7	15.3	15.7	16.2	16.8	16.3	16.7	17.3	17.9	17.3	17.7	18.3	19.0
	Hi PR	226	243	256	267	253	272	288	300	288	310	327	341	328	353	373	389	369	397	419	437	408	439	463	483
	Lo PR	110	117	127	136	116	123	135	143	120	128	140	149	127	135	147	157	133	141	154	164	137	146	159	170
	MBh	46.7	47.7	50.9	54.4	45.6	46.6	49.7	53.2	44.5	45.5	48.6	51.9	43.4	44.3	47.4	50.6	41.2	42.1	45.0	48.1	38.2	39.0	41.7	44.6
	S/T	0.96	0.90	0.73	0.55	1.00	0.93	0.76	0.57	1.00	0.96	0.78	0.58	1.00	1.00	0.80	0.60	1.00	1.00	0.83	0.62	1.00	1.00	0.84	0.63
	ΔT	23	22	19	15	23	22	19	15	23	22	19	15	22	23	19	16	21	22	19	15	20	20	18	14
	kW	3.31	3.38	3.48	3.58	3.55	3.62	3.73	3.85	3.76	3.84	3.96	4.08	3.95	4.03	4.16	4.29	4.11	4.19	4.33	4.47	4.24	4.33	4.47	4.62
	Amps	12.3	12.6	13.0	13.5	13.3	13.6	14.1	14.6	14.4	14.8	15.3	15.9	15.4	15.8	16.4	17.0	16.4	16.8	17.4	18.1	17.4	17.9	18.5	19.2
	Hi PR	228	245	259	270	256	275	291	303	291	313	331	345	331	356	376	393	373	401	423	442	412	443	468	488
	Lo PR	111	118	129	137	117	125	136	145	122	129	141	151	128	136	148	158	134	143	156	166	139	147	161	171
85	MBh	42.5	43.4	45.4	48.5	41.5	42.4	44.4	47.3	40.6	41.3	43.3	46.2	39.6	40.3	42.2	45.1	37.6	38.3	40.1	42.8	34.8	35.5	37.2	39.7
	S/T	0.93	0.89	0.81	0.65	0.96	0.93	0.84	0.68	0.98	0.95	0.86	0.70	1.00	0.98	0.88	0.72	1.00	1.00	0.92	0.74	1.00	1.00	0.93	0.75
	ΔT	26	25	24	21	26	26	24	21	26	26	24	21	26	26	25	21	25	25	24	21	23	23	23	20
	kW	3.24	3.30	3.40	3.50	3.47	3.54	3.65	3.76	3.67	3.75	3.86	3.99	3.85	3.94	4.06	4.19	4.01	4.09	4.22	4.36	4.14	4.23	4.36	4.50
	Amps	12.0	12.2	12.6	13.1	12.9	13.2	13.7	14.2	14.0	14.4	14.9	15.4	15.0	15.4	15.9	16.5	16.0	16.4	16.9	17.6	16.9	17.4	17.9	18.6
	Hi PR	221	238	251	262	248	267	282	294	282	304	321	334	321	346	365	381	361	389	411	428	399	430	454	473
	Lo PR	108	114	125	133	114	121	132	140	118	126	137	146	124	132	144	153	130	138	151	161	134	143	156	166
	MBh	46.1	47.0	49.2	52.5	45.0	45.9	48.1	51.3	43.9	44.8	46.9	50.1	42.9	43.7	45.8	48.8	40.7	41.5	43.5	46.4	37.7	38.5	40.3	43.0
	S/T	0.96	0.93	0.84	0.68	1.00	0.96	0.87	0.70	1.00	0.98	0.89	0.72	1.00	1.00	0.92	0.74	1.00	1.00	0.95	0.77	1.00	1.00	0.96	0.78
	ΔT	25	25	24	20	26	25	24	21	25	25	24	21	25	25	24	21	23	24	24	21	22	22	22	19
	kW	3.31	3.38	3.48	3.58	3.55	3.62	3.73	3.85	3.76	3.84	3.96	4.08	3.95	4.03	4.16	4.29	4.11	4.19	4.33	4.47	4.24	4.33	4.47	4.62
	Amps	12.3	12.6	13.0	13.5	13.3	13.6	14.1	14.6	14.4	14.8	15.3	15.9	15.4	15.8	16.4	17.0	16.4	16.8	17.4	18.1	17.4	17.9	18.5	19.2
	Hi PR	228	245	259	270	256	275	291	303	291	313	331	345	331	356	376	393	373	401	423	442	412	443	468	488
	Lo PR	111	118	129	137	117	125	136	145	122	129	141	151	128	136	148	158	134	143	156	166	139	147	161	171
1800	MBh	47.5	48.4	50.7	54.1	46.4	47.3	49.5	52.8	45.3	46.1	48.3	51.6	44.2	45.0	47.1	50.3	42.0	42.8	44.8	47.8	38.9	39.6	41.5	44.3
	S/T	1.00	0.97	0.88	0.71	1.00	1.00	0.91	0.74	1.00	1.00	0.93	0.76	1.00	1.00	0.96	0.78	1.00	1.00	1.00	0.81	1.00	1.00	1.00	0.82
	ΔT	24	24	23	20	24	24	23	20	23	24	23	20	23	23	23	20	21	22	23	20	20	20	21	18
	kW	3.34	3.40	3.50	3.61	3.58	3.65	3.76	3.88	3.79	3.87	3.99	4.11	3.98	4.06	4.19	4.32	4.14	4.23	4.36	4.50	4.28	4.37	4.51	4.65
	Amps	12.4	12.7	13.1	13.6	13.4	13.7	14.2	14.7	14.6	14.9	15.4	16.0	15.6	16.0	16.5	17.1	16.6	17.0	17.6	18.2	17.6	18.0	18.6	19.3
	Hi PR	230	248	262	273	258	278	294	306	294	316	334	348	335	360	380	397	376	405	428	446	416	448	473	493
	Lo PR	112	119	130	138	118	126	137	146	123	131	143	152	129	137	150	160	135	144	157	167	140	149	163	173
		Shaded area reflects ARI conditions																							
		Amps = outdoor unit amps (comp.+fan)																							
		kW = Total system power																							

ARI PERFORMANCE RATINGS

Outdoor Unit	Indoor Units		Cooling Capacity (BTU/h)				ARI #
	Indoor Coil & Blower	Furnace	Total	Sensible	SEER ¹	EER ²	
GSX13 0181A*	ACNF18XX16A*		17,200	12,400	13.00	11.00	3001408
	ADPF182416A*		18,000	13,000	13.00	11.00	1332751
	ADPF182416B*		18,000	13,000	13.00	11.00	1443913
	AEPF183016A*		18,000	13,000	14.00	11.60	1332752
	AEPF183016B*		18,000	13,000	14.00	11.60	1487018
	AR*F182416A*		18,000	13,000	13.00	11.00	1333014
	AR*F182416B*		18,000	13,000	13.00	11.00	1443931
	AT*F182416A*		18,000	13,000	13.00	11.00	1483520
	AWUF18XX16A*		17,400	12,500	13.00	11.00	3001409
	CA*F1824*6A*	G*E80704B**	18,000	13,000	14.00	11.60	1332753
	CA*F1824*6A*	G*V80704B**	18,000	13,000	14.00	11.60	1332754
	CA*F1824*6A*	G*V90704C**	18,000	13,000	14.00	11.60	1332755
	CA*F1824*6A*	G*V950453B**	18,000	13,000	14.00	11.60	1332756
	CA*F1824*6A*+EEP		18,000	13,000	13.00	11.00	1332757
	CA*F1824*6A*+MBE1200**-1		18,400	13,200	14.00	11.60	1332758
	CA*F1824*6B*	G*E80704B**	18,000	13,000	14.00	11.60	1333161
	CA*F1824*6B*	G*V80704B**	18,000	13,000	14.00	11.60	1333162
	CA*F1824*6B*	G*V90704C**	18,000	13,000	14.00	11.60	1333163
	CA*F1824*6B*	G*V950453B**	18,000	13,000	14.00	11.60	1333164
	CA*F1824*6B*+EEP		18,000	13,000	13.00	11.00	1333165
	CA*F1824*6B*+MBE1200**-1		18,400	13,200	14.00	11.60	1333152
	CA*F1824*6C*	G*E80704B**	18,000	13,000	14.00	11.60	1386209
	CA*F1824*6C*	G*V80704B**	18,000	13,000	14.00	11.60	1386210
	CA*F1824*6C*	G*V90704C**	18,000	13,000	14.00	11.60	1386211
	CA*F1824*6C*	G*V950453B**	18,000	13,000	14.00	11.60	1386212
	CA*F1824*6C*+EEP		18,000	13,000	13.00	11.00	1401019
	CA*F1824*6C*+EEP		18,000	13,000	13.00	11.00	1401043
	CA*F1824*6C*+MBE1200**-1		18,400	13,200	14.00	11.60	1386221
	CHPF1824A6A*+EEP		18,000	13,000	13.00	11.00	1333006
	CHPF1824A6B*+EEP		18,000	13,000	13.00	11.00	1332759
	CHPF2430B6A*	G*E80704B**	18,400	13,200	14.00	11.60	1332760
	CHPF2430B6A*	G*V80704B**	18,400	13,200	14.00	11.60	1332761
	CHPF2430B6A*	G*V950453B**	18,400	13,200	14.00	11.60	1332762
	CHPF2430B6A*+MBE1200**-1		18,400	13,200	14.00	11.60	1333015
	CHPF2430B6B*	G*E80704B**	18,400	13,200	14.00	11.60	1332763
	CHPF2430B6B*	G*V80704B**	18,400	13,200	14.00	11.60	1332764
	CHPF2430B6B*	G*V950453B**	18,400	13,200	14.00	11.60	1332765
	CHPF2430B6B*+MBE1200**-1A*		18,400	13,200	14.00	11.60	1333153
	CSCF1824N6A*	G*E80704B**	18,000	13,000	14.00	11.60	1332766
	CSCF1824N6A*	G*V80704B**	18,000	13,000	14.00	11.60	1332767
	CSCF1824N6A*	G*V90704C**	18,000	13,000	14.00	11.60	1332768

¹ Seasonal Energy Efficiency Ratio; Certified per ARI 210/240 @ 80°F/ 67°F/ 95°F

² Energy Efficiency Ratio @ 80°F/ 67°F/ 95°F

ARI PERFORMANCE RATINGS (CONT.)

Outdoor Unit	Indoor Units		Cooling Capacity (BTU/h)				ARI #
	Indoor Coil & Blower	Furnace	Total	Sensible	SEER ¹	EER ²	
GSX13 0181A* (cont.)	CSCF1824N6A*	G*V950453B**	18,000	13,000	14.00	11.60	1332769
	CSCF1824N6A*+EEP		18,000	13,000	13.00	11.00	1333007
	CSCF1824N6B*	G*E80704B**	18,000	13,000	14.00	11.60	1333016
	CSCF1824N6B*	G*V80704B**	18,000	13,000	14.00	11.60	1333017
	CSCF1824N6B*	G*V90704C**	18,000	13,000	14.00	11.60	1333018
	CSCF1824N6B*	G*V950453B**	18,000	13,000	14.00	11.60	1333019
	CSCF1824N6B*+EEP		18,000	13,000	13.00	11.00	1333020
	CT*F1824*6A*	G*E80704B**	18,000	13,000	14.00	11.60	1449780
	CT*F1824*6A*	G*V80704B**	18,000	13,000	14.00	11.60	1449781
	CT*F1824*6A*	G*V90704C**	18,000	13,000	14.00	11.60	1449782
	CT*F1824*6A*	G*V950453B**	18,000	13,000	14.00	11.60	1449783
	CT*F1824*6A*+EEP		18,000	13,000	13.00	11.00	1449784
	CT*F1824*6A*+MBE1200**-1		18,400	13,200	14.00	11.60	1449785
GSX13 0181B*	ACNF18XX16A*		17,200	12,400	13.0	11.0	3080551
	ADPF182416B*		18,000	13,000	13.0	11.0	3080552
	AEPF183016C*		18,000	13,000	14.0	11.6	3080553
	AR*F182416B*		18,000	13,000	13.0	11.0	3080554
	ASPF183016B*		19,000	13,700	14.0	12.2	3080555
	AT*F182416A*		18,000	13,000	13.0	11.0	3080556
	AWUF18XX16A*		17,400	12,500	13.0	11.0	3080557
	CA*F1824*6B*	G*V950453B**	18,000	13,000	14.0	11.6	3080558
	CA*F1824*6B*	G*V80704B**	18,000	13,000	14.0	11.6	3080559
	CA*F1824*6B*	G*V90704C**	18,000	13,000	14.0	11.6	3080560
	CA*F1824*6B*	G*E80704B**	18,000	13,000	14.0	11.6	3080561
	CA*F1824*6B*+EEP		18,000	13,000	13.0	11.0	3080562
	CA*F1824*6B*+MBE1200**-1		18,400	13,200	14.0	11.6	3080563
	CHPF1824A6B*+EEP		18,000	13,000	13.0	11.0	3080564
	CHPF2430B6B*	G*V80704B**	18,400	13,200	14.0	11.6	3080566
	CHPF2430B6B*	G*E80704B**	18,400	13,200	14.0	11.6	3080567
	CHPF2430B6B*	G*V950453B**	18,400	13,200	14.0	11.6	3080568
	CHPF2430B6B*+EEP		18,000	13,000	13.0	11.0	3080565
	CHPF2430B6B*+MBE1200**-1A*		18,400	13,200	14.0	11.6	3080569
	CSCF1824N6B*	G*V950453B**	18,000	13,000	14.0	11.6	3080570
	CSCF1824N6B*	G*V90704C**	18,000	13,000	14.0	11.6	3080571
	CSCF1824N6B*	G*V80704B**	18,000	13,000	14.0	11.6	3080572
	CSCF1824N6B*	G*E80704B**	18,000	13,000	14.0	11.6	3080573
	CSCF1824N6B*+EEP		18,000	13,000	13.0	11.0	3080574
	CT*F1824*6A*	G*E80704B**	18,000	13,000	14.0	11.6	3080575
	CT*F1824*6A*	G*V950453B**	18,000	13,000	14.0	11.6	3080576
	CT*F1824*6A*	G*V80704B**	18,000	13,000	14.0	11.6	3080577
	CT*F1824*6A*+EEP		18,000	13,000	13.0	11.0	3080578
	CT*F1824*6A*+MBE1200**-1		18,400	13,200	14.0	11.6	3080579

See Notes on Page 29.

ARI PERFORMANCE RATINGS (CONT.)

Outdoor Unit	Indoor Units		Cooling Capacity (BTU/h)				ARI #
	Indoor Coil & Blower	Furnace	Total	Sensible	SEER ¹	EER ²	
GSX13 0241A*	ACNF24XX16A*		23,000	16,800	13.00	11.00	3001412
	ADPF182416A*		23,000	16,800	13.00	11.00	1332770
	ADPF182416B*		23,000	16,800	13.00	11.00	1443914
	AEPF183016A*		23,400	17,100	14.00	11.60	1332771
	AEPF183016B*		23,400	17,100	14.00	11.60	1487019
	AR*F182416A*		23,000	16,800	13.00	11.00	1333021
	AR*F182416B*		23,000	16,800	13.00	11.00	1443932
	ASPF183016A*		23,400	17,100	14.00	11.60	1333022
	ASPF183016B*		23,400	17,100	14.00	11.60	1492494
	AT*F182416A*		23,000	16,800	13.00	11.00	1483521
	AWUF24XX16A*		23,000	16,800	13.00	11.00	3001410
	AWUF30XX16A*		23,200	16,900	13.00	11.00	3001411
	CA*F1824*6A*	G*E80704B**	23,000	16,800	14.00	11.60	1332772
	CA*F1824*6A*	G*V80704B**	23,000	16,800	14.00	11.60	1332773
	CA*F1824*6A*	G*V950453B**	23,000	16,800	14.00	11.60	1332774
	CA*F1824*6A*	G*V950704C**	23,000	16,800	14.00	11.60	1332775
	CA*F1824*6A*+EEP		23,000	16,800	13.00	11.00	1332776
	CA*F1824*6A*+MBE1200**-1		23,000	16,800	14.00	11.60	1332777
	CA*F1824*6B*	G*E80704B**	23,000	16,800	14.00	11.60	1333166
	CA*F1824*6B*	G*V80704B**	23,000	16,800	14.00	11.60	1333167
	CA*F1824*6B*	G*V950453B**	23,000	16,800	14.00	11.60	1333168
	CA*F1824*6B*	G*V950704C**	23,000	16,800	14.00	11.60	1333169
	CA*F1824*6B*+EEP		23,000	16,800	13.00	11.00	1333170
	CA*F1824*6B*+MBE1200**-1		23,000	16,800	14.00	11.60	1333154
	CA*F1824*6C*	G*E80704B**	23,000	16,800	14.00	11.60	1386213
	CA*F1824*6C*	G*V80704B**	23,000	16,800	14.00	11.60	1386214
	CA*F1824*6C*	G*V950453B**	23,000	16,800	14.00	11.60	1386215
	CA*F1824*6C*	G*V950704C**	23,000	16,800	14.00	11.60	1386216
	CA*F1824*6C*+EEP		23,000	16,800	13.00	11.00	1401044
	CA*F1824*6C*+EEP		23,000	16,800	13.00	11.00	1401020
	CA*F1824*6C*+MBE1200**-1		23,000	16,800	14.00	11.60	1386222
	CHPF1824A6A*+EEP		23,000	16,800	13.00	11.00	1333008
	CHPF1824A6B*+EEP		23,000	16,800	13.00	11.00	1332778
	CHPF2430B6A*	G*E80704B**	23,400	17,100	14.00	11.60	1332779
	CHPF2430B6A*	G*V80704B**	23,400	17,100	14.00	11.60	1332780
	CHPF2430B6A*	G*V950453B**	23,400	17,100	14.00	11.60	1332781
	CHPF2430B6A*+MBE1200**-1		23,400	17,100	14.00	11.60	1333023
	CHPF2430B6B*	G*E80704B**	23,400	17,100	14.00	11.60	1332782
	CHPF2430B6B*	G*V80704B**	23,400	17,100	14.00	11.60	1332783
	CHPF2430B6B*	G*V950453B**	23,400	17,100	14.00	11.60	1332784
	CHPF2430B6B*+MBE1200**-1A*		23,400	17,100	14.00	11.60	1333155

See Notes on Page 29.

ARI PERFORMANCE RATINGS (CONT.)

Outdoor Unit	Indoor Units		Cooling Capacity (BTU/h)				ARI #
	Indoor Coil & Blower	Furnace	Total	Sensible	SEER ¹	EER ²	
GSX13 0241A* (cont.)	CSCF1824N6A*	G*E80704B**	23,000	16,800	13.00	11.00	1332785
	CSCF1824N6A*	G*V80704B**	23,000	16,800	13.00	11.00	1332786
	CSCF1824N6A*	G*V90704C**	23,000	16,800	14.00	11.60	1332787
	CSCF1824N6A*	G*V950453B**	23,000	16,800	14.00	11.60	1332788
	CSCF1824N6A*+EEP		23,000	16,800	13.00	11.00	1333009
	CSCF1824N6B*	G*E80704B**	23,000	16,800	13.00	11.00	1333024
	CSCF1824N6B*	G*V80704B**	23,000	16,800	13.00	11.00	1333025
	CSCF1824N6B*	G*V90704C**	23,000	16,800	14.00	11.60	1333026
	CSCF1824N6B*	G*V950453B**	23,000	16,800	14.00	11.60	1333027
	CSCF1824N6B*+EEP		23,000	16,800	13.00	11.00	1333028
	CT*F1824*6A*	G*E80704B**	23,000	16,800	14.00	11.60	1449786
	CT*F1824*6A*	G*V80704B**	23,000	16,800	14.00	11.60	1449787
	CT*F1824*6A*	G*V950453B**	23,000	16,800	14.00	11.60	1449788
	CT*F1824*6A*	G*V950704C**	23,000	16,800	14.00	11.60	1449789
	CT*F1824*6A*+EEP		23,000	16,800	13.00	11.00	1449790
	CT*F1824*6A*+MBE1200**-1		23,000	16,800	14.00	11.60	1449791
GSX13 0241B*	ACNF24XX16A*		23,000	16,800	13.0	11.0	3080580
	ADPF182416B*		23,000	16,800	13.0	11.0	3080581
	AEPF183016C*		23,400	17,100	14.0	11.6	3080582
	AR*F182416B*		23,000	16,800	13.0	11.0	3080583
	ASPF183016B*		23,400	17,100	14.0	11.6	3080584
	AT*F182416A*		23,000	16,800	13.0	11.0	3080585
	AWUF24XX16A*		23,000	16,800	13.0	11.0	3080586
	AWUF30XX16A*		23,200	16,900	13.0	11.0	3080587
	CA*F1824*6B*	G*V950453B**	23,000	16,800	14.0	11.6	3080588
	CA*F1824*6B*	G*E80704B**	23,000	16,800	14.0	11.6	3080589
	CA*F1824*6B*	G*V950704C**	23,000	16,800	14.0	11.6	3080590
	CA*F1824*6B*	G*V80704B**	23,000	16,800	14.0	11.6	3080591
	CA*F1824*6B*+EEP		23,000	16,800	13.0	11.0	3080592
	CA*F1824*6B*+MBE1200**-1		23,000	16,800	14.0	11.6	3080593
	CHPF1824A6B*+EEP		23,000	16,800	13.0	11.0	3080594
	CHPF2430B6B*	G*E80704B**	23,400	17,100	14.0	11.6	3080595
	CHPF2430B6B*	G*V950453B**	23,400	17,100	14.0	11.6	3080596
	CHPF2430B6B*	G*V80704B**	23,400	17,100	14.0	11.6	3080597
	CHPF2430B6B*+EEP		23,000	16,800	13.0	11.0	3080610
	CHPF2430B6B*+MBE1200**-1A*		23,400	17,100	14.0	11.6	3080598

¹ Seasonal Energy Efficiency Ratio; Certified per ARI 210/240 @ 80°F/ 67°F/ 95°F

² Energy Efficiency Ratio @ 80°F/ 67°F/ 95°F

Notes

- Always check the S&R plate for electrical data on the unit being installed.
- When matching the outdoor unit to the indoor unit, use the piston supplied with the outdoor unit or that specified on the piston kit chart supplied with the indoor unit.
- EEP - Order from Service Dept. Part No. B13707-38 or new Solid State Board B13707-35S. Part No. B13707-38 is not interchangeable with B13707-35S. The Goodman Gas Furnace contains the EEP cooling time delay

ARI PERFORMANCE RATINGS (CONT.)

Outdoor Unit	Indoor Units		Cooling Capacity (BTU/h)				ARI #
	Indoor Coil & Blower	Furnace	Total	Sensible	SEER ¹	EER ²	
GSX13 0241B* (cont.)	CSCF1824N6B*	G*V80704B**	23,000	16,800	13.0	11.0	3080599
	CSCF1824N6B*	G*V90704C**	23,000	16,800	14.0	11.6	3080600
	CSCF1824N6B*	G*E80704B**	23,000	16,800	13.0	11.0	3080601
	CSCF1824N6B*	G*V950453B**	23,000	16,800	14.0	11.6	3080602
	CSCF1824N6B*+EEP		23,000	16,800	13.0	11.0	3080603
	CT*F1824*6A*	G*E80704B**	23,000	16,800	14.0	11.6	3080604
	CT*F1824*6A*	G*V80704B**	23,000	16,800	14.0	11.6	3080605
	CT*F1824*6A*	G*V950704C**	23,000	16,800	14.0	11.6	3080606
	CT*F1824*6A*	G*V950453B**	23,000	16,800	14.0	11.6	3080607
	CT*F1824*6A*+EEP		23,000	16,800	13.0	11.0	3080608
	CT*F1824*6A*+MBE1200**-1		23,000	16,800	14.0	11.6	3080609
GSX13 0301A*	ACNF30XX16A*		27,600	20,400	13.00	11.00	3001413
	ADPF304216A*		28,400	21,000	13.00	11.00	1332917
	ADPF304216B*		28,400	21,000	13.00	11.00	1492495
	AEPF183016A*		28,400	21,000	14.00	11.60	1332918
	AEPF183016B*		28,400	21,000	14.00	11.60	1487020
	AR*F182416A*+TXV		27,400	20,300	13.00	11.00	1411921
	AR*F182416B*+TXV		27,400	20,300	13.00	11.00	1443947
	AR*F303016A*		28,400	21,000	13.00	11.00	1333029
	AR*F303016B*		28,400	21,000	13.00	11.00	1492496
	ASPF183016A*		28,400	21,000	14.00	11.60	1333030
	ASPF183016B*		28,400	21,000	14.00	11.60	1492497
	AT*F182416A*+TXV		27,400	20,300	13.00	11.00	1483487
	AT*F303016A*		28,400	21,000	13.00	11.00	1483511
	AWUF30XX16A*		27,600	20,400	13.00	11.00	3001414
	AWUF36XX16A*		27,800	20,600	13.00	11.00	3001415
	AWUF37XX16A*		28,000	20,700	13.00	11.00	3001416
	CA*F3030*6A*	G*E80704B**	28,400	21,000	13.50	11.30	1332919
	CA*F3030*6A*	G*V80704B**	28,400	21,000	13.50	11.30	1332920
	CA*F3030*6A*	G*V90704C**	28,400	21,000	14.00	11.60	1332921
	CA*F3030*6A*	G*V950453B**	28,400	21,000	14.00	11.60	1332922
	CA*F3030*6A*	G*V950704C**	28,400	21,000	14.00	11.60	1332923
	CA*F3030*6A*+EEP		28,400	21,000	13.00	11.00	1333010
	CA*F3030*6B*	G*E80704B**	28,400	21,000	13.50	11.30	1333171
	CA*F3030*6B*	G*V80704B**	28,400	21,000	13.50	11.30	1333172
	CA*F3030*6B*	G*V90704C**	28,400	21,000	14.00	11.60	1333173
	CA*F3030*6B*	G*V950453B**	28,400	21,000	14.00	11.60	1333174
	CA*F3030*6B*	G*V950704C**	28,400	21,000	14.00	11.60	1333175
	CA*F3030*6B*+EEP		28,400	21,000	13.00	11.00	1333176
	CA*F3131*6A*	G*E80704B**	28,600	21,200	14.00	11.60	1332924
	CA*F3131*6A*	G*V80704B**	28,600	21,200	14.00	11.60	1332925
	CA*F3131*6A*	G*V90704C**	28,600	21,200	14.00	11.60	1332926

See Notes on Page 29.

ARI PERFORMANCE RATINGS (CONT.)

Outdoor Unit	Indoor Units		Cooling Capacity (BTU/h)				ARI #
	Indoor Coil & Blower	Furnace	Total	Sensible	SEER ¹	EER ²	
GSX13 0301A* (cont.)	CA*F3131*6A*	G*V950453B**	28,600	21,200	14.00	11.60	1332927
	CA*F3131*6A*	G*V950704C**	28,600	21,200	14.00	11.60	1332928
	CA*F3131*6A*+EEP		28,600	21,200	13.00	11.00	1332929
	CA*F3131*6A*+MBE1200**-1		28,400	21,000	14.00	11.60	1332930
	CA*F3131*6B*	G*E80704B**	28,600	21,200	14.00	11.60	1333177
	CA*F3131*6B*	G*V80704B**	28,600	21,200	14.00	11.60	1333178
	CA*F3131*6B*	G*V90704C**	28,600	21,200	14.00	11.60	1333179
	CA*F3131*6B*	G*V950453B**	28,600	21,200	14.00	11.60	1333180
	CA*F3131*6B*	G*V950704C**	28,600	21,200	14.00	11.60	1333181
	CA*F3131*6B*+EEP		28,600	21,200	13.00	11.00	1333182
	CA*F3131*6B*+MBE1200**-1		28,400	21,000	14.00	11.60	1333156
	CA*F3131*6C*	G*E80704B**	28,600	21,200	14.00	11.60	1386224
	CA*F3131*6C*	G*V80704B**	28,600	21,200	14.00	11.60	1386225
	CA*F3131*6C*	G*V90704C**	28,600	21,200	14.00	11.60	1386226
	CA*F3131*6C*	G*V950453B**	28,600	21,200	14.00	11.60	1386227
	CA*F3131*6C*	G*V950704C**	28,600	21,200	14.00	11.60	1386228
	CA*F3131*6C*+EEP		28,600	21,200	13.00	11.00	1386230
	CA*F3131*6C*+MBE1200**-1		28,400	21,000	14.00	11.60	1386231
	CHPF2430B6A*	G*E80704B**	28,400	21,000	14.00	11.60	1332931
	CHPF2430B6A*	G*V80704B**	28,400	21,000	14.00	11.60	1332932
	CHPF2430B6A*	G*V90704C**	28,400	21,000	14.00	11.60	1332933
	CHPF2430B6A*	G*V950453B**	28,400	21,000	14.00	11.60	1332934
	CHPF2430B6A*+EEP		28,400	21,000	13.00	11.00	1333011
	CHPF2430B6A*+MBE1200**-1		28,400	21,000	14.00	11.60	1333031
	CHPF2430B6B*	G*E80704B**	28,400	21,000	14.00	11.60	1332935
	CHPF2430B6B*	G*V80704B**	28,400	21,000	14.00	11.60	1332936
	CHPF2430B6B*	G*V90704C**	28,400	21,000	14.00	11.60	1332937
	CHPF2430B6B*	G*V950453B**	28,400	21,000	14.00	11.60	1332938
	CHPF2430B6B*+EEP		28,400	21,000	13.00	11.00	1332939
	CHPF2430B6B*+MBE1200**-1A*		28,400	21,000	14.00	11.60	1333229
	CSCF3036N6A*	G*E80704B**	28,400	21,000	14.00	11.60	1332940
	CSCF3036N6A*	G*V80704B**	28,400	21,000	14.00	11.60	1332941
	CSCF3036N6A*	G*V90704C**	28,400	21,000	14.00	11.60	1332942
	CSCF3036N6A*	G*V950453B**	28,400	21,000	14.00	11.60	1332943
	CSCF3036N6A*+EEP		28,400	21,000	13.00	11.00	1332944
	CSCF3036N6B*	G*E80704B**	28,400	21,000	14.00	11.60	1333032
	CSCF3036N6B*	G*V80704B**	28,400	21,000	14.00	11.60	1333033
	CSCF3036N6B*	G*V90704C**	28,400	21,000	14.00	11.60	1333034
	CSCF3036N6B*	G*V950453B**	28,400	21,000	14.00	11.60	1333035
	CSCF3036N6B*+EEP		28,400	21,000	13.00	11.00	1333036
	CT*F3030*6A*	G*E80704B**	28,400	21,000	13.50	11.30	1449792

See Notes on Page 29.

ARI PERFORMANCE RATINGS (CONT.)

Outdoor Unit	Indoor Units		Cooling Capacity (BTU/h)				ARI #
	Indoor Coil & Blower	Furnace	Total	Sensible	SEER ¹	EER ²	
GSX13 0301A* (cont.)	CT*F3030*6A*	G*V80704B**	28,400	21,000	13.50	11.30	1449793
	CT*F3030*6A*	G*V90704C**	28,400	21,000	14.00	11.60	1449794
	CT*F3030*6A*	G*V950453B**	28,400	21,000	14.00	11.60	1449795
	CT*F3030*6A*	G*V950704C**	28,400	21,000	14.00	11.60	1449796
	CT*F3030*6A*+EEP		28,400	21,000	13.00	11.00	1449797
	CT*F3131*6A*	G*E80704B**	28,600	21,200	14.00	11.60	1449798
	CT*F3131*6A*	G*V80704B**	28,600	21,200	14.00	11.60	1449799
	CT*F3131*6A*	G*V90704C**	28,600	21,200	14.00	11.60	1449800
	CT*F3131*6A*	G*V950453B**	28,600	21,200	14.00	11.60	1449801
	CT*F3131*6A*	G*V950704C**	28,600	21,200	14.00	11.60	1449802
	CT*F3131*6A*+EEP		28,600	21,200	13.00	11.00	1449803
	CT*F3131*6A*+MBE1200**-1		28,400	21,000	14.00	11.60	1449804
GSX13 0361A*	ADPF304216A*		35,000	25,200	13.00	11.00	1332945
	ADPF304216B*		35,000	25,200	13.00	11.00	1492498
	AEPF303616A*		35,000	25,200	14.00	11.60	1332946
	AEPF303616B*		35,000	25,200	14.00	11.60	1487021
	AEPF303616C*		35,000	25,200	14.00	11.60	1443923
	AR*F363616A*		34,400	24,800	13.00	11.00	1438784
	AR*F363616B*		34,400	24,800	13.00	11.00	1492499
	AR*F364216A*		35,000	25,200	13.00	11.00	1333037
	AR*F364216B*		35,000	25,200	13.00	11.00	1483000
	ASPF303616A*		35,000	25,200	14.00	11.60	1333038
	ASPF303616B*		35,000	25,200	14.00	11.60	1443943
	AT*F363616A*		34,400	24,800	13.00	11.00	1483512
	AT*F364216A*		35,000	25,200	13.00	11.00	1483522
	AWUF36XX16A*		33,400	24,000	13.00	11.00	3001417
	AWUF37XX16A*		34,000	24,500	13.00	11.00	3001418
	CA*F3636*6A*	G*E80704B**	35,000	25,200	13.50	11.30	1332947
	CA*F3636*6A*	G*E80905C**	35,000	25,200	13.50	11.30	1332948
	CA*F3636*6A*	G*V80704B**	35,000	25,200	13.50	11.30	1332949
	CA*F3636*6A*	G*V80905C**	35,000	25,200	13.50	11.30	1332950
	CA*F3636*6A*	G*V90905D**	35,000	25,200	13.50	11.30	1332951
	CA*F3636*6A*	G*V950905D**	35,000	25,200	13.50	11.30	1332952
	CA*F3636*6A*	G*V951155D**	35,000	25,200	13.50	11.30	1332953
	CA*F3636*6A*+EEP		35,000	25,200	13.00	11.00	1332954
	CA*F3636*6B*	G*E80704B**	35,000	25,200	13.50	11.30	1333183
	CA*F3636*6B*	G*E80905C**	35,000	25,200	13.50	11.30	1333184
	CA*F3636*6B*	G*V80704B**	35,000	25,200	13.50	11.30	1333185
	CA*F3636*6B*	G*V80905C**	35,000	25,200	13.50	11.30	1333186
	CA*F3636*6B*	G*V90905D**	35,000	25,200	13.50	11.30	1333187
	CA*F3636*6B*	G*V950905D**	35,000	25,200	13.50	11.30	1333188

See Notes on Page 29.

ARI PERFORMANCE RATINGS (CONT.)

Outdoor Unit	Indoor Units		Cooling Capacity (BTU/h)				ARI #
	Indoor Coil & Blower	Furnace	Total	Sensible	SEER ¹	EER ²	
GSX13 0361A* (cont.)	CA*F3636*6B*	G*V951155D**	35,000	25,200	13.50	11.30	1333189
	CA*F3636*6B*+EEP		35,000	25,200	13.00	11.00	1333190
	CA*F3642*6A*	G*E80704B**	35,400	25,500	14.00	11.60	1332955
	CA*F3642*6A*	G*E80905C**	35,400	25,500	14.00	11.60	1332956
	CA*F3642*6A*	G*V80704B**	35,400	25,500	14.00	11.60	1332957
	CA*F3642*6A*	G*V80905C**	35,400	25,500	14.00	11.60	1332958
	CA*F3642*6A*	G*V90905D**	35,400	25,500	14.00	11.60	1332959
	CA*F3642*6A*	G*V950905D**	35,400	25,500	14.00	11.60	1332960
	CA*F3642*6A*	G*V951155D**	35,400	25,500	14.00	11.60	1332961
	CA*F3642*6A*+MBE1600**-1		35,400	25,500	14.00	11.60	1332962
	CA*F3642*6B*	G*E80704B**	35,400	25,500	14.00	11.60	1333191
	CA*F3642*6B*	G*E80905C**	35,400	25,500	14.00	11.60	1333192
	CA*F3642*6B*	G*V80704B**	35,400	25,500	14.00	11.60	1333193
	CA*F3642*6B*	G*V80905C**	35,400	25,500	14.00	11.60	1333194
	CA*F3642*6B*	G*V90905D**	35,400	25,500	14.00	11.60	1333195
	CA*F3642*6B*	G*V950905D**	35,400	25,500	14.00	11.60	1333196
	CA*F3642*6B*	G*V951155D**	35,400	25,500	14.00	11.60	1333197
	CA*F3642*6B*+MBE1600**-1		35,400	25,500	14.00	11.60	1333198
	CHPF3636B6A*	G*E80704B**	35,000	25,200	13.50	11.30	1332963
	CHPF3636B6A*	G*V80704B**	35,000	25,200	13.50	11.30	1332964
	CHPF3636B6A*+EEP		35,400	25,500	13.00	11.00	1332965
	CHPF3636B6B*	G*E80704B**	35,000	25,200	13.50	11.30	1332966
	CHPF3636B6B*	G*V80704B**	35,000	25,200	13.50	11.30	1332967
	CHPF3636B6B*+EEP		35,400	25,500	13.00	11.00	1332968
	CHPF3642C6A*	G*E80905C**	35,000	25,200	14.00	11.60	1332969
	CHPF3642C6A*	G*V80905C**	35,000	25,200	14.00	11.60	1332970
	CHPF3642C6A*+EEP		35,400	25,500	13.00	11.00	1332972
	CHPF3642C6A*+MBE1600**-1		35,400	25,500	14.00	11.60	1332971
	CHPF3642C6B*	G*E80905C**	35,000	25,200	14.00	11.60	1332973
	CHPF3642C6B*	G*V80905C**	35,000	25,200	14.00	11.60	1332974
	CHPF3642C6B*+EEP		35,400	25,500	13.00	11.00	1332976
	CHPF3642C6B*+MBE1600**-1		35,400	25,500	14.00	11.60	1332975
	CHPF3642D6A*	G*V90905D**	35,000	25,200	14.00	11.60	1332977
	CHPF3642D6A*	G*V950905D**	35,000	25,200	14.00	11.60	1332978
	CHPF3642D6A*	G*V951155D**	35,000	25,200	14.00	11.60	1332979
	CHPF3642D6A*+EEP		35,400	25,500	13.00	11.00	1332980
	CHPF3642D6B*	G*V90905D**	35,000	25,200	14.00	11.60	1332981
	CHPF3642D6B*	G*V950905D**	35,000	25,200	14.00	11.60	1332982
	CHPF3642D6B*	G*V951155D**	35,000	25,200	14.00	11.60	1332983
	CHPF3642D6B*+EEP		35,400	25,500	13.00	11.00	1332984
	CSCF3036N6A*	G*V80704B**	35,000	25,200	13.50	11.30	1332985

See Notes on Page 29.

ARI PERFORMANCE RATINGS (CONT.)

Outdoor Unit	Indoor Units		Cooling Capacity (BTU/h)				ARI #
	Indoor Coil & Blower	Furnace	Total	Sensible	SEER ¹	EER ²	
GSX13 0361A* (cont.)	CSCF3036N6A*+EEP		35,000	25,200	13.00	11.00	1332986
	CSCF3036N6B*	G*V80704B**	35,000	25,200	13.50	11.30	1333039
	CSCF3036N6B*+EEP		35,000	25,200	13.00	11.00	1333040
	CSCF3642N6A*	G*E80704B**	35,400	25,500	14.00	11.60	1332987
	CSCF3642N6A*	G*E80905C**	35,400	25,500	14.00	11.60	1332988
	CSCF3642N6A*	G*V80704B**	35,400	25,500	14.00	11.60	1332989
	CSCF3642N6A*	G*V80905C**	35,400	25,500	14.00	11.60	1332990
	CSCF3642N6A*	G*V90905D**	35,400	25,500	14.00	11.60	1332991
	CSCF3642N6A*	G*V950905D**	35,400	25,500	14.00	11.60	1332992
	CSCF3642N6A*	G*V951155D**	35,400	25,500	14.00	11.60	1332993
	CSCF3642N6A*+EEP		35,400	25,500	13.00	11.00	1332994
	CSCF3642N6C*	G*E80704B**	35,400	25,500	14.00	11.60	1332995
	CSCF3642N6C*	G*E80905C**	35,400	25,500	14.00	11.60	1332996
	CSCF3642N6C*	G*V80704B**	35,400	25,500	14.00	11.60	1332997
	CSCF3642N6C*	G*V80905C**	35,400	25,500	14.00	11.60	1333041
	CSCF3642N6C*	G*V90905D**	35,400	25,500	14.00	11.60	1332998
	CSCF3642N6C*	G*V950905D**	35,400	25,500	14.00	11.60	1332999
	CSCF3642N6C*	G*V951155D**	35,400	25,500	14.00	11.60	1333000
	CSCF3642N6C*+EEP		35,400	25,500	13.00	11.00	1333042
	CT*F3636*6A*	G*E80704B**	35,000	25,200	13.50	11.30	1449805
	CT*F3636*6A*	G*E80905C**	35,000	25,200	13.50	11.30	1449806
	CT*F3636*6A*	G*V80704B**	35,000	25,200	13.50	11.30	1449807
	CT*F3636*6A*	G*V80905C**	35,000	25,200	13.50	11.30	1449808
	CT*F3636*6A*	G*V90905D**	35,000	25,200	13.50	11.30	1449809
	CT*F3636*6A*	G*V950905D**	35,000	25,200	13.50	11.30	1449810
	CT*F3636*6A*	G*V951155D**	35,000	25,200	13.50	11.30	1449811
	CT*F3636*6A*+EEP		35,000	25,200	13.00	11.00	1449812
	CT*F3642*6A*	G*E80704B**	35,400	25,500	14.00	11.60	1449813
	CT*F3642*6A*	G*E80905C**	35,400	25,500	14.00	11.60	1449814
	CT*F3642*6A*	G*V80704B**	35,400	25,500	14.00	11.60	1449815
	CT*F3642*6A*	G*V80905C**	35,400	25,500	14.00	11.60	1449816
	CT*F3642*6A*	G*V90905D**	35,400	25,500	14.00	11.60	1449817
	CT*F3642*6A*	G*V950905D**	35,400	25,500	14.00	11.60	1449818
	CT*F3642*6A*	G*V951155D**	35,400	25,500	14.00	11.60	1449819
	CT*F3642*6A*+MBE1600**-1		35,400	25,500	14.00	11.60	1449820
GSX13 0421A*	ADPF304216A*		40,000	29,200	13.00	11.10	1332789
	ADPF304216B*		40,000	29,200	13.00	11.10	1492500
	AEPF426016A*		41,000	29,900	14.00	11.60	1332790
	AEPF426016B*		41,000	29,900	14.00	11.60	1487022
	AR*F364216A*		40,000	29,200	13.00	11.10	1333043
	AR*F364216B*		40,000	29,200	13.00	11.10	1486994

See Notes on Page 37.

ARI PERFORMANCE RATINGS (CONT.)

Outdoor Unit	Indoor Units		Cooling Capacity (BTU/h)				ARI #
	Indoor Coil & Blower	Furnace	Total	Sensible	SEER ¹	EER ²	
GSX13 0421A* (cont.)	ASPF426016A*		41,000	29,900	14.00	11.60	1333044
	ASPF426016B*		41,000	29,900	14.00	11.60	1492501
	AT*F364216A*		40,000	29,200	13.00	11.10	1483523
	CA*F3642*6A*	G*E80905C**	40,000	29,200	13.50	11.30	1332791
	CA*F3642*6A*	G*V80905C**	40,000	29,200	13.50	11.30	1332792
	CA*F3642*6A*	G*V81155C**	40,000	29,200	13.50	11.30	1332793
	CA*F3642*6A*+EEP		40,000	29,200	13.00	11.10	1332794
	CA*F3642*6B*	G*E80905C**	40,000	29,200	13.50	11.30	1333199
	CA*F3642*6B*	G*V80905C**	40,000	29,200	13.50	11.30	1333200
	CA*F3642*6B*	G*V81155C**	40,000	29,200	13.50	11.30	1333201
	CA*F3642*6B*+EEP		40,000	29,200	13.00	11.10	1333202
	CA*F4860*6A*	G*E80905C**	41,000	29,900	14.00	11.60	1332795
	CA*F4860*6A*	G*E81155C**	41,000	29,900	14.00	11.60	1332796
	CA*F4860*6A*	G*V80905C**	41,000	29,900	14.00	11.60	1332797
	CA*F4860*6A*	G*V90905D**	41,000	29,900	14.00	11.60	1332798
	CA*F4860*6A*	G*V91155D**	41,000	29,900	14.00	11.60	1332799
	CA*F4860*6A*	G*V950905D**	41,000	29,900	14.00	11.60	1332800
	CA*F4860*6A*	G*V951155D**	41,000	29,900	14.00	11.60	1332801
	CA*F4860*6A*+EEP		41,000	29,900	13.00	11.10	1333001
	CA*F4860*6A*+MBE1600**-1		41,000	29,900	14.00	11.60	1332802
	CA*F4860*6B*	G*E80905C**	41,000	29,900	14.00	11.60	1333203
	CA*F4860*6B*	G*E81155C**	41,000	29,900	14.00	11.60	1333204
	CA*F4860*6B*	G*V80905C**	41,000	29,900	14.00	11.60	1333205
	CA*F4860*6B*	G*V90905D**	41,000	29,900	14.00	11.60	1333206
	CA*F4860*6B*	G*V91155D**	41,000	29,900	14.00	11.60	1333207
	CA*F4860*6B*	G*V950905D**	41,000	29,900	14.00	11.60	1333208
	CA*F4860*6B*	G*V951155D**	41,000	29,900	14.00	11.60	1333209
	CA*F4860*6B*+EEP		41,000	29,900	13.00	11.10	1333210
	CA*F4860*6B*+MBE1600**-1		41,000	29,900	14.00	11.60	1333157
	CHPF3642C6A*	G*E80905C**	40,000	29,200	13.50	11.30	1332803
	CHPF3642C6A*	G*V80905C**	40,000	29,200	13.50	11.30	1332804
	CHPF3642C6A*	G*V81155C**	40,000	29,200	13.50	11.30	1332805
	CHPF3642C6A*+EEP		40,000	29,200	13.00	11.10	1332806
	CHPF3642C6B*	G*E80905C**	40,000	29,200	13.50	11.30	1332807
	CHPF3642C6B*	G*V80905C**	40,000	29,200	13.50	11.30	1332808
	CHPF3642C6B*	G*V81155C**	40,000	29,200	13.50	11.30	1332809
	CHPF3642C6B*+EEP		40,000	29,200	13.00	11.10	1332810
	CHPF3642D6A*	G*E81155C**	40,000	29,200	13.50	11.30	1332811
	CHPF3642D6A*	G*V90905D**	40,000	29,200	13.50	11.30	1332812
	CHPF3642D6A*	G*V91155D**	40,000	29,200	13.50	11.30	1332813
	CHPF3642D6A*+EEP		40,000	29,200	13.00	11.10	1332814

See Notes on Page 37.

ARI PERFORMANCE RATINGS (CONT.)

Outdoor Unit	Indoor Units		Cooling Capacity (BTU/h)				ARI #
	Indoor Coil & Blower	Furnace	Total	Sensible	SEER ¹	EER ²	
GSX13 0421A* (cont.)	CHPF3642D6B*	G*E81155C**	40,000	29,200	13.50	11.30	1332815
	CHPF3642D6B*	G*V90905D**	40,000	29,200	13.50	11.30	1332816
	CHPF3642D6B*	G*V91155D**	40,000	29,200	13.50	11.30	1332817
	CHPF3642D6B*+EEP		40,000	29,200	13.00	11.10	1332818
	CHPF4860D6A*	G*E80905C**	41,000	29,900	14.00	11.60	1332819
	CHPF4860D6A*	G*E81155C**	41,000	29,900	14.00	11.60	1332820
	CHPF4860D6A*	G*V80905C**	41,000	29,900	14.00	11.60	1332821
	CHPF4860D6A*	G*V81155C**	41,000	29,900	14.00	11.60	1332822
	CHPF4860D6A*	G*V90905D**	41,000	29,900	14.00	11.60	1332823
	CHPF4860D6A*	G*V91155D**	41,000	29,900	14.00	11.60	1332824
	CHPF4860D6A*	G*V951155D**	41,000	29,900	14.00	11.60	1332825
	CHPF4860D6A*+EEP		41,000	29,900	13.00	11.10	1332826
	CHPF4860D6A*+MBE1600**-1		41,000	29,900	14.00	11.60	1333045
	CHPF4860D6C*	G*E80905C**	41,000	29,900	14.00	11.60	1332827
	CHPF4860D6C*	G*E81155C**	41,000	29,900	14.00	11.60	1332828
	CHPF4860D6C*	G*V80905C**	41,000	29,900	14.00	11.60	1332829
	CHPF4860D6C*	G*V81155C**	41,000	29,900	14.00	11.60	1332830
	CHPF4860D6C*	G*V90905D**	41,000	29,900	14.00	11.60	1332831
	CHPF4860D6C*	G*V91155D**	41,000	29,900	14.00	11.60	1332832
	CHPF4860D6C*	G*V951155D**	41,000	29,900	14.00	11.60	1332833
	CHPF4860D6C*+EEP		41,000	29,900	13.00	11.10	1332834
	CHPF4860D6C*+MBE1600**-1		41,000	29,900	14.00	11.60	1333046
	CSCF3642N6A*+EEP		40,000	29,200	13.00	11.50	1332835
	CSCF3642N6C*+EEP		40,000	29,200	13.00	11.50	1332836
	CSCF4860N6A*	G*E80905C**	41,000	29,900	14.00	11.60	1332837
	CSCF4860N6A*	G*E81155C**	41,000	29,900	14.00	11.60	1332838
	CSCF4860N6A*	G*V80905C**	41,000	29,900	14.00	11.60	1332839
	CSCF4860N6A*	G*V81155C**	41,000	29,900	14.00	11.60	1332840
	CSCF4860N6A*	G*V90115D**	41,000	29,900	14.00	11.30	1332841
	CSCF4860N6A*	G*V90905D**	41,000	29,900	14.00	11.30	1332842
	CSCF4860N6A*	G*V951155D**	41,000	29,900	14.00	11.30	1332843
	CSCF4860N6A*+EEP		41,000	29,900	13.00	11.10	1332844
	CSCF4860N6C*	G*E80905C**	41,000	29,900	14.00	11.60	1333047
	CSCF4860N6C*	G*E81155C**	41,000	29,900	14.00	11.60	1333048
	CSCF4860N6C*	G*V80905C**	41,000	29,900	14.00	11.60	1333049
	CSCF4860N6C*	G*V81155C**	41,000	29,900	14.00	11.60	1333050
	CSCF4860N6C*	G*V90115D**	41,000	29,900	14.00	11.30	1333051
	CSCF4860N6C*	G*V90905D**	41,000	29,900	14.00	11.30	1333052
	CSCF4860N6C*	G*V951155D**	41,000	29,900	14.00	11.30	1333053
	CSCF4860N6C*+EEP		41,000	29,900	13.00	11.10	1333054
	CT*F3642*6A*	G*E80905C**	40,000	29,200	13.50	11.30	1449821

See Notes on Page 37.

ARI PERFORMANCE RATINGS (CONT.)

Outdoor Unit	Indoor Units		Cooling Capacity (BTU/h)				ARI #
	Indoor Coil & Blower	Furnace	Total	Sensible	SEER ¹	EER ²	
GSX13 0421A* (cont.)	CT*F3642*6A*	G*V80905C**	40,000	29,200	13.50	11.30	1449822
	CT*F3642*6A*	G*V81155C**	40,000	29,200	13.50	11.30	1449823
	CT*F3642*6A*+EEP		40,000	29,200	13.00	11.10	1449824
	CT*F4860*6A*	G*E80905C**	41,000	29,900	14.00	11.60	1449825
	CT*F4860*6A*	G*E81155C**	41,000	29,900	14.00	11.60	1449826
	CT*F4860*6A*	G*V80905C**	41,000	29,900	14.00	11.60	1449827
	CT*F4860*6A*	G*V90905D**	41,000	29,900	14.00	11.60	1449828
	CT*F4860*6A*	G*V91155D**	41,000	29,900	14.00	11.60	1449829
	CT*F4860*6A*	G*V950905D**	41,000	29,900	14.00	11.60	1449830
	CT*F4860*6A*	G*V951155D**	41,000	29,900	14.00	11.60	1449831
	CT*F4860*6A*+EEP		41,000	29,900	13.00	11.10	1449832
	CT*F4860*6A*+MBE1600**-1		41,000	29,900	14.00	11.60	1449833
GSX13 0481A*	ADPF486016A*		46,000	34,500	13.00	11.30	1332845
	ADPF486016B*		46,000	34,500	13.00	11.30	1492502
	AEPF426016A*		46,000	34,500	14.00	11.60	1332846
	AEPF426016B*		46,000	34,500	14.00	11.60	1487023
	AR*F486016A*		46,000	34,500	13.00	11.30	1333055
	AR*F486016B*		46,000	34,500	13.00	11.30	1492503
	ASPF426016A*		46,000	34,500	14.00	11.60	1333084
	ASPF426016B*		46,000	34,500	14.00	11.60	1492504
	AT*F486016A*		46,000	34,500	13.00	11.30	1483513
	CA*F4860*6A*+EEP		46,000	34,500	13.00	11.30	1332847
	CA*F4860*6A*+MBE2000**-1		46,000	34,500	14.00	11.60	1332848
	CA*F4860*6A*+TXV	G*E80905C**	46,000	34,500	14.00	11.60	1332859
	CA*F4860*6A*+TXV	G*E81155C**	46,000	34,500	14.00	11.60	1332860
	CA*F4860*6A*+TXV	G*V80905C**	46,000	34,500	14.00	11.60	1332861
	CA*F4860*6A*+TXV	G*V81155C**	46,000	34,500	14.00	11.60	1332862
	CA*F4860*6A*+TXV	G*V90115D**	46,000	34,500	14.00	11.60	1332863
	CA*F4860*6A*+TXV	G*V90905D**	46,000	34,500	14.00	11.60	1332864
	CA*F4860*6A*+TXV	G*V950905D**	46,000	34,500	14.00	11.60	1332865
	CA*F4860*6A*+TXV	G*V951155D**	46,000	34,500	14.00	11.60	1332866
	CA*F4860*6B*+EEP		46,000	34,500	13.00	11.30	1333211
	CA*F4860*6B*+MBE2000**-1		46,000	34,500	14.00	11.60	1333158
	CA*F4860*6B*+TXV	G*E80905C**	46,000	34,500	14.00	11.60	1333212
	CA*F4860*6B*+TXV	G*E81155C**	46,000	34,500	14.00	11.60	1333213
	CA*F4860*6B*+TXV	G*V80905C**	46,000	34,500	14.00	11.60	1333214

¹ Seasonal Energy Efficiency Ratio; Certified per ARI 210/240 @ 80°F/ 67°F/ 95°F

² Energy Efficiency Ratio @ 80°F/ 67°F/ 95°F

Notes

- Always check the S&R plate for electrical data on the unit being installed.
- When matching the outdoor unit to the indoor unit, use the piston supplied with the outdoor unit or that specified on the piston kit chart supplied with the indoor unit.
- EEP - Order from Service Dept. Part No. B13707-38 or new Solid State Board B13707-35S. Part No. B13707-38 is not interchangeable with B13707-35S. The Goodman Gas Furnace contains the EEP cooling time delay

ARI PERFORMANCE RATINGS (CONT.)

Outdoor Unit	Indoor Units		Cooling Capacity (BTU/h)				ARI #
	Indoor Coil & Blower	Furnace	Total	Sensible	SEER ¹	EER ²	
GSX130 481A* (cont.)	CA*F4860*6B*+TXV	G*V81155C**	46,000	34,500	14.00	11.60	1333215
	CA*F4860*6B*+TXV	G*V90115D**	46,000	34,500	14.00	11.60	1333216
	CA*F4860*6B*+TXV	G*V90905D**	46,000	34,500	14.00	11.60	1333217
	CA*F4860*6B*+TXV	G*V950905D**	46,000	34,500	14.00	11.60	1333218
	CA*F4860*6B*+TXV	G*V951155D**	46,000	34,500	14.00	11.60	1333219
	CHPF4860D6A*+EEP		46,000	34,500	13.00	11.30	1332849
	CHPF4860D6A*+MBE2000**-1		46,000	34,500	14.00	11.60	1332850
	CHPF4860D6A*+TXV	G*E80905C**	46,000	34,500	14.00	11.60	1332867
	CHPF4860D6A*+TXV	G*E81155C**	46,000	34,500	14.00	11.60	1332868
	CHPF4860D6A*+TXV	G*V80905C**	46,000	34,500	14.00	11.60	1332869
	CHPF4860D6A*+TXV	G*V81155C**	46,000	34,500	14.00	11.60	1332870
	CHPF4860D6A*+TXV	G*V90115D**	46,000	34,500	14.00	11.60	1332871
	CHPF4860D6A*+TXV	G*V90905D**	46,000	34,500	14.00	11.60	1332872
	CHPF4860D6A*+TXV	G*V950905D**	46,000	34,500	14.00	11.60	1332873
	CHPF4860D6A*+TXV	G*V951155D**	46,000	34,500	14.00	11.60	1332874
	CHPF4860D6C*+EEP		46,000	34,500	13.00	11.30	1332851
	CHPF4860D6C*+MBE2000**-1		46,000	34,500	14.00	11.60	1333056
	CHPF4860D6C*+TXV	G*E80905C**	46,000	34,500	14.00	11.60	1332875
	CHPF4860D6C*+TXV	G*E81155C**	46,000	34,500	14.00	11.60	1332876
	CHPF4860D6C*+TXV	G*V80905C**	46,000	34,500	14.00	11.60	1332877
	CHPF4860D6C*+TXV	G*V81155C**	46,000	34,500	14.00	11.60	1332878
	CHPF4860D6C*+TXV	G*V90115D**	46,000	34,500	14.00	11.60	1332879
	CHPF4860D6C*+TXV	G*V90905D**	46,000	34,500	14.00	11.60	1332880
	CHPF4860D6C*+TXV	G*V950905D**	46,000	34,500	14.00	11.60	1332881
	CHPF4860D6C*+TXV	G*V951155D**	46,000	34,500	14.00	11.60	1332882
	CSCF4860N6A*+EEP		46,000	34,500	13.00	11.30	1332852
	CSCF4860N6A*+TXV	G*E80905C**	46,000	34,500	14.00	11.60	1332883
	CSCF4860N6A*+TXV	G*E81155C**	46,000	34,500	14.00	11.60	1332884
	CSCF4860N6A*+TXV	G*V80905C**	46,000	34,500	14.00	11.60	1332885
	CSCF4860N6A*+TXV	G*V81155C**	46,000	34,500	14.00	11.60	1332886
	CSCF4860N6A*+TXV	G*V90115D**	46,000	34,500	14.00	11.60	1332887
	CSCF4860N6A*+TXV	G*V90905D**	46,000	34,500	14.00	11.60	1332888
	CSCF4860N6A*+TXV	G*V950905D**	46,000	34,500	14.00	11.60	1332889
	CSCF4860N6A*+TXV	G*V951155D**	46,000	34,500	14.00	11.60	1332890
	CSCF4860N6C*+EEP		46,000	34,500	13.00	11.30	1333057
	CSCF4860N6C*+TXV	G*E80905C**	46,000	34,500	14.00	11.60	1333058
	CSCF4860N6C*+TXV	G*E81155C**	46,000	34,500	14.00	11.60	1333059
	CSCF4860N6C*+TXV	G*V80905C**	46,000	34,500	14.00	11.60	1333060
	CSCF4860N6C*+TXV	G*V81155C**	46,000	34,500	14.00	11.60	1333061
	CSCF4860N6C*+TXV	G*V90115D**	46,000	34,500	14.00	11.60	1333062
	CSCF4860N6C*+TXV	G*V90905D**	46,000	34,500	14.00	11.60	1333063

See Notes on Page 37.

ARI PERFORMANCE RATINGS (CONT.)

Outdoor Unit	Indoor Units		Cooling Capacity (BTU/h)				ARI #
	Indoor Coil & Blower	Furnace	Total	Sensible	SEER ¹	EER ²	
GSX130 481A* (cont.)	CSCF4860N6C*+TXV	G*V950905D**	46,000	34,500	14.00	11.60	1333064
	CSCF4860N6C*+TXV	G*V951155D**	46,000	34,500	14.00	11.60	1333065
	CT*F4860*6A*+EEP		46,000	34,500	13.00	11.30	1449834
	CT*F4860*6A*+MBE2000**-1		46,000	34,500	14.00	11.60	1449835
	CT*F4860*6A*+TXV	G*E80905C**	46,000	34,500	14.00	11.60	1449836
	CT*F4860*6A*+TXV	G*E81155C**	46,000	34,500	14.00	11.60	1449837
	CT*F4860*6A*+TXV	G*V80905C**	46,000	34,500	14.00	11.60	1449838
	CT*F4860*6A*+TXV	G*V81155C**	46,000	34,500	14.00	11.60	1449839
	CT*F4860*6A*+TXV	G*V90905D**	46,000	34,500	14.00	11.60	1449840
	CT*F4860*6A*+TXV	G*V91155D**	46,000	34,500	14.00	11.60	1449841
	CT*F4860*6A*+TXV	G*V950905D**	46,000	34,500	14.00	11.60	1449842
	CT*F4860*6A*+TXV	G*V951155D**	46,000	34,500	14.00	11.60	1449843
GSX13 0601A*	ADPF486016A*		57,000	39,900	13.00	11.10	1332853
	ADPF486016B*		57,000	39,900	13.00	11.10	1492505
	AEPF426016A*		57,000	39,900	13.50	11.40	1332854
	AEPF426016B*		57,000	39,900	13.50	11.40	1487024
	AR*F486016A*		57,000	39,900	13.00	11.10	1333066
	AR*F486016B*		57,000	39,900	13.00	11.10	1492506
	ASPF426016A*		57,000	39,900	13.50	11.40	1333085
	ASPF426016B*		57,000	39,900	13.50	11.40	1492507
	AT*F486016A*		57,000	39,900	13.00	11.10	1483514
	CA*F4860*6A*+EEP		57,000	39,900	13.00	11.10	1332855
	CA*F4860*6A*+MBE2000**-1		57,000	39,900	13.50	11.40	1333012
	CA*F4860*6A*+TXV	G*E80905C**	57,000	39,900	13.50	11.40	1332891
	CA*F4860*6A*+TXV	G*E81155C**	57,000	39,900	13.50	11.40	1332892
	CA*F4860*6A*+TXV	G*V80905C**	57,000	39,900	13.50	11.40	1332893
	CA*F4860*6A*+TXV	G*V81155C**	57,000	39,900	13.50	11.40	1332894
	CA*F4860*6A*+TXV	G*V90905D**	57,000	39,900	13.50	11.40	1332895
	CA*F4860*6A*+TXV	G*V950905D**	57,000	39,900	13.50	11.40	1332896
	CA*F4860*6A*+TXV	G*V951155D**	57,000	39,900	13.50	11.40	1332897
	CA*F4860*6B*+EEP		57,000	39,900	13.00	11.10	1333220
	CA*F4860*6B*+MBE2000**-1		57,000	39,900	13.50	11.40	1333159
	CA*F4860*6B*+TXV	G*E80905C**	57,000	39,900	13.50	11.40	1333221
	CA*F4860*6B*+TXV	G*E81155C**	57,000	39,900	13.50	11.40	1333222
	CA*F4860*6B*+TXV	G*V80905C**	57,000	39,900	13.50	11.40	1333223
	CA*F4860*6B*+TXV	G*V81155C**	57,000	39,900	13.50	11.40	1333224
	CA*F4860*6B*+TXV	G*V90905D**	57,000	39,900	13.50	11.40	1333225
	CA*F4860*6B*+TXV	G*V950905D**	57,000	39,900	13.50	11.40	1333226
	CA*F4860*6B*+TXV	G*V951155D**	57,000	39,900	13.50	11.40	1333227
	CHPF4860D6A*+EEP		57,000	39,900	13.00	11.10	1332856
	CHPF4860D6A*+MBE2000**-1		57,000	39,900	13.50	11.40	1333013

See Notes on Page 37.

ARI PERFORMANCE RATINGS (CONT.)

Outdoor Unit	Indoor Units		Cooling Capacity (BTU/h)				ARI #
	Indoor Coil & Blower	Furnace	Total	Sensible	SEER ¹	EER ²	
GSX13 0601A* (cont.)	CHPF4860D6A*+TXV	G*E80905C**	57,000	39,900	13.50	11.40	1332898
	CHPF4860D6A*+TXV	G*E81155C**	57,000	39,900	13.50	11.40	1332899
	CHPF4860D6A*+TXV	G*V80905C**	57,000	39,900	13.50	11.40	1332900
	CHPF4860D6A*+TXV	G*V81155C**	57,000	39,900	13.50	11.40	1332901
	CHPF4860D6A*+TXV	G*V90115D**	57,000	39,900	13.50	11.40	1332902
	CHPF4860D6A*+TXV	G*V90905D**	57,000	39,900	13.50	11.40	1332903
	CHPF4860D6A*+TXV	G*V951155D**	57,000	39,900	13.50	11.40	1332904
	CHPF4860D6C*+EEP		57,000	39,900	13.00	11.10	1332857
	CHPF4860D6C*+MBE2000**-1		57,000	39,900	13.50	11.40	1333067
	CHPF4860D6C*+TXV	G*E80905C**	57,000	39,900	13.50	11.40	1332905
	CHPF4860D6C*+TXV	G*E81155C**	57,000	39,900	13.50	11.40	1332906
	CHPF4860D6C*+TXV	G*V80905C**	57,000	39,900	13.50	11.40	1332907
	CHPF4860D6C*+TXV	G*V81155C**	57,000	39,900	13.50	11.40	1332908
	CHPF4860D6C*+TXV	G*V90115D**	57,000	39,900	13.50	11.40	1332909
	CHPF4860D6C*+TXV	G*V90905D**	57,000	39,900	13.50	11.40	1332910
	CHPF4860D6C*+TXV	G*V951155D**	57,000	39,900	13.50	11.40	1332911
	CSCF4860N6A*+EEP		57,000	39,900	13.00	11.40	1332858
	CSCF4860N6A*+TXV	G*E80905C**	57,000	39,900	13.50	11.40	1332912
	CSCF4860N6A*+TXV	G*E81155C**	57,000	39,900	13.50	11.40	1332913
	CSCF4860N6A*+TXV	G*V80905C**	57,000	39,900	13.50	11.40	1332914
	CSCF4860N6A*+TXV	G*V81155C**	57,000	39,900	13.50	11.40	1332915
	CSCF4860N6A*+TXV	G*V90115D**	57,000	39,900	13.50	11.40	1333002
	CSCF4860N6A*+TXV	G*V90905D**	57,000	39,900	13.50	11.40	1332916
	CSCF4860N6A*+TXV	G*V951155D**	57,000	39,900	13.50	11.40	1333003
	CSCF4860N6C*+EEP		57,000	39,900	13.00	11.40	1333068
	CSCF4860N6C*+TXV	G*E80905C**	57,000	39,900	13.50	11.40	1333069
	CSCF4860N6C*+TXV	G*E81155C**	57,000	39,900	13.50	11.40	1333070
	CSCF4860N6C*+TXV	G*V80905C**	57,000	39,900	13.50	11.40	1333071
	CSCF4860N6C*+TXV	G*V81155C**	57,000	39,900	13.50	11.40	1333072
	CSCF4860N6C*+TXV	G*V90115D**	57,000	39,900	13.50	11.40	1333073
	CSCF4860N6C*+TXV	G*V90905D**	57,000	39,900	13.50	11.40	1333074
	CSCF4860N6C*+TXV	G*V951155D**	57,000	39,900	13.50	11.40	1333075
	CT*F4860*6A*+EEP		57,000	39,900	13.00	11.10	1449844
	CT*F4860*6A*+MBE2000**-1		57,000	39,900	13.50	11.40	1449845
	CT*F4860*6A*+TXV	G*E80905C**	57,000	39,900	13.50	11.40	1449846
	CT*F4860*6A*+TXV	G*E81155C**	57,000	39,900	13.50	11.40	1449847
	CT*F4860*6A*+TXV	G*V80905C**	57,000	39,900	13.50	11.40	1449848
	CT*F4860*6A*+TXV	G*V81155C**	57,000	39,900	13.50	11.40	1449849
	CT*F4860*6A*+TXV	G*V90905D**	57,000	39,900	13.50	11.40	1449850
	CT*F4860*6A*+TXV	G*V950905D**	57,000	39,900	13.50	11.40	1449851
	CT*F4860*6A*+TXV	G*V951155D**	57,000	39,900	13.50	11.40	1449852

See Notes on Page 37.

Wiring is subject to change. Always refer to the wiring diagram or the unit for the most up-to-date wiring.




High Voltage:

WARNING

Disconnect all power before servicing or installing this unit. Multiple power sources may be present. Failure to do so may cause property damage, personal injury, or death.

WIRING DIAGRAM — GSX13(18-48)1B



Wiring is subject to change. Always refer to the wiring diagram or the unit for the most up-to-date wiring.

WARNING

High Voltage:
Disconnect all power before servicing or installing this unit. Multiple power sources may be present. Failure to do so may cause property damage, personal injury, or death.

ACCESSORIES

Model	Description	GSX13 018	GSX13 024	GSX13 030	GSX13 036	GSX13 042	GSX13 048	GSX13 060
ABK-20	Anchor Bracket Kit *	X	X	X	X	X	X	X
ASC-01	Anti-Short Cycle Kit	X	X	X	X	X	X	X
CSR-U-1	Hard-start Kit	X	X	X	X			
CSR-U-2	Hard-start Kit					X	X	X
CSR-U-3	Hard-start Kit						X	X
FSK01A ¹	Freeze Protection Kit	X	X	X	X	X	X	X
LSK01A ²	Liquid Line Solenoid Kit	X	X	X	X	X	X	X
TX2N4 ²	TXV Kit	X						
TX3N4 ²	TXV Kit	X	X	X	X			
TX5N4 ²	TXV Kit					X	X	X

* Contains 20 brackets; four brackets needed to anchor unit to pad

¹ Installed on indoor coil

² Field-installed, non-bleed, expansion valve kit — Condensing units and heat pumps with reciprocating compressors require the use of start-assist components when used in conjunction with an indoor coil using a non-bleed thermal expansion valve refrigerant metering device or liquid line solenoid kit.

NOTES

