




## 4-WAY MULTIPOISE FIXED-CAPACITY CONDENSING GAS FURNACE

340AAV

Sizes 040 thru 140



A05086

The model 340AAV MultiPoise Condensing Furnace is specifically designed to meet the needs of the new construction market. This high-efficiency furnace utilizes a unique 4-way multipoise design and compact size to fit where other furnaces will not. The model 340AAV can be installed in any of 4 positions including horizontally in attics or crawlspaces, freeing space formerly used as a utility or furnace room. Except for the 140 size, all sizes of the model 340AAV can be installed in a manufactured (mobile) home when the optional kit is used. With the exception of the 180 size, all sizes can be installed with 2-pipe or 1-pipe venting. The 140 size can be installed only as a 2-pipe system. Sidewall or through-the-roof venting options and the use of PVC pipe eliminate the need for dedicated chimneys or chaseways to facilitate furnace venting. Time-saving installation features yield a very cost effective way to provide new home buyers with a high-efficiency and high-quality home comfort system.

### FEATURES

**3-Pass Primary Heat Exchangers**—This design accelerates heat transfer and extracts heat that conventional heat exchangers waste up the flue. The primary heat exchanger is made of aluminized steel for corrosion resistance.

**Combustion Air and Ventilation**—The 340AAV advanced design allows Schedule 40PVC, PVC-DWV, SDR-21 PVC, SDR-26 PVC (not approved in Canada), ABS-DWV, or ABS-F628 Schedule 40 pipe to bring outdoor air into the furnace for

combustion. The extracted heat lowers the temperature of the combustion products to a point (typically below 115°F) that any of the approved types of pipe can also be used for venting combustion products outside the structure. The combustion-air and vent pipes can terminate through a side wall or through the roof when using 1 of our approved vent termination kits.

**Flow-Through Secondary Heat Exchangers**—Each cell is laminated with our patented Everlastic™ polypropylene for greater resistance to corrosion. This breakthrough in heating technology helps extend the life of the furnace for years of dependable performance. The heat exchanger is positioned in the furnace to extract additional heat from the combustion products regardless of furnace orientation.

**Perfect Light™ Igniter**—Bryant's unique SiN igniter is not only physically robust but it is also electrically robust. It is capable of running at line voltage and does not require complex voltage regulators as do other brands. This unique feature further enhances the reliability of 340AAV gas furnace and continues Bryant's tradition of technology leadership and innovation in providing a reliable and durable product.

**Warranty**—Limited Lifetime Warranty on the heat exchangers for the lifetime of original owner in single family residence; 20 years in other residential and commercial applications. 5 year Limited Warranty on entire unit.

**Control Center**—The printed-circuit board and all internal wiring are factory installed. Convenient terminals permit quick-connection of a thermostat and air conditioning control circuits. Connections for a humidifier and air cleaner are also provided.

**4-Way Multipoise Design**—Allows a model 340AAV to be installed in an upflow, downflow, or horizontal orientation.


The model 340AAV is available in 12 heat/airflow combinations, and when combined with the 4-way design, allows for 48 different applications. Factory configured for upflow application, this furnace can easily be made ready for downflow or horizontal installations.

**Direct or Non-direct Venting**—The 340AAV can be installed as a 1 pipe/Non-Direct vent or 2 pipe/Direct vent furnace except the 140 size which can be installed as 2-pipe only. This provides added flexibility to meet diverse installation needs.

**Insulated Casing**—Foil-faced insulation in the heat exchanger section cuts heat loss. The casing also has the required openings for left- or right-side connection of gas, electric, drain, and vent connections.

**Certifications**—The 340AAV units are CSA (A.G.A./C.G.A.) design certified for use with natural and propane gases, as well as GAMA efficiency rating certified. The furnace is factory-shipped for use with natural gas. A CSA (A.G.A./C.G.A.) listed gas conversion kit is required to convert furnace for use with propane gas. The model 340AAV meets California Air Quality Management District emission requirements. Except for the 140 size unit, all 340AAV models can be installed in a manufactured (mobile) home when the optional kit is used, and in elevations up to 10,000 ft (140 size unit limitation of 7,000 ft).

**Quality Registration**—The 340AAV is engineered and manufactured under an ISO 9001 registered quality system.



**NOTES:**

1. Minimum return-air openings at furnace, based on metal duct. If flex duct is used, see flex duct manufacturer's recommendations for equivalent diameters.

2. Minimum return-air opening at furnace:

  - For 800 CFM—16-in. round or 14 $\frac{1}{2}$  x 12-in. rectangle.
  - For 1200 CFM—20-in. round or 14 $\frac{1}{2}$  x 19 $\frac{1}{2}$ -in. rectangle.
  - For 1600 CFM—22-in. round or 14 $\frac{1}{2}$  x 23 $\frac{1}{4}$ -in. rectangle.
  - For airflow requirements above 1800 CFM, see Air Delivery table in Product Data literature for specific use of single side inlets. The use of both side inlets, a combination of 1 side and the bottom, or the bottom only will ensure adequate return air openings for airflow requirements above 1800 CFM at 0.5° W.C. ESP.

### DIMENSIONS (In.)

UNIT SIZE	A	D	E	SHIP. WEIGHT (LB)
024040	17-1/2	15-7/8	16	165
036040	17-1/2	15-7/8	16	166
024060	17-1/2	15-7/8	16	172
036060	17-1/2	15-7/8	16	174
048060	17-1/2	15-7/8	16	174
036080	17-1/2	15-7/8	16	188
048080	17-1/2	15-7/8	16	194
060080	21	19-3/8	19-1/2	206
048100	21	19-3/8	19-1/2	219
060100	21	19-3/8	19-1/2	221
060120	24-1/2	22-7/8	23	250
060140	24-1/2	22-7/8	23	250



## Controls—Thermostats and Zoning

### Non-Programmable Thermostat Selection

<b>TSTATBBNAC01-C</b>	For use with 1-spd. Air Conditioner - deg. F/C, Auto Changeover
<b>TSTATBBNHP01-C</b>	For use with 1-spd. Air Conditioner - deg. F/C, Auto Changeover
<b>TSTATBBN2S01-C</b>	For use with 2-spd. Air Conditioner - deg. F/C, Auto Changeover
<b>TSTATBBBAC01-B</b>	For use with 1-spd. Air Conditioner - deg. F/C
<b>TSTATBBPRH01-B**</b>	For multi-use / stage configurations - deg. F/C, Auto Changeover/Temperature and Humidity Control

\* Model HP and 2S thermostat must be field converted to air conditioner operation.

\*\*Thermostat Control is versatile and can be configured for multiple use and staging, it must be configured for each specific application.

### Programmable Thermostat Selection

<b>TSTATBBPAC01-B</b>	For use with 1-spd. Air Conditioner - deg. F/C, Auto Changeover, 7-Day Programmable
<b>TSTATBBPHP01-B*</b>	For use with 1-spd. Air Conditioner - deg. F/C, Auto Changeover, 7-Day Programmable
<b>TSTATBBP2S01-B*</b>	For use with 2-spd. Air Conditioner - deg. F/C, Auto Changeover, 7-Day Programmable
<b>TSTATBBSAC01</b>	For use with 1-spd. Air Conditioner - deg. F/C, 5-2 Day Programmable
<b>TSTATBBPDF01-B**</b>	For use with multi-stage applications - deg. F/C, Auto Changeover, 7-Day Programmable
<b>TSTATBBPRH01-B***</b>	For multi-use / stage configurations - deg. F/C, Auto Changeover, 7-Day Programmable/Temperature and Humidity Control

\* Model HP and 2S thermostat must be field converted to air conditioner operation.

\*\*Dual Fuel thermostat is used with furnace and heat pump application

\*\*\*Thermostat Control can be configured for multiple use and staging, it must be configured for each specific application.

### Zoning Control Selection

<b>ZONEBB3Z(AC/HP)01</b>	Zone Perfect Two-Zone kit
<b>ZONEBB2KIT01-B</b>	Zone Perfect Plus 2-Zone kit/Temperature and Humidity Control
<b>ZONEBB4KIT01-B</b>	Zone Perfect Plus 4-Zone kit/Temperature and Humidity Control
<b>ZONEBB8KIT01-B</b>	Zone Perfect Plus 8-Zone kit/Temperature and Humidity Control

## SPECIFICATIONS

UNIT SIZE		024040	036040	024060	036060	048060	036080		
<b>RATINGS AND PERFORMANCE</b>									
Input Btuh*		40,000	40,000	60,000	60,000	60,000	80,000		
Output Capacity BTUH* (ICS)	Direct Vent (2-Pipe)	Upflow	37,000	37,000	56,000	56,000	56,000		
(Shaded capacities are specified on rating plate)		Downflow	37,000	37,000	56,000	56,000	74,000		
		Horizontal	37,000	37,000	56,000	56,000	74,000		
	Non-Direct Vent (1-Pipe)	Upflow	37,000	37,000	56,000	56,000	74,000		
		Downflow	37,000	37,000	56,000	56,000	74,000		
		Horizontal	37,000	37,000	56,000	56,000	74,000		
AFUE%	Direct Vent (2-Pipe)	Upflow	92.3	92.3	92.3	92.3	92.3		
Nonweatherized ICS		Downflow	91.2	91.2	91.2	91.2	91.2		
	Non-Direct Vent (1-Pipe)	Horizontal	92.1	92.1	92.1	92.1	92.1		
Certified Temperature Rise Range °F		30—60	15—45	45—75	30—60	20—50	40—70		
Certified External Static Pressure	Heating	0.10	0.10	0.12	0.12	0.12	0.15		
	Cooling	0.50	0.50	0.50	0.50	0.50	0.50		
Airflow CFM‡	Heating	850	1125	885	1065	1320	1190		
	Cooling	895	1215	900	1200	1545	1245		
<b>ELECTRICAL</b>									
Unit Volts—Hertz—Phase		115—60—1							
Operating Voltage Range Min—Max**		104—127							
Maximum Unit Amps		10.0	14.1	10.2	14.8	14.6	14.3		
Unit Ampacity††		13.4	18.4	13.5	19.3	19.1	18.8		
Minimum Wire Size		14	12	14	12	12	12		
Maximum Wire Length (Ft)‡‡		28	31	27	30	30	30		
Maximum Fuse Size or Ckt Bkr Amps (Time-Delay Type Recommended)		20	15	20	20	20	20		
Transformer (24v)		40va							
External Control	Heating	12va							
Power Available	Cooling	21va							
Air Conditioning Blower Relay		Standard							
<b>CONTROLS</b>									
Limit Control		SPST							
Heating Blower Control (Off Delay)		Factory-Set at 135 Sec							
Burners (Monoport)		4	4	5	5	6	6		
Gas Connection Size		1/2-in. NPT							
<b>GAS CONTROLS</b>									
Gas Valve (Redundant)	Manufacturer	White-Rodgers							
	Min Inlet Pressure (In. wc)	4.5 (Natural Gas)							
	Max Inlet Pressure (In. wc)	13.6 (Natural Gas)							
Ignition Device		Hot Surface							
<b>BLOWER DATA</b>									
Direct-Drive Motor HP (Permanent Split Capacitor)		1/2	3/4	1/2	3/4	3/4	3/4		
Motor Full Load Amps		7.9	11.1	7.9	11.1	11.1	11.1		
RPM (Nominal)—Speeds		1075—4							
Blower Wheel Diameter x Width (In.)		11 x 8	11 x 10	11 x 8	11 x 10	11 x 10	11 x 10		
Filter Size (In.)—Permanent Washable		(1) 20 x 25 x 1				(2) 16 x 25 x 1			
<b>FACTORY-AUTHORIZED AND LISTED, DEALER-INSTALLED OPTIONS</b>									
Gas Conversion Kit—Natural-to-Propane		KGANP4001ALL							
Gas Conversion Kit—Propane-to-Natural		KGAPN3301ALL							
Twining Kit		KGATW0601HSI							
Manufactured (Mobile) Home Kit		KGAMH0102KIT							
Downflow Base***		KGASB0201ALL							
Vent Termination Kit (Bracket Only for 2 Pipes)		2-in.—KGAVT0101BRA 3-in.—KGAVT0201BRA							
Concentric Vent Termination Kit (Single Exit)		2-in.—KGAVT0501CVT 3-in.—KGAVT0601CVT							
Condensate Freeze Protection Kit		KGAHT0101CFP							
Condensate Neutralizer Kit (Obtained Thru RCD)		P908-0001							
Side Filter Rack (Without Filter)—Upflow ONLY		KGAFR0206ALL							
Electronic/Mechanical Air Cleaner		Model EACA, EZXCAB, or FILCAB							
Humidifier		Model HUM							
Heat/Energy Recovery Ventilator		Model HRV							
UV Lights		Model UVL							
Door Gasket Kit		KGBAC0110DGK							

See notes on page 7.

## SPECIFICATIONS

UNIT SIZE		048080	060080	048100	060100	060120	060140
<b>RATINGS AND PERFORMANCE</b>							
Input Btuh*		80,000	80,000	100,000	100,000	120,000	140,000
Output Capacity BTUH* (ICS) (Shaded capacities are specified on rat- ing plate)	Direct Vent (2-Pipe)	Upflow	74,000	74,000	93,000	93,000	112,000
		Downflow	74,000	74,000	93,000	93,000	112,000
		Horizontal	74,000	74,000	93,000	93,000	112,000
AFUE%	Non-Direct Vent (1-Pipe)	Upflow	74,000	74,000	93,000	93,000	112,000
		Downflow	74,000	74,000	93,000	93,000	NA
		Horizontal	74,000	74,000	93,000	93,000	112,000
Nonweatherized ICS	Direct Vent (2-Pipe)	Upflow	92.3	92.3	92.3	92.3	92.3
		Downflow	91.2	91.2	91.2	91.2	91.2
		Horizontal	92.1	92.1	92.1	92.1	92
Certified Temperature Rise Range °F	Non-Direct Vent (1-Pipe)	Upflow		92.1			NA
		Downflow		91			NA
		Horizontal		91			NA
Certified External Static Pressure		Heating	0.10	0.10	0.12	0.12	0.15
		Cooling	0.50	0.50	0.50	0.50	0.50
Airflow CFM†		Heating	850	1125	885	1065	1320
		Cooling	895	1215	900	1200	1545
<b>ELECTRICAL</b>							
Unit Volts—Hertz—Phase				115—60—1			
Operating Voltage Range Min—Max**				104—127			
Maximum Unit Amps		6.1	7.3	6.1	7.1	9.5	7.6
Unit Ampacity††		8.4	10.0	8.4	9.8	12.8	10.4
Minimum Wire Size		14	14	14	14	14	14
Maximum Wire Length (Ft)‡‡		44	37	44	38	29	36
Maximum Fuse Size or Ckt Bkr Amps (Time-Delay Type Recommended)		15	15	15	15	15	15
Transformer (24v)				40va			
External Control	Heating			12va			
Power Available	Cooling			21va			
Air Conditioning Blower Relay				Standard			
<b>CONTROLS</b>							
Limit Control				SPST			
Heating Blower Control (Off Delay)				Factory-Set at 135 Sec			
Burners (Monoport)		2	2	3	3	3	4
Gas Connection Size				1/2-in. NPT			
<b>GAS CONTROLS</b>							
Gas Valve (Redundant)	Manufacturer			White-Rodgers			
	Min Inlet Pressure (In. wc)			4.5 (Natural Gas)			
	Max Inlet Pressure (In. wc)			13.6 (Natural Gas)			
Ignition Device				Hot Surface			
<b>BLOWER DATA</b>							
Direct-Drive Motor HP (Permanent Split Capacitor)		1/5	1/3	1/5	1/3	1/2	1/3
Motor Full Load Amps		4.9	5.8	4.9	5.8	7.9	5.8
RPM (Nominal)—Speeds		1075—3	1075—4	1075—3		1075—4	
Blower Wheel Diameter x Width (In.)		10 x 6	10 x 7	10 x 6	10 x 7	11 x 8	10 x 7
Filter Size (In.)—Permanent Washable				(1) 16 x 25 x 1			
<b>FACTORY-AUTHORIZED AND LISTED, DEALER-INSTALLED OPTIONS</b>							
Gas Conversion Kit—Natural-to-Propane				KGANP4001ALL			
Gas Conversion Kit—Propane-to-Natural				KGAPN3301ALL			
Twining Kit		N/A			KGATW0601HSI		N/A
Manufactured (Mobile) Home Kit				KGAMH0101KIT			
Downflow Base***				KGASB0201ALL			
Vent Termination Kit (Bracket Only for 2 Pipes)		2-in.—KGAVT0101BRA	3-in.—KGAVT0201BRA				
Concentric Vent Termination Kit (Single Exit)		2-in.—KGAVT0501CVT	3-in.—KGAVT0601CVT				
Condensate Freeze Protection Kit			KGAHT0101CFP				
Condensate Neutralizer Kit (Obtained Thru RCD)			P908-0001				
Side Filter Rack (Without Filter)—Upflow ONLY			KGAFR0206ALL				
Electronic/Mechanical Air Cleaner			Model EACB, EZXCAB, or FILCAB				
Humidifier			Model HUM				
Heat/Energy Recovery Ventilator			Model HRV				
UV Lights			Model UVL				
Door Gasket Kit			KGBAC0110DGK				

See notes on page 7.

- \* Gas input ratings are certified for elevations to 2000 ft. For elevations above 2000 ft, reduce ratings 2% for each 1000 ft above sea level. In Canada, derate the unit 5% from 2000 to 4500 ft above sea level.
  - † Capacity and AFUE in accordance with U.S. Government DOE test procedures.
  - ‡ Airflow shown is for bottom only return-air supply. Air delivery above 1800 CFM may require that both sides, a combination of 1 side and bottom, or bottom only of the furnace be used for return air, see Air Delivery table. Where 2 sets of data are listed, the first set is for bottom only return-air supply. The second set is for both sides, or 1 side and bottom return-air supply. A filter is required for each return-air supply.
  - \*\* Permissible voltage limits for proper furnace operation.
  - †† Unit ampacity = 125% of largest component's full load amps plus 100% of all other potential operating components (EAC, humidifier, etc.).
  - ‡‡ Length shown is measured 1 way along wire path between unit and service panel for maximum 2% voltage drop.
  - \*\*\* Required for installation on combustible floors when no coil box is used, or when any coil box other than a Bryant CD5, CK5, or KCAKC cased coil is used.
- N/A—Not applicable  
ICS—Isolated Combustion System

**COMBUSTION-AIR AND VENT PIPING Direct-Vent/2-Pipe (All Sizes) and  
Non-Direct Vent/1-Pipe (Sizes 040 Through 120 Only) Applications**

**MAXIMUM ALLOWABLE PIPE LENGTH (FT)**

ALTITUDE (FT)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY	NUMBER OF 90° ELBOWS						
		TERMINATION TYPE	PIPE DIA (IN.)*		PIPE DIA (IN.)*	1	2	3	4	5	6
			1	2	3	4	5	6			
0 to 2000	40,000	2 Pipe or 2-in Concentric	1	1	5	NA	NA	NA	NA	NA	
			1-1/2	1-1/2	70	70	65	60	60	55	
			2	2	70	70	70	70	70	70	
	60,000	2 Pipe or 2-in Concentric	1-1/2	1-1/2	20	15	10	5	NA	NA	
			2	2	70	70	70	70	70	70	
	80,000	2 Pipe or 2-in Concentric	1-1/2	1-1/2	10	NA	NA	NA	NA	NA	
			2	2	55	50	35	30	30	20	
			2-1/2	2-1/2	70	70	70	70	70	70	
	100,000	2 Pipe or 3-in Concentric	2	2	5	NA	NA	NA	NA	NA	
			2-1/2	2-1/2	40	30	20	20	10	NA	
			3	3	70	70	70	70	70	70	
	120,000	2 Pipe or 3-in. Concentric	2-1/2 one disk	2-1/2	10	NA	NA	NA	NA	NA	
			3†	NA	45	40	35	30	25	20	
			3† no disk	3†	70	70	70	70	70	70	
	140,000	2 Pipe or 3-in. Concentric	2-1/2 one disk	NA	5	NA	NA	NA	NA	NA	
			3† one disk	NA	40	35	30	25	20	15	
			3† no disk	NA	60	56	52	48	44	40	
			4† no disk	NA	70	70	70	70	70	70	
ALTITUDE (FT)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY	NUMBER OF 90° ELBOWS						
		TERMINATION TYPE	PIPE DIA (IN.)*		PIPE DIA (IN.)*	1	2	3	4	5	6
			1	2	3	4	5	6			
2001 to 3000	40,000	2 Pipe or 2-in Concentric	1-1/2	1-1/2	67	62	57	52	52	47	
			2	2	70	70	70	70	70	70	
	60,000	2 Pipe or 2-in Concentric	1-1/2	1-1/2	17	12	7	NA	NA	NA	
			2	2	70	67	66	61	61	61	
	80,000	2 Pipe or 2-in Concentric	2	2	49	44	30	25	25	15	
			2-1/2	2-1/2	70	70	70	70	70	70	
	100,000	2 Pipe or 3-in Concentric	2-1/2	2-1/2	35	26	16	16	6	NA	
			3	3	70	70	70	70	66	61	
	120,000	2 Pipe or 3-in. Concentric	3	NA	14	9	NA	NA	NA	NA	
			NA	3†	63	62	62	61	61	61	
			3† no disk	NA	70	70	63	56	50	43	
			4† no disk	4† no disk	70	70	70	70	70	70	
	140,000	2 Pipe or 3-in. Concentric	3† one disk	NA	20	15	10	5	NA	NA	
			3† no disk	NA	39	35	31	27	23	19	
			4† no disk	NA	70	70	70	70	70	70	
ALTITUDE (FT)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY	NUMBER OF 90° ELBOWS						
		TERMINATION TYPE	PIPE DIA (IN.)*		PIPE DIA (IN.)*	1	2	3	4	5	6
			1	2	3	4	5	6			
3001 to 4000	40,000	2 Pipe or 2-in Concentric	1-1/2	1-1/2	64	59	54	49	48	43	
			2	2	70	70	70	70	70	70	
	60,000	2 Pipe or 2-in Concentric	1-1/2	1-1/2	16	11	6	NA	NA	NA	
			2	2	68	63	62	57	57	56	
	80,000	2 Pipe or 2-in Concentric	2	2	46	41	28	23	22	13	
			2-1/2	2-1/2	70	70	70	70	70	70	
	100,000	2 Pipe or 3-in Concentric	2-1/2	2-1/2	33	24	15	14	5	NA	
			3	3	70	70	70	66	61	56	
	120,000	2 Pipe or 3-in. Concentric	3† no disk	NA	65	58	51	44	38	31	
			NA	3†	59	59	58	57	57	56	
	140,000	2 Pipe or 3-in. Concentric	4† no disk	4† no disk	70	70	70	70	70	70	
			3† one disk	NA	11	6	NA	NA	NA	NA	
			3† no disk	NA	30	26	22	18	14	10	
See notes at end of table											

**COMBUSTION-AIR AND VENT PIPING Direct-Vent/2-Pipe (All Sizes) and  
Non-Direct Vent/1-Pipe (Sizes 040 Through 120 Only) Applications**

**MAXIMUM ALLOWABLE PIPE LENGTH (FT) (CONTINUED)**

ALTITUDE (FT)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY	NUMBER OF 90° ELBOWS					
		TERMINATION TYPE	PIPE DIA (IN.)*		PIPE DIA (IN.)*	1	2	3	4	5
4001 to 5000‡	40,000	2 Pipe or 2-in Concentric	1-1/2	1-1/2	60	55	50	45	44	39
			2	2	70	70	70	70	70	70
	60,000	2 Pipe or 2-in Concentric	1-1/2	1-1/2	15	10	5	NA	NA	NA
			2	2	64	59	58	53	52	52
	80,000	2 Pipe or 2-in Concentric	2	2	44	39	26	21	20	11
			2-1/2	2-1/2	70	70	70	70	70	70
	100,000	2 Pipe or 3-in Concentric	2-1/2	2-1/2	31	22	13	12	NA	NA
			3	3	70	70	67	62	57	52
	120,000	2 Pipe or 3-in. Concentric	3† no disk	NA	53	46	40	33	26	20
			NA	3†	56	55	54	53	52	52
			4† no disk	4† no disk	70	70	70	70	70	70
	140,000	2 Pipe or 3-in. Concentric	3† no disk	NA	21	17	13	9	5	NA
			4† no disk	NA	69	64	59	54	49	44
ALTITUDE (FT)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY	NUMBER OF 90° ELBOWS					
		TERMINATION TYPE	PIPE DIA (IN.)*		PIPE DIA (IN.)*	1	2	3	4	5
5001 to 6000‡	40,000	2 Pipe or 2-in Concentric	1-1/2	1-1/2	57	52	47	42	40	35
			2	2	70	70	70	70	70	70
	60,000	2 Pipe or 2-in Concentric	1-1/2	1-1/2	14	9	NA	NA	NA	NA
			2	2	60	55	54	49	48	47
	80,000	2 Pipe or 2-in Concentric	2	2	41	36	23	18	17	8
			2-1/2	2-1/2	70	70	70	70	70	70
	100,000	2 Pipe or 3-in Concentric	2-1/2	2-1/2	29	21	12	11	NA	NA
			3	3	70	67	62	57	52	47
	120,000	2 Pipe or 3-in. Concentric	3† no disk	NA	42	35	29	22	15	9
			NA	3†	53	52	50	49	48	47
			4† no disk	4† no disk	70	70	70	70	70	70
	140,000	2 Pipe or 3-in. Concentric	3† no disk	NA	12	8	NA	NA	NA	NA
			4† no disk	NA	42	37	32	27	22	17
ALTITUDE (FT)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY	NUMBER OF 90° ELBOWS					
		TERMINATION TYPE	PIPE DIA (IN.)*		PIPE DIA (IN.)*	1	2	3	4	5
6001 to 7000‡	40,000	2 Pipe or 2-in Concentric	1-1/2	1-1/2	53	48	43	38	37	32
			2	2	70	70	68	67	66	64
	60,000	2 Pipe or 2-in Concentric	1-1/2	1-1/2	13	8	NA	NA	NA	NA
			2	2	57	52	50	45	44	43
	80,000	2 Pipe or 2-in Concentric	2	2	38	33	21	16	15	6
			2-1/2	2-1/2	70	70	68	67	66	64
	100,000	2 Pipe or 3-in Concentric	2-1/2	2-1/2	27	19	10	9	NA	NA
			3	3	68	63	58	53	48	43
	120,000	2 Pipe or 3-in. Concentric	3† no disk	NA	31	24	18	11	NA	NA
			NA	3†	49	48	47	45	44	43
			4† no disk	4† no disk	70	70	70	70	67	62
	140,000	2 Pipe or 3-in. Concentric	4† no disk	NA	17	12	7	NA	NA	NA

See notes at end of table

# COMBUSTION-AIR AND VENT PIPING Direct-Vent/2-Pipe (All Sizes) and Non-Direct Vent/1-Pipe (Sizes 040 Through 120 Only) Applications

## MAXIMUM ALLOWABLE PIPE LENGTH (FT) (CONTINUED)

ALTITUDE (FT)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY PIPE DIA (IN.) <sup>*</sup>	NUMBER OF 90° ELBOWS					
		TERMINATION TYPE	PIPE DIA (IN.) <sup>*</sup>		1	2	3	4	5	6
7001 to 8000‡	40,000	2 Pipe or 2-in Concentric	1-1/2	1-1/2	49	44	39	34	33	28
			2	2	66	65	63	62	60	59
	60,000	2 Pipe or 2-in Concentric	1-1/2	1-1/2	12	7	NA	NA	NA	NA
			2	2	53	48	46	41	40	38
	80,000	2 Pipe or 2-in Concentric	2	2	36	31	19	14	12	NA
			2-1/2	2-1/2	66	65	63	62	60	59
	100,000	2 Pipe or 3-in Concentric	2-1/2	2-1/2	25	17	8	7	NA	NA
			3	3	63	58	53	48	43	38
	120,000	2 Pipe or 3-in. Concentric	3† no disk	NA	20	13	7	NA	NA	NA
			NA	3†	46	44	43	41	40	38
			4† no disk	4† no disk	61	56	51	46	41	36
	140,000			NA						
ALTITUDE (FT)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY PIPE DIA (IN.) <sup>*</sup>	NUMBER OF 90° ELBOWS					
		TERMINATION TYPE	PIPE DIA (IN.) <sup>*</sup>		1	2	3	4	5	6
8001 to 9000‡	40,000	2 Pipe or 2-in Concentric	1-1/2	1-1/2	46	41	36	31	29	24
			2	2	62	60	58	56	55	53
	60,000	2 Pipe or 2-in Concentric	1-1/2	1-1/2	11	6	NA	NA	NA	NA
			2	2	49	44	42	37	35	34
	80,000	2 Pipe or 2-in Concentric	2	2	33	28	17	12	10	NA
			2-1/2	2-1/2	62	60	58	56	55	53
	100,000	2 Pipe or 3-in Concentric	2-1/2	2-1/2	23	15	7	5	NA	NA
			3	3	59	54	49	44	39	34
	120,000	2 Pipe or 3-in. Concentric	3† no disk	NA	10	NA	NA	NA	NA	NA
			NA	3†	43	41	39	37	35	34
			4† no disk	4† no disk	35	30	25	20	15	10
	140,000			NA						
ALTITUDE (FT)	UNIT SIZE (BTUH)	DIRECT VENT (2-PIPE) ONLY		NON-DIRECT VENT (1-PIPE) ONLY PIPE DIA (IN.) <sup>*</sup>	NUMBER OF 90° ELBOWS					
		TERMINATION TYPE	PIPE DIA (IN.) <sup>*</sup>		1	2	3	4	5	6
9001 to 10,000‡	40,000	2 Pipe or 2-in Concentric	1-1/2	1-1/2	42	37	32	27	25	20
			2	2	57	55	53	51	49	47
	60,000	2 Pipe or 2-in Concentric	2	2	45	40	38	33	31	29
			2-1/2	2-1/2	57	55	53	51	49	47
	80,000	2 Pipe or 2-in Concentric	2	2	30	25	14	9	7	NA
			2-1/2	2-1/2	57	55	53	51	49	47
	100,000	2 Pipe or 3-in Concentric	2-1/2	2-1/2	21	13	5	NA	NA	NA
			3	3	54	49	44	39	34	29
	120,000	2 Pipe or 3-in. Concentric	NA	3†	39	37	35	33	31	29
			4† no disk	4† no disk	10	5	NA	NA	NA	NA
	140,000			NA						

\*Disk usage-Unless otherwise specified, use perforated disk assembly (factory-supplied in loose parts bag). If one disk is stated, separate 2 halves of perforated disk assembly and use shouldered disk half. When using shouldered disk half, install screen side toward inlet box.

†Wide radius elbow.

‡Vent sizing for Canadian installations over 4500 ft (1370 m) above sea level are subject to acceptance by the local authorities having jurisdiction.

NA-Not Allowed; pressure switch will not make.

### NOTES:

1. Do not use pipe size greater than those specified in table or incomplete combustion, flame disturbance, or flame sense lockout may occur.
2. Size both the combustion-air and vent pipe independently, then use the larger diameter for both pipes.
3. Assume two 45° elbows equal one 90° elbow. Wide radius elbows are desirable and may be required in some cases.
4. Elbows and pipe sections within the furnace casing and at the vent termination should not be included in vent length or elbow count.
5. The minimum pipe length is 5 ft for all applications.
6. Use 3-in. diameter vent termination kit for installations requiring 4-in diameter pipe.



**MAXIMUM ALLOWABLE EXPOSED VENT PIPE LENGTH (FT) WITH AND WITHOUT INSULATION  
IN WINTER DESIGN TEMPERATURE AMBIENT\***

UNIT SIZE	WINTER DESIGN TEMPERATURE (°F)	MAX PIPE DIAMETER (IN.)	WITHOUT INSULATION	WITH 3/8-IN. OR THICKER INSULATION†
024040 036040	20	1-1/2	51	70
	0	1-1/2	28	70
	-20	1-1/2	16	70
024060 036060 048060	20	2	65	70
	0	2	35	70
	-20	2	20	70
036080 048080 060080	20	2-1/2	70	70
	0	2-1/2	47	70
	-20	2-1/2	28	70
048100 060100	20	3	70	70
	0	3	50	70
	-20	3	28	70
060120	20	4	70	70
	0	4	48	70
	-20	4	23	70
060140	20	4	70	70
	0	4	57	70
	-20	4	30	70

\* Pipe length (ft) specified for maximum vent pipe lengths located in unconditioned spaces. Vent pipes located in unconditioned space cannot exceed the total allowable pipe length as specified in Maximum Allowable Pipe Length table.

† Insulation thickness based on R value of 3.5 per in.

**CONDENSATE TRAP**




A93026

FRONT VIEW


SIDE VIEW

## ACCESSORIES

### CONCENTRIC VENT FOR DIRECT VENT (2-PIPE) APPLICATION (ALL MODEL SIZES)



### SIDE FILTER RACK\*



A80199

\* Accepts one 16 x 25 x 1 in. filter.

### DIMENSIONS (In.)

PART NO.	A*	B	C	D†	E	F
KGAVT0501CVT	33-3/8	2	3-1/2	16-5/8	6-1/4	5-3/4
KGAVT0601CVT	38-7/8	3	4-1/2	21-1/8	7-3/8	6-1/2

\* Dimension A will change accordingly as dimension D is lengthened or shortened.


† Dimension D may be lengthened to 60 in. maximum. Dimension D may also be shortened by cutting the pipes provided in the kit to 12 in. minimum.

NOTE: See furnace Installation Instructions when venting multiple furnaces near each other.

### LENGTH OF STRAIGHT PIPE PORTION OF COMBUSTION AIR INLET PIPE ASSEMBLY (IN.)


CASING WIDTH	A
17-1/2	8-1/2 ± 1/2
21	10-1/2 ± 1/2
24-1/2	12 ± 1/2

### Combination-Air Pipe for Non-Direct Vent (1-Pipe) Application (Sizes 040 Through 120 Only)




A96211

### ACCESSORY DOWNFLOW SUBBASE



Disassembled



Assembled

FURNACE CASING WIDTH	FURNACE IN DOWNFLOW APPLICATION	PLENUM OPENING*		FLOOR OPENING		HOLE NO. FOR WIDTH ADJUSTMENT
		A	B	C	D	
17-1/2	Furnace with or without Cased Coil Assembly or Coil Box	15-1/8	19	16-3/4	20-3/8	3
21	Furnace with or without Cased Coil Assembly or Coil Box	18-5/8	19	20-1/4	20-3/8	2
24-1/2	Furnace with or without Cased Coil Assembly or Coil Box	22-1/8	19	23-3/4	20-3/8	1



\* The plenum should be constructed 1/4 in. smaller in width and depth than the plenum dimensions shown above.



**AIR DELIVERY—CFM (With Filter)\***


UNIT SIZE	RETURN-AIR SUPPLY	SPEED	EXTERNAL STATIC PRESSURE (In. wc)							
			0.1	0.2	0.3	0.4	0.5	0.6	0.7	0.8
024040	1 side or bottom	High Med-Low Low	1075 850 740	1040 825 700	995 780 650	945 740 620	895 685 565	840 635 515	760 560 455	670 480 385
036040	1 side or bottom	High Med-High Med-Low Low	1470 1315 1125 930	1415 1280 1110 925	1400 1235 1085 910	1285 1180 1045 850	1215 1115 990 830	1120 1035 915 770	995 930 830 705	890 825 740 635
024060	1 side or bottom	High Med-Low Low	1100 890 745	1065 865 710	1005 810 670	945 765 625	900 705 565	805 620 505	730 540 425	610 475 360
036060	1 side or bottom	High Med-High Med-Low Low	1430 1270 1070 915	1375 1260 1055 895	1325 1215 1045 885	1275 1160 1015 865	1200 1105 975 840	1135 1035 920 800	1040 950 850 720	935 850 750 650
048060	1 side or bottom	High Med-High Med-Low Low	1700 1500 1325 1205	1695 1465 1295 1170	1640 1435 1265 1145	1580 1385 1230 1110	1545 1355 1190 1080	1450 1300 1150 1035	1380 1250 1105 990	1310 1185 1050 950
036080	1 side or bottom	High Med-High Med-Low Low	1535 1395 1200 1040	1470 1350 1175 1020	1405 1300 1125 990	1330 1225 1065 960	1245 1155 1030 910	1160 1080 970 860	1065 985 890 785	935 880 780 680
048080	1 side or bottom	High Med-High Med-Low Low	1750 1495 1310 1135	1685 1455 1260 1105	1635 1405 1225 1075	1575 1355 1170 1040	1525 1305 1125 995	1445 1250 1095 995	1380 1185 1040 910	1310 1120 980 860
060080	1 side or bottom	High Med-High Med-Low Low	2200 2100 1815 1560	2175 2025 1760 1555	2085 1945 1720 1515	2025 1865 1670 1460	1925 1785 1620 1435	1820 1700 1550 1390	1735 1620 1480 1340	1635 1540 1405 1270
	both sides or 1 side and bottom	High Med-High	2360 1965	2280 1925	2210 1870	2130 1830	2035 1760	1960 1710	1875 1670	1790 1575
048100	1 side or bottom	High Med-High Med-Low Low	1740 1500 1340 1195	1705 1470 1315 1175	1660 1445 1300 1165	1615 1410 1270 1130	1570 1375 1235 1100	1500 1330 1200 1070	1425 1280 1140 1030	1355 1210 1095 975
060100	1 side or bottom	High Med-High Med-Low Low	2250 2020 1725 1490	2175 1950 1690 1480	2090 1900 1660 1460	2020 1840 1630 1440	1930 1790 1575 1380	1855 1710 1520 1340	1760 1640 1460 1295	1670 1545 1370 1230
	both sides or 1 side and bottom	High Med-High	2360 1960	2315 1940	2265 1930	2200 1900	2130 1850	2055 1800	1965 1740	1890 1660
060120	bottom only	High Med-High Med-Low Low	2350 2100 1770 1545	2250 2015 1720 1520	2160 1955 1675 1465	2070 1875 1620 1415	2000 1810 1575 1365	1885 1710 1515 1325	1790 1650 1450 1265	1635 1540 1365 1185
	both sides or 1 side and bottom	High Med-High	2435 2040	2360 2000	2285 1950	2220 1905	2130 1835	2050 1790	1965 1725	1875 1650
	1 side only	High Med-High	2255 1985	2190 1930	2115 1890	2045 1840	1965 1780	1890 1720	1800 1645	1710 1560
060140	bottom only	High Med-High Med-Low Low	2285 2020 1675 1460	2210 1970 1650 1445	2140 1920 1620 1430	2065 1870 1590 1400	1990 1805 1560 1370	1910 1730 1510 1320	1830 1660 1450 1275	1745 1590 1390 1230
	both sides or 1 side and bottom	High Med-High	2310 1975	2255 1945	2185 1900	2120 1860	2045 1835	1965 1775	1880 1720	1800 1640
	1 side only	High Med-High	2140 1930	2080 1850	2025 1800	1945 1740	1875 1725	1795 1660	1725 1580	1625 1495

\* A filter is required for each return-air supply.

• For horizontal and downflow applications, use "1 side or bottom" or "bottom only" as airflow reference.







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

UNIT MUST BE INSTALLED IN ACCORDANCE  
WITH INSTALLATION INSTRUCTIONS

Cancels: PDS 340M.40.12