











High-performance ventilation solutions

Panasonic is the premier manufacturer of powerful, energy-efficient ventilation fans that quietly exhaust unhealthy, unpleasant or moist air from your home or business. Contractors, builders, architects and homeowners rely on us for our quality and for the wide array of solutions we offer—from bathroom fans with both motion and humidity sensors to remote in-line fans. Panasonic is also proud to be recognized by the EPA for the third consecutive year, garnering their most prestigious ENERGY STAR® honor, the **Sustained Excellence 2012 Award.**

The idea of delivering a breath of fresh air to our customers is consistent with a simple mission statement eloquently articulated by our founder nearly a century ago: Panasonic serves society with high-quality products that make peoples' everyday lives more healthy, productive and enjoyable. This guiding principle continues to drive everything we do and is what we call "ideas for life."

Fresh air driven by fresh ideas. Breathe new life into your environment with Panasonic Ventilation.

Panasonic Advanced Ventilation Solutions

2003 2006
2007 2011 2012

Whisperson Whispervalue Whisperson Whispervalue Whispervalue Solution

Retrofit Solution
ASHRAE 62.2 Complance Solution

ASHRAE 62.2 Complance Solution

Balanced Air Solution
Cal Green Complance Solution
Design Solution



Panasonic Ventilation

Fan Benefits

Certified & Code Compliant

Panasonic ventilation fans are certified by the Home Ventilating Institute (HVI) and ENERGY STAR® qualified, where guidelines exist. All models also comply with ASHRAE 62.2, the ventilation standard required by LEED for Homes, ENERGY STAR IAP, CalGreen, NAHB Green Building Standard, EarthCraft, Washington Ventilation Code and other building programs.

Powerful & Quiet

Fully enclosed DC and AC condenser motors assure remarkable performance and quiet operation at industry standard, .25" w.g.

Long Life

Permanently lubricated motors are engineered for trouble-free, continuous operation for 30,000 hours on AC motors, along with rust-proof paint and galvanized housing.

Easy Installation

Detachable duct adapters, adjustable mounting brackets (up to 24" o.c.), fan/motor units that easily detach from the housing and uncomplicated wiring all lend to user-friendly installation. Doublehanger bar systems allowing for ideal positioning.

Energy Savings

For high energy efficiency, input wattage readings are among the lowest in the industry.

Safety

WhisperGreen models are protected by UL Class 2 Power Unit while all other models are equipped with thermal fuse protection. With the exception of

the ERV and heater fans, all models are UL listed for tub/shower enclosure when used with a GFCI branch circuit wire.

Airflow

A built-in damper in all ceiling-mounted models prevents backdraft.

Illumination

ENERGY STAR rated compact fluorescent light bulbs can be used to comply with Title 24 has 10,000 hours of rated life and a 4-Watt night light are available on select models.

Green Manufacturing

All fan only models are RoHS Approved. Restriction of Hazardous Substances Directive (RoHS) restricts the use of the following six substances in the manufacturing process: Lead, Mercury, Cadium, Hexavalent chromium [CR(VI)], Polybrominated biphenyls (PBB), and Polybrominated diphenyl ether (PBDE).

Warranty

6 Year warranty on DC motor and 3 Year warranty on all other models and parts.



Panasonic ideas for life

Fans with Built-in Controls

Whisper Green



FV-08VKM3 80 CFM 4" or 6" Duct FV-13VKM3 130 CFM 6" Duct FV-08VKS3 80 CFM 4" or 6" Duct FV-13VKS3 130 CFM 6" Duct



WhisperGreen Key Benefits:

- SmartFlow[™] technology for optimal CFM output
- Fully enclosed DC motor for long life rated for 60,000 hours continuous run
- SmartAction® motion sensor (FV-08VKM3, FV-13VKM3)
- · Built-in variable speed controls and high/low delay timer up to 60 minutes
- Detachable dual 4" or 6" duct adapter on 80 CFM models
- Fits in 2 x 8 construction



Variable Speed Models Only







FV-08VQC5 80 CFM 4" or 6" Duct FV-11VQC5 110 CFM 4" or 6" Duct





WhisperSense Key Benefits:

- Dual motion and humidity sensors with versatile functionality
 - Motion On / Motion Off
 - Motion On / Humidity Off
 - Humidity On / Humidity Off
- · Adjustable delay timer from 30 seconds to 60 minutes
- Variable humidity controls from 30-80% RH (Relative Humidity)
- · Built-in sensors, timers and controls
- Detachable dual 4" or 6" duct adapter included
- Fits in 2 x 8 construction



Built-in Controls

Whisperwelcome"



FV-05VFM2 50 CFM 4" or 3" Duct FV-08VFM2 80 CFM 4" or 3" Duct



6

WhisperWelcome Key Benefits:

- Low profile housing design Ideal for remodeling!
- SmartAction® motion sensor with built-in 20-minute delay timer
- Fits in 2 x 6 & 2 x 8 construction



INCLUDED: 4 to 3 inch adapter

Single Speed Fans (On/Off)

Whisper Green



FV-05VK3 50 CFM 4" or 6" Duct **FV-08VK3** 80 CFM 4" or 6" Duct

FV-11VK3 110 CFM 4" or 6" Duct

WhisperGreen Key Benefits:

- SmartFlow[™] technology for optimal CFM output
- Fully enclosed DC motor for long life rated for 60,000 hours continuous run
- Detachable dual 4" or 6" duct adapter included
- Fits 2 X 8 construction

Whisperceiling"



FV-05VQ5 50 CFM 4" or 6" Duct **FV-15VQ5** 150 CFM 6" Duct

FV-08VQ5 80 CFM 4" or 6" Duct **FV-11VQ5** 110 CFM 4" or 6" Duct

WhisperCeiling Key Benefits:

- Detachable dual 4" or 6" duct adapter on 50-110 CFM models
- Fits 2 X 8 construction

Whisperfit



FV-05VF2 50 CFM 4" or 3" Duct **FV-08VF2** 80 CFM 4" or 3" Duct **FV-11VF2** 110 CFM 4" or 3" Duct

WhisperFit Key Benefits:

- Low profile housing design Ideal for remodeling!
- Fits in 2 X 6 & 2 X 8 construction



INCLUDED: 4 to 3 inch adapter

Whisper Value



FV-05VS1 50 CFM 4" Oval Duct **FV-08VS1** 80 CFM 4" Oval Duct **FV-10VS1** 100 CFM 4" Oval Duct

8

WhisperValue Key Benefits:

- · Super low profile housing design
- UL listed for wall or ceiling installation
- Fits in 2 x 4, 2 x 6 & 2 x 8 construction

WhisperValue U-Can Contractor Pack

Universal Housing Can	Motor/Grille Assembly	Complete Fan Unit	Master Pack
FV-05-08VSA1	FV-05VSB1	FV-05VS1	4
FV-05-08VSA1	FV-08VSB1	FV-08VS1	4
FV-05-08VSA1	FV-10VSB1	FV-10VS1	4

The Contractor Pack includes four complete fans. The housing and motor/grille are packaged separately for flexibility during installation.

Fan/Lights with Built-in Controls

Whisper Green-Lite





FV-08VKML3 80 CFM 4" or 6" Duct FV-08VKSL3 80 CFM 4" or 6" Duct FV-13VKML3 130 CFM 6" Duct FV-13VKSL3 130 CFM 6" Duct



WhisperGreen-Lite Key Benefits:

- SmartFlow[™] technology for optimal CFM output
- Fully enclosed DC motor for lone life rated for 60,000 hours continuous run
- SmartAction® motion sensor (FV-08VKML3, FV-13VKML3)
- Built-in variable speed controls and high/low delay timer up to 60 minutes
- Detachable dual 4" or 6" duct adapter for 80 CFM models included
- Fits in 2 x 8 construction



80 CFM Variable Spee Models Only





INCLUDES: One 32-Watt Panasonic CFL/3500 Kelvin/High CRI/2400 Lumens/ENERGY STAR® qualified/10,000 hours rated average life/equivalent to (2) 75-Watt incandescent lamp/electronic ballast for flicker-free operation/plus 4-Watt night-light

Whispersense-Lite"



FV-08VQCL5 80 CFM 4" or 6" Duct **FV-11VQCL5** 110 CFM 4" or 6" Duct







Built-in Controls

WhisperSense-Lite Key Benefits:

• Dual motion and humidity sensors with versatile functionality

Motion On / Motion Off

Motion On / Humidity Off

Humidity On / Humidity Off

- · Adjustable delay timer from 30 seconds to 60 minutes
- Variable humidity controls from 30-80% RH (Relative Humidity)
- Built-in sensors, timers and controls
- Detachable dual 4" or 6" duct adapter included
- Fits in 2 x 8 construction



INCLUDES: One 32-Watt Panasonic CFL/3500 Kelvin/High CRI/2400 Lumens/ENERGY STAR® qualified/10,000 hours rated average life/equivalent to (2) 75-Watt incandescent lamp/electronic ballast for flicker-free operation/plus 4-Watt hight-light

Single Speed Fans with Lights (On/Off)

Whisper Recessed





FV-08VRL1 80 CFM 4" or 6" Duct

WhisperRecessed Key Benefits:

- Adjustable lamp positioning and deeper regression reduces glare
- · Beautiful illumination with 6-1/2" aperture



INCLUDED: One 18-Watt GU24 Spiral CFL/2700 Kelvin/84 CRI/1380 Lumens each/ENERGY STAR® qualified/10,000 hours rated average life/equivalent to 75-Watt incandescent lamp/integral electronic ballast for flicker-free operation.

WhisperGreen-Lite





FV-08VKL3 80 CFM 4" or 6" Duct **FV-11VKL3** 110 CFM 4" or 6" Duct

WhisperGreen-Lite Key Benefits:

- SmartFlow™ technology for optimal CFM output
- Fully enclosed DC motor for long life rated for 60,000 hours continuous run
- Detachable dual 4" or 6" duct adapter included
- Fits in 2 x 8 construction

WhisperLite





FV-08VQL5 80 CFM 4" or 6" Duct **FV-11VQL5** 110 CFM 4" or 6" Duct **FV-15VQL5** 150 CFM 6" Duct

WhisperLite Key Benefits:

- Detachable dual 4" or 6" duct adapter on 80-110 CFM models included
- Fits in 2 x 8 construction



INCLUDED with WhisperGreen-Lite, WhisperLite, WhisperFit-Lite, and WhisperValue-Lite: One 32-Watt Panasonic CFL/3500 Kelvin/High CRI/2400 Lumens/ENERGY STAR® qualified/10,000 hours rated average life/equivalent to (2) 75-Watt incandescent lamp/electronic ballast for flickerfree operation/plus 4-Watt night-light

Whisperfit-Lite"





12

FV-05VFL3 50 CFM 4" or 3" Duct **FV-08VFL3** 80 CFM 4" or 3" Duct **FV-11VFL3** 110 CFM 4" or 3" Duct

WhisperFit-Lite Key Benefits:

- Low profile housing design Ideal for remodeling!
- Fits in 2 x 6 & 2 x 8 construction



INCLUDED: 4 to 3 inch adapter

Whisper Value - Lite



FV-08VSL2 80 CFM 4" Oval Duct

WhisperValue-Lite Key Benefits:

- Super low profile housing design
- First in 2 x 4 , 2 x 6 and 2 x 8 construction

WhisperValue-Lite U-Can Contractor Pack

Universal Housing Can	Motor/Grille Assembly	Complete Fan Unit	Master Pack
FV-08VSLA2	FV-08VSLB2	FV-08VSL2	4
FV-08VSLA2	FV-10VSLB2	FV-10VSL2	4

The Contractor Pack includes four complete fans. The housing and motor/grille are packaged separately for flexibility during installation.

Specialty Fans

Whisperwarm"

FV-11VH2 110 CFM 4" Duct FV-11VHL2 110 CFM 4" Duct

WhisperWarm Key Benefits:

- Durable 1400 Watt stainless steel sheathed heating element
- Thermal fuse protection on motor and 3-level safety device for heater
- Quick 1 minute warm-up
- Fits in 2 x 8 construction



INCLUDES: Two 18-Watt Panasonic CFL/3500 Kelvin/ High CRI/1200 Lumens each/ENERGY STAR® qualified/10,000 hours rated average life/equivalent to 100-Watt incandescent lamp/electronic ballast for flickerfree operation/plus 4-Watt night-light

Whisperceiling



FV-20VQ3 190 CFM 6" Duct FV-30V03 290 CFM 6" Duct FV-40V03 380 CFM 6" Duct



WhisperCeiling Key Benefits:

· Large volume exhaust fans ideal for light commercial applications

Whisper/



FV-08WQ1 70 CFM



WhisperWall Key Benefits:

- UL listed for through-the-wall application
- 10" galvanized sleeve and steel exterior hood included



Exterior Hood included

WhisperComfort"







Supply and exhaust air flows through a single exterior opening

FV-04VE1 FV-WC04VE1

14

40/20 CFM or 20/10 CFM 2x4" Ducts

FV-EB04VE1

Optional Exterior Wall Cap

Optional Elbow

WhisperComfort Key Benefits:

- ERV balances air pressure by supplying fresh exterior air while exhausting stale interior air
- · MERV 6 supply filter and damper employed
- · Exchange capillary core recovers temperature and moisture
- Dual setting air volume for 40/20 or 20/10 CFM
- · Ideal for new air tight houses built to meet energy efficiency standards
- Compact size fits in ceilings and 2 x 8 construction
- Sensible Energy Recovery 66%
- Latent Energy Recovery 33%
- · Does not require a condensation line or drain

Whisperline"



FV-10NLF1 120 CFM 4" Duct **FV-20NLF1** 240 CFM 6" Duct **FV-30NLF1** 340 CFM 6" Duct FV-40NLF1 380 CFM 8" Duct



WhisperLine Key Benefits:

- · Remote mount in-line fan for single or multiple inlets
- · Insulated housing to prevent condensation and noise
- Tapered duct adapter for easy connection
- 5 positions for installation
- · Joist or truss attachment brackets included
- · Suspension brackets included

WhisperControl

Condensation Sensor

On/Off-

FV-WCCS1-W (White) FV-WCCS1-A (Light Almond)

On/Off/Light— **FV-WCCS2-W** (White) **FV-WCCS2-A** (Light Almond)







WhisperControl Condensation Sensor Features & Benefits:

- Humidity Control Automatically turns on when relative humidity and temperature change is detected
- 30 minute countdown timer
- Manual On/Off Control
- Compatible with single-speed fans or fan/lights
- Stylish design with wall plate included
- 1 year limited warranty
- ENERGY STAR®, LEED for Homes, ASHRAE 62.2, and CALGreen compliant
- LED indicator

WhisperControl

Switches

1 Function Control

FV-WCSW11-W (White) FV-WCSW11-A (Light Almond)



WhisperControl Switches Features & Benefits:

- Pilot light rocker visible when fan is on
- Back & side wiring terminals accept both solid & stranded wire for easier installation
- Full-rated current capacity with fluorescent or resistive loads.
 Motor capacity is 80% of switch rating
- Commercial grade
- Includes matching wall plate

WhisperControl

Switches

2 Function Control

FV-WCSW21-W (White) FV-WCSW21-A (Light Almond)



WhisperControl Switches Features & Benefits:

- Multi-switch combination saves space and adds convenience
- Common feed shunted internally to all switches
- Includes matching wall plate
- Commercial grade
- Elegant styling provides multiple controls in a single-gang wall box

WhisperControl

Switches

3 Function Control

FV-WCSW31-W (White)
FV-WCSW31-A (Light Almond)



WhisperControl Switches Features & Benefits:

- Multi-switch combination saves space and adds convenience
- · Common feed shunted internally to all switches
- · Commercial grade
- · Includes matching wall plate
- Elegant styling provides multiple controls in a single-gang wall box

WhisperControl

Switches

4 Function Control

 $\textbf{FV-WCSW41-W} \ (\textbf{White only})$

Designed for model FV-11VHL2 Heater/Fan/Light/Night-light



WhisperControl Switches Features & Benefits:

- Single pole/double throw on-off-on top switch, two single pole on-off switches
- Multi-switch combination saves space and adds convenience
- · Common feed shunted internally to all switches
- Commercial grade
- Includes matching wall plate
- Elegant styling provides multiple controls in a single-gang wall box

WhisperControl

Switches

Preset Count Down Delay Off Timer Switch

FV-WCD01-W (White) FV-WCD01-A (Light Almond)



WhisperControl Switches Features & Benefits:

- Timer switch has four preset buttons options: 10-20-30 or 60 minutes
- LED light indicates countdown time and flashes two minutes before OFF warning
- Press and hold override timer function allows you to hold down the button until LED light indicates it is on
- Multi-switch combination saves space and adds convenience
- Common feed shunted internally to all switches
- Commercial grade
- Elegant styling provides multiple controls in a single-gang wall box
- · Easy installation in single gang wallbox
- · Includes matching wallplate

Cross Reference for Applicable Combination of WhisperControl to Product

	Model	FV-WCCS1-W/A	FV-WCCS2-W/A	FV-WCD01-W/A	FV-WCSW11-W/A	FV-WCSW21-W/A	FV-WCSW31-W/A	FV-WCSW41-W
	Switch Type	Condensation Sensor On/Off	Condensation Sensor On/Off/Light	Delay Off Timer	1 Function Control	2 Function Control	3 Function Control	4 Function Control
	FV-05VK3	х	_	х	x			
	FV-08VK3	х		х	х			
	FV-11VK3	х		х	х			
	FV-08VKL3		x			x	х	
WhisperGreen	FV-11VKL3		x			x	х	
	FV-08VKSL3					X**		
	FV-08VKML3					X**		
	FV-13VKSL3					X**		
	FV-13VKML3					X**		
WhisperRecessed	FV-08VRL1		x			х		
	FV-05VQ5	х		х	x			
	FV-08VQ5	x		х	х			
	FV-11VQ5	x		х	x			
	FV-15VQ5	x		x	x			
WhienerOellin	FV-20VQ3	x		х	x			
WhisperCeiling	FV-30VQ3	х		х	х			
	FV-40VQ3	x		х	x			
	FV-08VQL5		x			x	x	
	FV-11VQL5		x			x	x	
	FV-15VQL5		x			x	x	
W/L:	FV-08VQCL5					X**		
WhisperSense	FV-11VQCL5					X**		
	FV-05VF2	x		x	x			
	FV-08VF2	x		x	x			
WhienerPik	FV-11VF2	x		х	x			
WhisperFit	FV-05VFL3		x			х	x	
	FV-08VFL3		x			x	x	
	FV-11VFL3		x			x	х	
	FV-05VS1	x		х	x			
	FV-08VS1	x		x	x			
WhisperValue	FV-10VS1	х		х	x			
	FV-08VSL2		x			х	х	
	FV-10VSL2		x			х	х	
WhisperWall	FV-08WQ1	x		х	x			
WhisperWarm	FV-11VH2*			X*	Х*			
willsperwarm	FV-11VHL2*			X*				X *
	FV-10NLF1	х		х	x			
Whienard inc	FV-20NLF1	x		x	x			
WhisperLine	FV-30NLF1	x		x	x			
	FV-40NLF1	x		х	x			
WhisperComfort	FV-04VE1					x		

WhisperWelcome, WhisperSense, and WhisperGreen S/M3 models are not compatible with the above switches.

* Needs 1 control per function;

** Switch is for light and night-light only.

Ceiling Radiation Damper

PC-RD05C4










Radiation Damper Features:

- UL classification (UL standard 555C) for use in 1, 2 or 3 hour fire-rated floor/ceiling and roof/ceiling designs
- Compatible with 50-150 CFM fans, fans with motion sensor and select fan/lights
- Galvanized steel frame with 165° F fusible link
- High temperature, non-asbestos, reinforced fiber thermal fabric

Damper Model whisperGreen, WhisperGreen-Lite, WhisperCeiling 50-150 CFM, WhisperCeiling 50-150 CFM, WhisperSenseLite, WhisperSenseLite, WhisperWelcome, WhisperFit, WhisperValue

Passive Inlet Vent

FV-GKF32S1





Inlet Vent Features:

Panasonic Passive Inlet provides make-up air to help balance indoor vs. outdoor air pressure.

- Foam pad reduces outdoor noise and condensation
- Insulation lining to prevent condensation
- · Durable ABS and PP resin body
- 7 stainless steel installation screws included
- Sturdy open/close lever
- · 2-position air delivery

	Passive Inlet	FV-GKF32S1
0	Air Volume Positions	2
Specifications	CFM Settings	12 & 18
	Open/Close Louver Setting	Yes
	Washable Air Filter	Yes
Features	Bug Screen	Yes
	3" x 12" Sleeve Included	Yes
	Body	ABS & PP
Installation	Wall Opening (diameter)	3 inch
installation	Installation Screw Included	Yes

PV-GL3TDA FV-GL3TDB

Characteristics	FV-GL3TDA	FV-GL3TDB	FV-GL3MTL
Grille Size (inches sq.)	13	14-1/5	13
Shipping Gross Weight (lbs)	1.1	1.3	1.5
Trend Style Category	Traditional	Traditional	Commercial
Material	ABS	ABS	26 Gauge Galvanized Steel
UL Approved ¹	Yes	Yes	Yes
HVI Certified ¹	Yes	Yes	Yes
Mfg. in ISO 9001 Certified Facility	Yes	Yes	Yes

Designer Grille Features:

- Easy and affordable to change
- Change your grille to fit your room decor without compromising the performance and quality of the unit
- Applicable Models

WhisperGreen: FV-13VKS3, FV-11VK3, FV-08VKS3, FV-08VK3, FV-05VK3

WhisperCeiling: FV-15VQ5, FV-11VQ5,

FV-08VQ5, FV-05VQ5

WhisperFit: FV-11VF2, FV-08VF2, FV-05VF2
WhisperValue: FV-10VS1, FV-08VS1, FV-05VS1

(For FV-GL3MTL only)

Fans with Built-in Controls



WhisperGreen		FV-08VKS3 FV-08VKM3									EV.	121/1	real	LEV	4 2 1/4	rma.						
Characteristics				FV-U	OVR	,3 F	V- Uc	VINIO						FV-13VKS3 FV-13VKM3								
Static pressure in inches w. g.	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25
Air Volume (CFM)	80	79	70	75	60	59	50	54	40	39	30	32	130	135	110	111	90	93	70	71	50	53
Noise (sones)	<0.3	0.4	<0.3	0.4	<0.3	0.3	<0.3	0.3	<0.3	<0.3	<0.3	<0.3	<0.3	0.7	<0.3	0.6	<0.3	0.6	<0.3	0.4	<0.3	<0.3
Power Consumption (Watts)	7.0	11.0	5.4	10.1	5.0	8.7	4.3	7.5	3.7	6.6	3.2	5.8	11.6	21.1	8.7	15.1	6.0	12.1	4.1	9.6	2.4	5.8
Energy Efficiency (CFMs/Watt)	12.1	7.6	13.3	7.7	13.6	7.7	12.4	7.7	12.8	7.1	11.4	6.7	11.2	6.4	12.5	7.3	15.2	7.8	18.7	7.9	23.3	10.0
Speed	832	1130	791	1125	773	1106	749	1101	740	1093	745	1087	662	917	643	912	580	900	506	874	430	781
Current	0.02	0.01	0.03	0.01	0.05	0.01	0.05	0.02	0.05	0.03	0.06	0.04	0.01	0.12	0.03	0.09	0.02	0.07	0.04	0.01	0.06	0.03
Power Rating (V/Hz)		120/60						120/60														



WhisperSense	FV -08	VQC5	FV-11	IVQC5	
Characteristics					
Static pressure in inches w. g.	0.1	0.25	0.1	0.25	
Air Volume (CFM)	80	59	110	91	
Noise (sones)	<0.3	<0.3	0.3	0.5	
Power Consumption (Watts)	15.8	15.6	24.3	24.2	
Energy Efficiency (CFMs/Watt)	5.1	3.9	4.6	3.9	
Speed	825	1110	957	1170	
Current	0.14	0.14	0.22	0.21	
Power Rating (V/Hz)	120)/60	120/60		



WhisperWelcome		FV -0	5VFM2		FV-08VFM2				
Characteristics	4" [Duct	3"	Duct	4" [Duct	3" Duct		
Static pressure in inches w. g.	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	
Air Volume (CFM)	50	30	50	34	80	62	70	56	
Noise (sones)	<0.3	0.7	0.4	0.8	0.9	1.1	0.8	1.0	
Power Consumption (Watts)	16.3	16.0	16.1	16.0	24.5	24.3	24.3	24.0	
Energy Efficiency (CFMs/Watt)	3.6	2.4	3.3	2.2	3.5	2.7	3.1	2.5	
Speed	678	924	740	958	749	945	868	1003	
Current	0.13 0.13 0.13 0.13				0.20	0.19	0.20	0.19	
Power Rating (V/Hz)		12	0/60		120/60				

Single Speed Fans (On/Off)



WhisperGreen	FV- 0	FV-05VK3		08VK3	FV-11VK3		
Characteristics							
Static pressure in inches w. g.	0.1	0.25	0.1	0.25	0.1	0.25	
Air Volume (CFM)	50	54	80	79	110	112	
Noise (sones)	<0.3	0.3	<0.3	0.4	0.3	0.8	
Power Consumption (Watts)	4.3	7.5	7.0	11.0	11.5	16.2	
Energy Efficiency (CFMs/Watt)	12.4	7.7	12.1	7.6	9.7	70	
Speed	749	1101	832	1130	953	1229	
Current	0.05	0.02	0.02	0.01	0.21	0.30	
Power Rating (V/Hz)	120)/60	12	0/60	120/60		

Whisper Ceiling"

WhisperCeiling	EV-0	EVOE	FV-08VQ	5	EV-1	1VQ5	EV-1	EVOE	
Characteristics	FV-05VQ5		FV-05VQ5		LA.AL	1143	FV-15VQ5		
Static pressure in inches w. g.	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	
Air Volume (CFM)	50	36	80	62	110	91	150	127	
Noise (sones)	<0.3	0.4	<0.3	0.4	<0.3	0.5	<0.3	0.5	
Power Consumption (Watts)	11.1	11.7	14.7	14.5	21.1	20.7	28.4	27.3	
Energy Efficiency (CFMs/Watt)	4.7	3.2	5.8	4.5	5.3	4.5	5.3	4.7	
Speed	731	1060	829	1089	950	1161	691	911	
Current	0.09	0.10	0.12	0.12	0.18	0.17	0.24	0.23	
Power Rating (V/Hz)	120/60		120/60		120)/60	120/60		

Whisperfit

WhisperFit	FV-05VF2				FV-08VF2				FV-11VF2			
Characteristics	4" Duct		3" Duct		4" [4" Duct		3" Duct		4" Duct		Duct
Static pressure in inches w. g.	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25
Air Volume (CFM)	50	30	50	31	80	60	70	53	110	94	90	78
Noise (sones)	0.4	0.9	0.5	1.1	0.8	1.0	0.8	1.1	1.5	1.5	1.5	2.0
Power Consumption (Watts)	15.0	14.7	15.0	14.8	24.5	24.3	24.0	24.0	33.5	33.2	33.8	33.5
Energy Efficiency (CFMs/Watt)	3.3	2.0	2.0	2.1	3.3	2.5	2.9	2.2	3.3	2.8	2.7	2.3
Speed	637	932	741	978	757	956	845	1007	830	1000	1029	1128
Current	0.13	0.12	0.13	0.12	0.20	0.20	0.20	0.20	0.28	0.28	0.28	0.28
Power Rating (V/Hz)	120/60				120/60			120/60				

Whisper Value

WhisperValue	FV-0	5VS1	FV-0	8 VS 1	FV-10VS1		
Characteristics	4" Oval Duct		4" Ova	al Duct	4" Oval Duct		
Static pressure in inches w. g.	0.1	0.25	0.1	0.25	0.1	0.25	
Air Volume (CFM)	50	38	80	71	100	90	
Noise (sones)	0.8	N/A	1.3	1.5	1.5	1.5	
Power Consumption (Watts)	15.8	15.3	27.4	27.6	36.4	36.1	
Energy Efficiency (CFMs/Watt)	3.2	2.4	3.4	2.8	2.9	2.7	
Speed (RPM)	759	948	878	1026	840	979	
Current (amps)	0.04 0.04		0.11	0.11	0.30	0.30	
Power Rating (V/Hz)	120	120/60)/60	120/60		

Fan/Lights with Built-in Controls

Whisper Green-Lite

WhisperGreen-Lite			EV.	novk	el a	l EV.	OOVI	(ML3							EV.4	2VK	EL 2	FV -1	SVK	MI 2		
Characteristics			EV-	JOYN	JLJ	I- V-	OBVE	LIVILO							F V- 1	JVK.	JLJ	FV-	SVK	IVILO		
Static pressure in inches w. g.	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25
Air Volume (CFM)	80	79	70	78	60	60	50	52	40	42	30	35	130	137	110	115	90	91	70	69	50	57
Noise (sones)	<0.3	0.6	<0.3	0.6	<0.3	0.5	<0.3	0.5	<0.3	0.5	<0.3	0.5	0.8	1.3	0.6	1.2	0.3	1.1	<0.3	0.9	<0.3	0.8
Power Consumption (Watts)	7.4	12.4	6.0	11.6	5.3	9.0	4.2	7.8	3.8	6.7	3.5	6.2	14.2	24.2	10.7	19.4	7.8	14.9	5.9	10.5	4.1	8.5
Energy Efficiency (CFMs/Watt)	11.2	6.6	11.9	6.8	12.1	7.2	12.5	7.0	11.1	6.6	8.8	5.8	9.0	5.5	10.1	5.8	11.5	6.1	12.0	6.7	12.3	6.7
Speed	866	1166	815	1157	675	941	765	1106	758	1084	611	879	742	968	707	972	676	969	669	932	648	939
Current	0.01	0.02	0.03	0.02	0.05	0.09	0.04	0.02	0.06	0.05	0.04	0.06	0.04	0.15	0.05	0.12	0.03	0.09	0.03	0.01	0.04	0.01
Power Rating (V/Hz)		120/60							120/60													

Whispersense-Lite

WhisperSense-Lite	FV-08\	VOCL 5	FV-11VQCL5				
Characteristics	10-00	4025	11-1114023				
Static pressure in inches w. g.	0.1	0.25	0.1	0.25			
Air Volume (CFM)	80	62	110	91			
Noise (sones)	<0.3	0.4	0.3	0.5			
Power Consumption (Watts)	17.5	17.6	24.3	24.2			
Energy Efficiency (CFMs/Watt)	4.7	3.6	4.3	3.5			
Speed	825	1110	957	1170			
Current	0.14	0.14	0.22	0.21			
Power Rating (V/Hz)	120)/60	120/60				

Single Speed Fans with Lights (On/Off)

Whisper Green-Lite*

WhisperGreen-Lite Characteristics	FV-08	VKL3	FV-11VKL3				
Static pressure in inches w. g.	0.1	0.25	0.1	0.25			
Air Volume (CFM)	80	79	110	108			
Noise (sones)	<0.3	0.6	0.7	1.1			
Power Consumption (Watts)	7.4	12.4	12.5	18.0			
Energy Efficiency (CFMs/Watt)	11.2	6.6	8.9	6.0			
Speed	866	1166	1019	1256			
Current	0.01	0.02	0.25	0.34			
Power Rating (V/Hz)	120)/60	120/60				

WhisperLite*

WhisperLite Characteristics	FV-08	FV-08VQL5		VQL5	FV-15VQL5		
Static pressure in inches w. g.	0.1	0.25	0.1 0.25		0.1	0.25	
Air Volume (CFM)	80	62	110	90	150	128	
Noise (sones)	<0.3	0.4	0.5	0.6	0.9	1.0	
Power Consumption (Watts)	14.9	14.7	23.4	23.0	31.8	30.9	
Energy Efficiency (CFMs/Watt)	5.5	4.3	4.7	3.9	4.8	4.2	
Speed	863	1117	1006	1193	800	988	
Current	0.12 0.12		0.20	0.20 0.19		0.26	
Power Rating (V/Hz)	120)/60	120/60)	120/60		

Whisperfit-Lite"

WhisperFit-Lite		FV-0	5VFL3			FV-08	BVFL3		FV-11VFL3			
Characteristics	4" [Duct	3" [3" Duct		Duct	3" [Duct	4" [Duct	3" Duct	
Static pressure in inches w. g.	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25
Air Volume (CFM)	50	35	50	35	80	67	70	60	110	96	90	78
Noise (sones)	<0.3	0.4	<0.3	0.5	0.5	0.8	0.5	0.8	1.3	1.5	1.5	2.0
Power Consumption (Watts)	15.9	15.8	15.9	15.8	28.8	28.6	28.4	28.0	33.0	32.6	32.5	32.1
Energy Efficiency (CFMs/Watt)	3.5	2.5	3.1	2.2	2.8	2.4	2.6	2.3	3.3	2.9	2.9	2.6
Speed	703	917	769	989	763	962	895	1050	906	1033	1048	1162
Current	0.13	0.13	0.13	0.13	0.24	0.24	0.24	0.23	0.28	0.27	0.27	0.27
Power Rating (V/Hz)		120	0/60		120/60			120/60				

Whisper Value-Lite"

WhisperValue-Lite	FV-08	VSL2	FV-10VSL2			
Characteristics	4" Ova	l Duct	4" Ova	al Duct		
Static pressure in inches w. g.	80	67	100	90		
Air Volume (CFM)	1.3	1.5	1.5	2.5		
Noise (sones)	24.6	25.0	36.6	36.3		
Power Consumption (Watts)	3.3	2.7	2.7	2.5		
Energy Efficiency (CFMs/Watt)	944	1063	911	1019		
Speed (RPM)	0.21	0.21	0.31	0.30		
Current (amps)	0.21	0.21	0.31	0.30		
Power Rating (V/Hz)	120	/60	120/60			

Whisper Recessed

WhisperRecessed	FV-08	VDI 4		
Characteristics	FV-06	VILI		
Static pressure in inches w. g.	0.1 0.25			
Air Volume (CFM)	80	66		
Noise (sones)	0.8	0.7		
Power Consumption (Watts)	20.5	19.5		
Energy Efficiency (CFMs/Watt)	4.0	3.4		
Speed	1378	1501		
Current	0.17 0.17			
Power Rating (V/Hz)	120)/60		



WhisperWarm	FV-1	1VH2	FV-11	VHL2		
Characteristics						
Static pressure in inches w. g.	0.1	0.25	0.1	0.25		
Air Volume (CFM)	110	89	110	89		
Noise (sones)	0.6	1.0	0.7	1.0		
Power Consumption (Watts)	30.7	30.5	30.6	30.5		
Energy Efficiency (CFMs/Watt)	3.6	2.9	3.6	2.9		
Speed	778	935	812	956		
Current	0.25	0.25	0.25	0.25		
Power Rating (V/Hz)	120)/60	120/60			

Whisperceiling"

WhisperCeiling Characteristics	FV-2	o v Q3		FV-30VQ3	FV-40VQ3			
	0.1	0.25	0.1	0.25	0.1	0.25		
Static pressure in inches w. g.	0.1	0.25	0.1	0.25	0.1	0.25		
Air Volume (CFM)	190	145	290	257	390	359		
Noise (sones)	0.8	1.4	2	N/A	3	3		
Power Consumption (Watts)	43.7	42.9	64	62	112	110		
Energy Efficiency (CFMs/Watt)	4.6	3.6	4.5	4.1	3.4	3.2		
Speed	761	949	877	990	774	858		
Current	0.34	0.33	0.53 0.52		0.97	0.96		
Power Rating (V/Hz)	120)/60		120/60	120/60			

Whisper Wall

WhisperWall	FV-08WQ1
Characteristics	FV-03WQ1
Static pressure in inches w. g.	0.03
Air Volume (CFM)	70
Noise (sones)	1.1
Power Consumption (Watts)	18.0
Energy Efficiency (CFMs/Watt)	4.3
Speed	660
Current	0.20
Power Rating (V/Hz)	120/60

Whisper Comfort

WhisperComfort		FV-04VE1	
Characteristics	40 CFM	20 CFM	10 CFM
Static pressure in inches w. g.	0.1	0.1	0.1
Air Volume Exhaust (CFM)	40	20	10
Air Volume Supply (CFM)	30	20	10
Noise (sones)	0.8	<0.3	N/A
Power Consumption (Watts)	23	21	17
Speed	1479	1292	1095
Current	0.15	0.10	0.09
Power Rating (V/Hz)		120/60	

Whisperline"

WhisperLine	EV.	10N	I E4	EV.	20N	I E4	EV.	SUM	I E4	FV-4	ION	E4
Characteristics		·			ZUN			3014			·	
Static pressure in inches w.g.	0.2	0.3	0.4	0.2	0.3	0.4	0.2	0.3	0.4	0.2	0.3	0.4
Air Volume (CFM)	120	105	82	240	225	200	340	322	302	440	421	407
Power Consumption (Watts)	36.2	35.0	33.5	55.5	53.5	51.1	95.2	93.5	91.5	136	132	130
Energy Efficiency (CFMs/Watt)		3.5		4.1			3.2			3.2		
Speed		1590		1260		1337			1150			
Current	0.31		0.46		0.86			1.10				
Power Rating (V/Hz)	1	20/6	0	1	20/6	0	120/60			120/60		

WhisperLine Installation Kits								
Model No.	Description	Inlet Grille	Backdraft Damper	Clamp	Y-Adaptor			
FV-NLF04G	4" Inlet Grille	1 (4")	-	-	-			
FV-NLF06G	6" Inlet Grille	1 (6")	-	-	-			
PC-NLF04S	4" Single Inlet Kit	1 (4")	1 (4")	6	-			
PC-NLF06S	6" Single Inlet Kit	1 (6")	1 (6")	6	-			
PC-NLF04D	4" Double Inlet Kit	2 (4")	2 (4")	12	1 (4"- 4"x 2)			
PC-NLF06D	6" Double Inlet Kit	2 (6")	2 (6")	12	1 (6"- 6"x 2)			
PC-NLF64D	6"-4" Double Inlet Kit	2 (4")	2 (4")	12	1 (6"- 4"x 2)			
PC-NLF86Y	8"-6" Y-Adaptor	-	-	-	1 (8"- 6"x 2)			

Sizing

Information and Instructions

Fan Selection Guide

- 1. What is the size of the bathroom?
- a. Need 1 CFM (cubic foot per minute) per square foot
- b. Length x Width = CFM (length) x (width) = (Total CFM needed)
- c. Example: 8 ft length x 10 ft wide = 80 CFM is needed to properly ventilate the bathroom
- 2. What features are needed/wanted? Fan only? Light? Heat? Variable speed? Motion? Humidity? Time delay?
- **3.** What type of construction is available? Truss size is necessary if it is smaller than 2×8 construction so the selected fan housing size will fit the installation.
- a. 2 x 8 construction can use any fan combination that we have
- b. 2 x 6 construction can use our fan combinations that fit 2 x 6 or 2 x 4 construction
- c. 2 x 4 construction can use our fan combinations that fit 2 x 4 construction
- **4.** Now that you know the CFM needed, the features wanted and the construction size, you are ready to find your fan combination.

Equivalent Duct Length (EDL)

The Equivalent Duct Length Table (Figure B) shows you how to calculate the equivalent straight duct length in order to overcome static pressure. The EDL chart helps ensure fan performs as expected under the airflow resistance caused by the listed components.

A ventilating fan's performance is plotted on a graph called a performance curve. The performance curve shows airflow in cubic feet per minute (CFM) along the horizontal axis and static pressure (resistance) along the vertical axis. Figure A shows how a performance curve works. The fan with a "Closed Duct" has high static pressure and no airflow; and the fan with "No Duct" has low static pressure and high airflow. In reality, an installed fan will be somewhere in between these two points.

Sizing and selecting a Ceiling Mounted Fan:

Proper sizing requires that you determine the needed CFM, the square footage of the room or home, and the length and type of duct.

34

Example: Sizing for an 8 ft x 10 ft x 8 ft ceiling bathroom using 12 foot long, 4 inch diameter aluminum flex duct, one elbow, one wall cap.

Step 1: Determine application

Bathroom = 1 CFM/square foot

Step 2: Calculate the area to be ventilated in square feet.

Assuming an 8 ft ceiling: room length x width = area in square feet

8 ft x 10 ft = 80 sa ft

Step 3: Calculate your required CFM

1 CFM x 80 sq ft = 80 CFM

Step 4: Use the Equivalent Duct Length chart above to calculate duct run.

4a. 12 ft aluminum flex duct x 1.25 = 15 ft

4b. One elbow = 15 ft EDL

4c. One wall cap = 30 ft EDL


15 ft + 15 ft + 30 ft = 60 ft EDL

This is the equivalent duct length (or resistance) the fan must overcome to move air through the duct to the outside.

Step 5: Review models in catalog pages to find a model with desired feature. Features may include light fixture, heater or low-profile housing.

Note: Check with your local building inspector to confirm that these methods are accepted in your area.

FIG. A



Equivalent Duct Length Duct Diameter									
Duct	Smooth Metal	Same as measured duct length							
Material	Flex Aluminum	1.25 x duct length	1.25 X duct length	1.5 X duct length	1.5 X duct length				
	Insulated Flex	1.5 X duct length	1.5 X duct length	1.75 X duct length	1.75 X duct length				
Terminal	Wall Cap	30 feet	30 feet	40 feet	40 feet				
Device	Roof Jack	30 feet	30 feet	40 feet	40 feet				
Elbow	Adjustable	15 feet	15 feet	20 feet	20 feet				